





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




'A' Ø
(MIN)

PANDUIT PART NO.	DIMENSIONS			MAXIMUM BUNDLE DIAMETER	USE WITH PANDUIT PART NO.	WEIGHT lbs 10 (g) pcs.
	A	B	'C'			
PWT38	0.435 (11.05)	3.365 (85.47)	2.506 (63.65)	0.430 (10.92)	PW38	0.26 (117.93)
PWT50	0.560 (14.22)	4.33 (109.98)	3.39 (86.0)	0.55 (13.97)	PW50	0.54 (244.94)
PWT75	0.860 (21.84)			0.81 (20.57)	PW75	0.82 (371.95)
PWT100	1.12 (28.45)	4.65 (118.11)	3.63 (92.2)	1.11 (28.19)	PW100	1.18 (535.24)
PWT150	1.68 (42.67)	5.38 (136.65)	4.53 (115.06)	1.67 (42.42)	PW150	2.32 (1052.3)



NOTES:
1. MATERIAL: ABS
COLOR: WHITE



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G02607DD/01B

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

PAN-WRAP APPLICATION
TOOL (PWT__)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

OIB	8/5/09	TMSA	<i>[Signature]</i>	ADD PWT38 PART NUMBER	GB2607DD	OIB	<i>[Signature]</i>			DRAWN BY	JAD	MAT'L:	SCALE	NONE
I	8/17/04	JAD		ADD PWT100, PWT150, AND 'C' DIM TO TABLE	GB2607DD	I				DATE	10/8/02	SEE NOTE 1	DRAWING NO.	GB2607DD
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D	<i>[Signature]</i>			ORIG A SIZE