

SINGLE-PHASE GLASS PASSIVATED SILICON BRIDGE RECTIFIER


VOLTAGE RANGE 50 to 1000 Volts CURRENT 4.0 Ampere

FEATURES

- * Ideal for printed circuit board
- * Surge overload rating: 150 amperes peak
- * Mounting position: Any

MECHANICAL DATA

- * UL listed the recognized component directory, file #E245106
- * Epoxy: Device has UL flammability classification 94V-O



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 °C ambient temperature unless otherwise specified.
Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

MAXIMUM RATINGS (At TA = 25°C unless otherwise noted)

[illegible]


ELECTRICAL CHARACTERISTICS (At T_A = 25°C unless otherwise noted)

CHARACTERISTICS		SYMBOL	RBU401M	RBU402M	RBU403M	RBU404M	RBU405M	RBU406M	RBU407M	UNITS
Maximum Forward Voltage Drop per Bridgeat Element at 4.0A DC		V _F	1.0							Volts
Maximum Reverse Current at Rated	@ T _A = 25°C	I _R	5.0							uAmps
Dc Blocking Voltage per element	@ T _A = 125°C		0.5							mAmps


NOTES : 1. Measured at 1 MHz and applied reverse voltage of 4.0 volts
2. Unit case mounted on 1.6 x 1.6 x 0.06" thick (4.0 x 4.0 x 0.15cm) Al. Plate
3. Units mounted on P.C.B. with 0.5 x 0.5" (12 x 12mm) copper pads and 0.375" (9.5mm) lead length
4. Equivalent to GS's GBU4X series
5. "Fully ROHS Compliant", "100% Sn Plating(Pb-Free)"

RATING AND CHARACTERISTIC CURVES (RBU401M-RBU407M)


**Fig. 1 — Derating Curve
Output Rectified Current**




**Fig. 2 — Maximum Non-Repetitive
Peak Forward Surge Current Per Leg**




**Fig. 3 — Typical Forward
Characteristics Per Leg**



**Fig. 4 — Typical Reverse Leakage
Characteristics Per Leg**



**Fig. 5 — Typical Junction
Capacitance Per Leg**



**Fig. 6 — Typical Transient
Thermal Impedance**

