




Fig. 1




Fig. 2




Fig. 3




Fig. 4





Fig. 5

- Series 800 and 802 single and double row pin headers use MM #5016 pins. See page 182 for details.
- Series 801 and 803 single and double row sockets use MM #1303 pins. See page 150 for details.
- Series 801 and 803 receptacles use Hi-Rel, 6-finger BeCu #47 contacts rated at 4.5 amps. Receptacles accept .030" diameter and .025" square pins. See page 221 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1	Single Row	Low Profile Pin Header			
	800-XX-0 _ _ -10-002000 Specify # of pins └───→ 01-64				
Fig. 2	Double Row	Low Profile Pin Header			
	802-XX-0 _ _ -10-002000 Specify # of pins └───→ 02-64				
For Electrical, Mechanical & Environmental Data, See pg. 4 XX=Plating Code See Below For RoHS compliance select ◇ plating code.					
SPECIFY PLATING CODE XX=		10◇	90	40◇	
Pin Plating 		10μ" Au	200μ" Sn/Pb	200μ" Sn	
Fig. 3	Single Row	Low Profile Socket (short insulator)			
	801-XX-0 _ _ -10-002000 Specify # of pins └───→ 01-64				
Fig. 4	Single Row	Low Profile Socket (long insulator)			
	801-XX-0 _ _ -10-012000 Specify # of pins └───→ 01-36				
Fig. 5	Double Row	Low Profile Socket			
	803-XX-0 _ _ -10-002000 Specify # of pins └───→ 02-72				
For Electrical, Mechanical & Environmental Data, See pg. 4 XX=Plating Code See Below For RoHS compliance select ◇ plating code.					
SPECIFY PLATING CODE XX=			93	99	43◇
Sleeve (Pin) 			200μ" Sn/Pb	200μ" Sn/Pb	200μ" Sn
Contact (Clip) 			30μ" Au	200μ" Sn/Pb	30μ" Au