





REVISIONS				
P	LN	DESCRIPTION	DATE	BY
A12		REVISED PER ECR-17-013047	12SEP2017	J.Z D.Z

△ NOTE DELETED.

- PARTS COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- WIRE RANGE: 0.3 - 0.6 mm² (22 - 20 AWG).
- INSULATION RANGE: 2.54 [.100] DIA MAX.
- DIMENSIONS IN BRACKETS ARE IN INCHES.



MINI	PRE TIN	0.25 [.010] BRASS	3-42642-3
MINI	PRE TIN-LEAD	0.25 [.010] BRASS	42642-3
APPLICATOR TYPE	FINISH	MATERIAL	PART NUMBER

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		BY: K. WHITAKER 11MAY2008	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK: K. WHITAKER 11MAY2008	TERMINAL, AMP-IN(TM)	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP: K. WHITAKER 11MAY2008	RESTRICTED TO	
D: .010		PRODUCT SPEC	SIZE: 10:1	
F: .010		APPLICATION SPEC	SHEET 1 OF 1	
H: .010		WEIGHT: 0.000000	REV: A12	
MATERIAL: SEE TABLE		CUSTOMER DRAWING	DRAWING NO: A100779	
FINISH: SEE TABLE		PART NUMBER: 3-42642		