



## SERIES 125 AND 126 RETAINERS

### WEIGHT

.40 g/cm (.036 oz/in)

### MATERIALS AND FINISH

#### Material:

.41 (.016) thick Stainless  
Steel Type 301, Cond.  
1/2 H, ASTM -A240

#### Finish:



Passivated per MILS-5002

### SPRING RATE

60.4N/cm (34.5lbs/in)  
of deflection per spring finger

| Dash No. | PCB Thickness | B Dimension<br>+0.38 (.015)<br>-0.0 (.000) | G Dimension<br>+0.0 (.00)<br>-0.80 (.03) |
|----------|---------------|--------------------------------------------|------------------------------------------|
| -06      | 1.6 (1/16)    | 1.91 (.075)                                | 1.14 (.045)                              |
| -09      | 2.4 (3/32)    | 2.67 (.105)                                | 1.91 (.075)                              |

125 Shown, 126 Opposite



#### Part Number Code

|                                                                 |     |       |
|-----------------------------------------------------------------|-----|-------|
| 125 or 126                                                      | -06 | -3.25 |
| PCB Thickness                                                   |     |       |
| 1.6 (.063)                                                      |     | 06    |
| 2.4 (.094)                                                      |     | 09    |
| Length                                                          |     |       |
| 31.75 (1.25) to 311.15 (12.25)                                  |     | 3.25  |
| in 25.4 (1.00) increments<br>Other lengths available on request |     |       |

#### Part Number Code Example:

125-06-4.25  
Series 125 passivated stainless steel,  
107.95 (4.25) long designed for 1.6 (.063)  
thick printed circuit boards