

1N914 & 1N4148-1



Silicon Switching Diode

Rev. V2

Features

- Available in JAN, JANTX, and JANTXV per MIL-PRF-19500/116
- Metallurgically Bonded
- Hermetically Sealed
- Double Plug Construction


Maximum Ratings

Operating & Storage Temperature: -65°C to +200°C

Operating Current: 200 mA @ $T_A = +25^\circ\text{C}$

Derating Factor: 1.14 mA/°C above $T_A = +25^\circ\text{C}$

Surge Current A: 2.00 A, sinewave, $P_w = 8.3$ ms




Electrical Specifications @ +25°C (unless otherwise Specified)

JEDEC TYPE#	VBR @ 100 μA	VRWM	IO	Vf1 IF = 10 mA	Vf2 IF = 50 mA	Trr ¹	IR1 @ 20 Vdc	IR2 @ 75 Vdc	IR3 @ 20 Vdc $T_A = 150^\circ\text{C}$	IR4 @ 75 Vdc $T_A = 150^\circ\text{C}$	Capacitance @ 0 V	Capacitance @ 1.5 V
	Volts	Volts (pk)	mA	Vdc	Vdc	nsec	nA	μA	μA	μA	pF	pF
1N914	100	75	75	0.8	1.2	5	25	0.5	35	75	4.0	2.8
1N4148-1	100	75	200	0.8	1.2	5	35	0.5	35	75	4.0	2.8

1. IF = IR = 10 mA, $R_L = 100$ ohms.

Outline Drawing



LEADED DESIGN DATA

CASE: Hermetically sealed glass case per MIL-S-19500/116, DO – 35

LEAD MATERIAL: Copper clad steel

LEAD FINISH: Tin / Lead

THERMAL RESISTANCE: ($R_{\theta JL}$): 250 °C/W maximum at $L = 0.375$ in

THERMAL IMPEDANCE: ($Z_{\theta JX}$): 70 °C/W maximum

POLARITY: Cathode end is banded.


1N914 & 1N4148-1



Silicon Switching Diode


Rev. V2

Graphs



Typical Forward Current
vs Forward Voltage

NOTE : All temperatures shown on graphs are
junction temperatures



Typical Reverse Current
vs Reverse Voltage

VPT Components All rights reserved.

Information in this document is provided in connection with VPT Components' products. These materials are provided by VPT Components as a service to its customers and may be used for informational purposes only. Except as provided in VPT Components' Terms and Conditions of Sale for such products or in any separate agreement related to this document, VPT Components assumes no liability whatsoever. VPT Components assumes no responsibility for errors or omissions in these materials. VPT Components may make changes to specifications and product descriptions at any time, without notice. VPT Components makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF VPT COMPONENTS' PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. VPT COMPONENTS FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. VPT COMPONENTS SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

VPT Components' products are not intended for use in medical, lifesaving or life sustaining applications. VPT Components' customers using or selling VPT Components' products for use in such applications do so at their own risk and agree to fully indemnify VPT Components for any damages resulting from such improper use or sale.