




FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE NOTE 1



mat'l. code SEE NOTE 3				surface ISO 1302 ✓ ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecn no	dr	date	tolerances unless otherwise specified					INCH/MM scale 1:1 	title VERTICAL SHROUD 3 ROW W/O GUIDE PIN			
A	v12795	RDS	10/24/91	angles	linear	.XX ±.01/.3				sheet 1 of 2 size 50434 A3			
B	V20224	MRC	2/28/92			.XXX ±.005/.13							
C	V23049	SAR	7/24/92			.XXXX ±.0020/.051							
D	V41077	GAH	7/06/94			dr	D. SHEAFFER	8/07/91					
E	V94441	JWS	12/30/99	enr	S. CLARK	10/24/91	type Product Customer Drawing						
F	V05-0967	DAI	10/20/05	chr	S. CLARK	10/24/91							
G	M06-0255	AEA	7/07/06	appd	S. CLARK	10/24/91							
sheet	revision	G	G										
index	sheet	1	2										

form: A3


PDM: Rev:G

STATUS: Released


Printed: May 13, 2011

PRODUCT NUMBER

SEE NOTE 1



SECTION U-U



SECTION X-X

NOTES:

- PRODUCT NUMBERING CODE:
50434-X YYY X LF
 LEAD FREE (OPTIONAL)
 ALWAYS "X"
 NO. OF POSITIONS SEE NOTE 2
 ALWAYS "X"
 BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE.
i.e.: 6, 7, 8, 9,.....79, 80.
- MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC. FLAME RETARDANT PER UL94 V-0. COLOR: BLACK
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.
- LENGTH FORMULAS
 DIM A= .100/2.54 x NO. OF COLUMNS + .75/19.1
 DIM B= .100/2.54 x NO. OF COLUMNS + .450/11.43
 DIM C= .100/2.54 x NO. OF COLUMNS - .100/2.54
- THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE OVEN.

mat'l. code SEE NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ec	no	dr	date	tolerances unless otherwise specified		title
G					angles linear .XX ±.01/.3		VERTICAL SHROUD
					.XXX ±.005/.13		3 ROW W/O GUIDE PIN
					0°±2° .XXXX ±.0020/.051		scale 1:1
			dr	D. SHEAFFER	8/07/91		dwg no
			enr	S. CLARK	10/24/91		sheet 2 of 2
			chr	S. CLARK	10/24/91		size A3
			appd	S. CLARK	10/24/91		type Product Customer Drawing
sheet index	revision sheet						