

HDMI Extender Equalizer, Active Repeater for Video and Audio, 1920x1200, 1080p at 24Hz (HDMI M/F) 1-ft.

MODEL NUMBER: **B123-001**



Description

Tripp Lite's B123-001 HDMI Signal Extender increases the distance a 1080p @ 24Hz (or 1920 x 1200) signal can be transmitted beyond the recommended 16 ft. (5 m.). It supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p @ 24Hz, at a maximum distance of 150 ft. from the source. Use P568-Series HDMI cables in most applications. When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100 ft. are available from Tripp Lite as a custom order) 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable. Simply connect the longer cable between the source and the B123-001, and then connect the built-in cable to the monitor. Software or drivers are not required. HDCP compliant. Compatible with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Extend a 1080p @ 24Hz (or 1920 x 1200) HDMI signal up to 150 ft. from the source
- Use P568-Series HDMI cables in most applications
- When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD. (Lengths over 100 ft. are available from Tripp Lite as a custom order)
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- HDCP compliant
- No software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Extend a 1080p @ 24Hz (or 1920 x 1200) HDMI signal up to 150 ft. from the source
- When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75 ft., use cable made with 24Awg wiring, such as the P568-100-HD
- 24Awg HDMI cable is also needed when extending a 3D signal more than 50 ft.. A 3D signal can be extended up to 125 ft. using 24Awg HDMI cable
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- When an HDTV display is located a long distance from the video source.

Package Includes

- HDMI Active Extender Cable, M/F, 1 ft.

Specifications

General Info



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Group	SPLITTERS, SWITCHES & EXTENDERS
OVERVIEW	
Intended Application	Connecting Devices
Cable Type	CAT5/CAT5E
Display Style	Signal Booster
Model Type	HDMI
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
CONNECTIONS	
Connector A	HDMI (MALE)
Connector B	HDMI (FEMALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.