

CHEMTRONICS®

Technical Data Sheet

TDS # CWik

Chem-Wik® Rosin

PRODUCT DESCRIPTION

Chem-Wik® Rosin is especially designed for today's heat sensitive electronic components. The lighter mass, pure copper braid construction allows for better thermal conductivity, even at low temperatures. Chem-Wik® Rosin responds as much as 50% faster than conventional desoldering braids. This design minimizes overheating and requires less "contact" pressure for greater operator control. All sizes are coated with a Type "R" organic flux system.

- Requires little or no post solder cleaning
- No corrosive residues
- Optimized weave design for faster wicking and heat transfer
- Halide free
- Minimal risk of heat damage to components and circuit boards

TYPICAL APPLICATIONS

Chem-Wik® Rosin desoldering braid safely removes solder from:

- Thru-hole Components
- Surface Mount Device Pads
- BGA Pads
- Micro Circuits
- Terminals
- Lugs and Posts
- Identification Script

TYPICAL PRODUCT DATA AND PHYSICAL PROPERTIES

Chem-Wik® Rosin	
Flux Type:	Grade WW, Type "R"
Clean-up Required:	No
Military Specifications:	MIL-F-14256F
Shelf Life – 2 years from manufacturer date	
RoHS/WEEE Status	

Part #	Size Inches	Size Metric
2-5L	.030"	.76mm
5-5L	.050"	1.27mm
7-5L	.075"	1.91mm
10-5L	.100"	2.54mm

STATIC DISSIPATIVE PACKAGING

Static Dissipative packaging is available on all 5 foot bobbins. The static dissipative bobbins qualify as electrostatic discharge protective per DOD Standard 1686 and DOD Handbook 263. Meets the static delay rate provision of MIL-B-81705C.

- 5) As solder becomes molten, the color of the wick will change from copper to silver.
- 6) Remove wick and iron from solder joint simultaneously once color change has stopped.
- 7) The component lead is now clean and free from solder.
- 8) Clip and discard the used portion of the wick.

Width	Color Code	5 ft. Bobbin	25 ft. Spool	50 ft. Spool	100 ft. Spool	500 ft. Spool
.030"	White	2-5L	2-25L	2-50L	2-100L	2-500L
.050"	Yellow	5-5L	5-25L	5-50L	5-100L	5-500L
.075"	Green	7-5L	7-25L	7-50L	7-100L	7-500L
.100"	Blue	10-5L	10-25L	10-50L	10-100L	10-500L

MIL-F-14256F, Type R
MIL-STD-2000A
MIL-B-81705C
NASA NHB5300.4(3A)
NASA SP-5002
NASA NPC200-4
IPC SF-818
DOD Handbook 263
DOD Standard 1686
BELLCORE TR-NWT-00078

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly.

CHEMTRONICS® does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

ITW CHEMTRONICS
8125 COBB CENTER DRIVE
KENNESAW, GA 30152
1-770-424-4888

REV. D (06/06)

Chemtronics® provides a technical hotline to answer your technical and application related questions. The toll free number is:
1-800-TECH-401.

DISTRIBUTED BY: