


AD6025 SERIES



External Dimensions



Frame: Plastic (UL: 94V-0)
Impeller: Plastic (UL: 94V-0)
Lead wire: UL1007AWG24

Specifications(Nominal)


*Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x25	AD06012DB257100	◎ ※ ●	12	0.03	0.36	2000	0.280 9.980	0.050 1.240	12.4	53.0
	AD06012LB257100	◎ ※ ●	12	0.05	0.60	2500	0.360 12.710	0.080 1.930	15.9	
	AD06012MB257100	◎ ※ ●	12	0.08	0.96	3500	0.490 17.340	0.130 3.330	26.9	
	AD06012HB257100	◎ ※ ●	12	0.12	1.44	4500	0.660 23.340	0.230 5.920	33.8	
	AD06012UB257100	◎ ※ ●	12	0.17	2.04	5000	0.740 25.970	0.280 7.190	37.1	
	AD06012XB257100	◎ ※ ●	12	0.26	3.12	6000	0.890 31.380	0.370 9.300	42.8	
	AD06012VB257100	◎	12	0.33	3.96	6600	0.980 34.700	0.440 11.130	46.8	
	AD06024LB257100	◎ ※ ●	24	0.04	0.96	2500	0.360 12.710	0.080 1.930	15.9	
	AD06024MB257100	◎ ※ ●	24	0.05	1.20	3500	0.490 17.340	0.130 3.330	26.9	
	AD06024HB257100	◎ ※ ●	24	0.08	1.92	4500	0.660 23.340	0.230 5.920	33.8	
	AD06024UB257100	◎ ※ ●	24	0.10	2.40	5000	0.740 25.970	0.280 7.190	37.1	
	AD06024XB257100	◎ ※ ●	24	0.14	3.36	6000	0.890 31.380	0.370 9.300	42.8	
	AD06024VB257100	◎	24	0.20	4.80	6600	0.980 34.700	0.440 11.130	46.8	

Specifications subject to change without notice.

The specification for bearing type is for reference only, for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主, 若需其他產品資訊請聯絡您在ADDA的業務代表, 謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓					✓		✓

*Safety approvals

UL	UL	SP	CE	CE
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0605LB-A72G\(T\)-LF](#)