

TG/LTG-Series




The TG-Series Mini Tippet rocker switches are single or double pole and feature an all nylon double-insulated construction. These switches are designed with snap-in mounting for fast, low cost assembly. The illuminated version (LTG) is available with either a paddle or rocker actuator. These AC rated switches are also suitable for low-voltage DC applications.

- Specifications
- Certifications\*: UL, CSA, VDE
  - Dielectric Strength: 1,000 V (minimum)
  - Insulation Resistance: 100 Megohms (minimum)
  - Base Material: Nylon
  - Actuator Material: Nylon or Polycarbonate
  - Bezel Material: Nylon

\* Due to ongoing technological advances, consult factory for certification specifics.


Dimensional Specifications: in. [mm]



| LTG                                                                                                                                                                                                                                                                 |                                      | G      | O                                            | 50 | 1                    | -      | T | B                           | -                   | B | -                       | R     | /     | 125N         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------|--------|----------------------------------------------|----|----------------------|--------|---|-----------------------------|---------------------|---|-------------------------|-------|-------|--------------|
| SERIES                                                                                                                                                                                                                                                              |                                      | RATING |                                              |    | ACTUATOR STYLE       |        |   | ACTUATOR COLOR <sup>2</sup> |                     |   | BASE COLOR <sup>2</sup> |       |       |              |
| TG                                                                                                                                                                                                                                                                  | DOUBLE POLE<br>NON-LIGHTED           | 40     | 5A 250VAC<br>10A 125VAC<br>1/2HP 125-250VAC  |    | P                    | PADDLE |   | B                           | BLACK               |   | B                       | BLACK |       |              |
| LTG                                                                                                                                                                                                                                                                 | DOUBLE POLE<br>W/INDICATOR<br>LIGHTS |        | 10(4)A 250VAC μ                              |    | T                    | ROCKER |   | W                           | WHITE               |   | W                       | WHITE |       |              |
| CIRCUIT <sup>1</sup>                                                                                                                                                                                                                                                |                                      |        |                                              |    | TERMINATION/FUNCTION |        |   |                             |                     |   | LENS COLOR <sup>3</sup> |       |       |              |
| See Circuit Designation<br>Chart Page 39                                                                                                                                                                                                                            |                                      | 50     | 10A 250VAC<br>15A 125VAC<br>3/4HP 125-250VAC |    |                      |        |   | .250<br>TAB<br>(QC)         | .187<br>TAB<br>(QC) |   |                         | A     | AMBER |              |
|                                                                                                                                                                                                                                                                     |                                      |        |                                              |    |                      |        |   |                             |                     |   |                         | C     | CLEAR |              |
|                                                                                                                                                                                                                                                                     |                                      |        |                                              |    |                      |        |   |                             |                     |   |                         | R     | RED   |              |
|                                                                                                                                                                                                                                                                     |                                      |        |                                              |    |                      |        |   |                             |                     |   |                         |       |       | LAMP VOLTAGE |
|                                                                                                                                                                                                                                                                     |                                      |        |                                              |    |                      |        |   |                             |                     |   |                         |       |       |              |
| CENTER POSITION                                                                                                                                                                                                                                                     |                                      |        |                                              |    |                      |        |   |                             |                     |   |                         |       |       |              |
| C                                                                                                                                                                                                                                                                   | CENTER OFF<br>THREE POSITION         |        |                                              |    |                      |        |   |                             |                     |   |                         |       |       |              |
| O                                                                                                                                                                                                                                                                   | NO CENTER OFF<br>TWO POSITION        |        |                                              |    |                      |        |   |                             |                     |   |                         |       |       |              |
| NOTES:<br>Shading indicates standard configurations.<br>Imprinting is available. Please specify when ordering.<br>Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in |                                      |        |                                              |    |                      |        |   |                             |                     |   |                         |       |       |              |

NOTES:  
Shading indicates standard configurations.  
Imprinting is available. Please specify when ordering.  
Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.  
1 TG available with circuits A, B, C, D, E, F.  
LTG available with circuits G, H, I, J, M, N, P, Q, R, T, U, V, Y, Z.  
3 Custom colors are available. Consult factory.  
4 Specify lens color for LTG-Series only.

## Circuit Designation Chart - refers to TG/LTG, TTG and TLG-Series Switches pages 36-38



● CONTACT TERMINAL  
Will make contact with switching lever

○ ISOLATED TERMINAL  
Does not make contact with switching lever

● CONTACT TERMINAL AND SWITCH LEVER

○ BULB

NOTES:  
For variations to above circuits, consult factory.