

Metal Drilling Tools
Bradrad Step Drills



A range of high speed steel, multi-diameter drilling and deburring tools for use on sheet metals.

488953

Type	Tool	Shank Size (in)	Range	Order Code	Price Each
S	E1	½	¼ - 1 ½in	137-6537	
S	M2	½	6 - 36mm	137-6538	
S	M6	½	7 - 37mm	137-6539	
S	M6	½	8 - 38mm	137-6540	
A	E1	2MT	1 ½ - 2 ½in	137-6541	