

DETAILS

Product Number	CN12932_LENINA-S
Family	Lenina
Type	RefPack
Color	metal
Diameter	74 mm
Height	46,5 mm
Style	round
Optic Material	PC
Holder Material	PC
Fastening	socket, screw
Status	ready
ROHS Comliant	Yes
Date Updated	18/03/2013



OPTICAL PROPERTIES

LED	Viewing Angle	Light Beam	Efficiency	cd/lm	connector
LUXEON K12	16 degrees		89 %	4.800	-
LUXEON K16	18 degrees		87 %	4.000	-

D C B A

4




4

3

3

2

2



NOTE:

Using optional sublens, add 2.1mm to the system height

Dimension 'h2' varies from 4.5mm to 7mm depending on the LED specific base part

This drawing is our property. It can't be reproduced or communicated without our written agreement.



Ledil Oy
Salorankatu 10
FIN-24240 SALO
Finland


DRAWING TITLE					
Datasheet Lenina series					
DRAWN BY	DATE	SIZE	DRAWING NUMBER		REV
ks	23.04.2014	A4	--		1
CHECKED BY	DATE	SCALE	1:1	WEIGHT (g)	SHEET
DESIGNED BY	DATE				1 / 1
p1	08.03.2012				

1


1

D A


Luminaire: LEDiL Oy CN12932_LENINA-S_(Luxeon-K12) Eff.89.4%
Lamps: 1 x Luxeon-K12 (834.916lm@250mA)




Luminaire: LEDiL Oy CN12932_LENINA-S_(Luxeon_K16) Eff.87.3%
Lamps: 1 x Luxeon_K16 (1008.05lm@250mA)



Luminaire: LEDiL Oy CN12932_LENINA-S_(Luxeon-K12) Eff.89.4%
Lamps: 1 x Luxeon-K12 (834.916lm@250mA)



Luminaire: LEDiL Oy CN12932_LENINA-S_(Luxeon_K16) Eff.87.3%
Lamps: 1 x Luxeon_K16 (1008.05lm@250mA)



NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

GENERAL INFORMATION

- Product series especially designed & optimized for series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Reflector is made of aluminium coated PC (120 degrees of Celcius / 248 degrees of Fahrenheit) with protective lacquer (short term 100 degrees of Celcius / 212 degrees of Fahrenheit).