


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT

REVISIONS					LOC	DIST
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			J1	REVISED PER ECO-11-005294	13APR11	HMR



1. WIRE INSULATION DIA. - SEE TABLE

2. BODY FINISH: TIN PLATE (MIL-T-10727)
.000100 MIN THK

	.115 - .170	100	LOOSE PC. BOX	8-320863-1
0	.115 - .170	100	ON TAPE, SW. BOX	2-320863-6
5	.115 - .170	100	ON TAPE, LA. BOX	2-320863-5
083,	.115 - .170	100	LOOSE PIECE	2-320863-3
	.115 - .170	5000	ON TAPE, REEL	2-320863-2
	.115 - .170	1	LOOSE PIECE	320863

WIRE INS DIA		QUANTITY	DESCRIPTION	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .003 ANGLES ±		CONTRACT NO	TE TE Connectivity	
MATERIAL INSULATION: NYLON - BLUE BODY & SLEEVE: COPPER (33-C-576)		DR UTA / RFB 9-30-89		
FINISH BODY: 2		CHK <i>Philly</i> 11-26-13	NAME WIRE TERMINAL P.I.D.G.-FLANGED SPADE WIRE SIZE: 16-14	
		APPD <i>NA</i> 11-26-13		
		DSGN APPD	SIZE B	FSCM NO 00779
		OTHER APPD	DRAWING NO 320863	
			SCALE NTS	SHEET 1 OF 1

CUSTOMER DRAWING