



## **SMT power inductors**

Size 10 x 10 mm

**Series/Type:** **B82464G2**

**Date:** January 2006  
**Pages** -5- (incl. title)



**Size 10x10 mm**

**Rated inductance 0,82 – 330  $\mu$ H**

### **Construction**

- Ferrite core
- Magnetically shielded
- Winding: enamel copper wire
- Winding welded to terminals

### **Features**

- Wide temperature range
- Very high rated current
- Low DC resistance
- Suitable for reflow soldering

### **Applications**

- Filtering of supply voltages
- Coupling, decoupling
- DC/DC converters
- Automotive electronics

### **Terminals**

- Tinned

### **Marking**

Marking on component:

Manufacturer, L value ( $\mu$ H, coded), tolerance (coded)

Minimum marking on reel:

Manufacturer, part number, ordering code,

L value and tolerance


quantity, date of packing

### **Delivery mode**

16-mm blister tape, reel packing, 1250 pcs. per reel


**General technical data**

|                                  |   |
|----------------------------------|---|
| Rated inductance $L_R$           | Measured with HP 4294A ,<br>measuring voltage 100 mV  |
| Rated current $I_R$              | Maximum permissible DC with temperature increase of $\leq 40$ K at ambient temperature of 85 °C |
| Saturation current $I_{Sat,typ}$ | Maximum permissible DC with inductance decrease $\Delta L/L_0 \approx 10\%$                     |
| Climatic category                | In accordance with IEC 60068-1 55/125/56<br>(-55 °C/ +125 °C/ 56 days damp heat test)           |
| Solderability                    | 5s, 235°C, wetting > 90%  |
| DC resistance $R_{max}$          | Measured at 20 °C ambient temperature   |
| Weight                           | Approx. 2g  |

**Dimensional drawing and layout recommendation**



**Characteristics and ordering codes**

| $L_R$<br>$\mu H$ | $f_L$<br>MHz | Tolerance | $I_{sat}$<br>A | $I_R$<br>A | $R_{max}$<br>$\Omega$ | Ordering code   |
|------------------|--------------|-----------|----------------|------------|-----------------------|-----------------|
| 0,82             | 0,1          | 20 %      | 7,50           | 6,20       | 0,0075                | B82464G2821M000 |
| 1,2              | 0,1          | 20 %      | 6,80           | 5,60       | 0,009                 | B82464G2122M000 |
| 2,0              | 0,1          | 20 %      | 5,40           | 4,50       | 0,014                 | B82464G2202M000 |
| 2,7              | 0,1          | 20 %      | 4,25           | 3,85       | 0,019                 | B82464G2272M000 |
| 3,9              | 0,1          | 20 %      | 3,45           | 3,45       | 0,027                 | B82464G2392M000 |
| 4,7              | 0,1          | 20 %      | 3,10           | 3,10       | 0,033                 | B82464G2472M000 |
| 7,5              | 0,1          | 20 %      | 2,65           | 2,60       | 0,047                 | B82464G2752M000 |
| 10               | 0,1          | 20 %      | 2,25           | 2,25       | 0,062                 | B82464G2103M000 |
| 15               | 0,1          | 20 %      | 1,85           | 1,80       | 0,090                 | B82464G2153M000 |
| 22               | 0,1          | 20 %      | 1,52           | 1,50       | 0,130                 | B82464G2223M000 |
| 33               | 0,1          | 20 %      | 1,25           | 1,20       | 0,195                 | B82464G2333M000 |
| 47               | 0,1          | 20 %      | 1,10           | 1,12       | 0,235                 | B82464G2473M000 |
| 68               | 0,1          | 20 %      | 0,88           | 0,91       | 0,370                 | B82464G2683M000 |
| 100              | 0,1          | 20 %      | 0,73           | 0,75       | 0,530                 | B82464G2104M000 |
| 150              | 0,1          | 20 %      | 0,59           | 0,61       | 0,84                  | B82464G2154M000 |
| 220              | 0,1          | 20 %      | 0,49           | 0,50       | 1,20                  | B82464G2224M000 |
| 330              | 0,1          | 20 %      | 0,40           | 0,41       | 1,60                  | B82464G2334M000 |

## Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of passive electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of a passive electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of a passive electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as "hazardous")**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.epcos.com/material](http://www.epcos.com/material)). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available.

6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, CeraDiode, CSSP, PhaseCap, PhaseMod, SIFI, SIKOREL, SilverCap, SIMID, SIOV, SIP5D, SIP5K, TOPcap, UltraCap, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.epcos.com/trademarks](http://www.epcos.com/trademarks).