




1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. MATERIAL: HOUSING AND COVER – POLYPHENYLENE OXIDE.
CABLE CLAMP – POLYESTER MOLDING COMPOUND.
TERMINAL – HIGH STRENGTH COPPER ALLOY PLATED WITH 0.76μm [.000030] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, 0.76μm [.000030] MIN TOTAL ON MATING SURFACE, OVER 1.27μm [.000050] MIN NICKEL PLATING.
HARDWARE – ZINC PLATED STEEL.
DUST COVER – POLYETHYLENE MOLDING COMPOUND.
4. THIS KIT SHIPPED NOT ASSEMBLED.
5. WIRE SIZE: 24 & 26 AWG SOLID & 24 AWG STRAND COPPER CONDUCTORS. MAXIMUM INSULATION DIAMETER OF 1.15[.045] IS ACCEPTABLE FOR MOST APPLICATIONS.
6. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF AMP INCORPORATED.
7. OBSOLETE

BULK PACKED	$\phi 7.62-8.26$ [$\phi .300-.325$]	YES	BLACK	 6-229913-7
	$\phi 8.89-10.80$ [$\phi .350-.425$]	YES	GRAY	 6-229913-4
		YES	BLACK	 6-229913-3
		NO	BLACK	 6-229913-1
POLY BAGGED	$\phi 10.80-12.70$ [$\phi .425-.500$]	YES	BLACK	 3-229913-1
		NO	BLACK	 2-229913-1
	$\phi 8.89-10.80$ [$\phi .350-.425$]	YES	GRAY	 1-229913-4
		YES	BLACK	 1-229913-1
		NO	GRAY	 229913-4
		NO	BLACK	229913-1
PACKAGING	CABLE RANGE	DUST COVER	COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

2

3

APVD

30 AUG 93

15 NOV 93

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

RECEPTACLE KIT, 50 POSITION, B-SLOT, SCREW LOCK, TAPERED COVER, CHAMP-LOK®

A200779

C=229913

SCALE 2:1

SHEET 1 of 1

REV AL2