



LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REV PER ECO 13-016525	12-10-13	CT	JW



1 STAMP AMP 8 AL90CU APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 150° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.5mm ² [13,100-20,800] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

BODY: COPPER PER ASTM B-152 TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727 INSERT: COPPER PER ASTM B-152 TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	184076-1
MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 18JUL94	 TE Connectivity								
		CHK AJ KAUFMAN 20JUL94									
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL, RING TONGUE, COPALUM TM							
	0 PLC ± -		APVD —					NAME			
	1 PLC ± -		PRODUCT SPEC —								
	2 PLC ± -		—								
	3 PLC ± -		APPLICATION SPEC —								
	4 PLC ± -		—	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO			
	ANGLES ± -		—	A2	00779	C=184076					
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —		A2 00779 C=184076		—			
CUSTOMER DRAWING						SCALE	4:1	SHEET	1 of 1	REV	A