


290EEX




NOTE: ALL LEADS 9" OUT MIN., STRIPPED .5"

DIMENSIONS:

A	3.438" ± 0.063
B	4.063" ± 0.125
C	4.125" ± 0.063
D	1.844" ± 0.063
E	2.750" ± 0.063
F	3.438" ± 0.063

PRIMARY SECONDARY



ELECTRICAL DATA:

Turns ratio:	1 : 2.87 (RED - RED)
Exciting Current	@ 240V, 50Hz, BLK - WHT = 228mA Max.
DCR	@ 20C, BLK - WHT = 5.634 Ω $\pm 20\%$
	@ 20C, RED - RED = 37.821 Ω $\pm 20\%$
	@ 20C, GRN - GRN = 0.102 Ω $\pm 20\%$
Pri. Voltage	240V 50Hz
Sec. Voltage (RMS)	660VCT @ 276mA C/W 53V TAP , 6.5V @ 3.15A
No Load Voltage	688.70VCT/ 6.78V



PHONE (519) 886-6181
FAX # (519) 886-9540

TITLE

POWER TRANSFORMER

			DR BY IOAN POP
1	08/11/09	PRELIMINARY.	DATE 05/12/09
NO	DATE	REVISION	DIM IN(X)MM()

290EEX