

# R\_10005

## Driving the LPC2900 with Murata resonators

Rev. 1.1 — 21 November 2013

Report

### Document information

Info	Content
<b>Keywords</b>	LPC2939FBD208; LPC2930FBD208, LPC2929FBD144; LPC2927FBD144, LPC2926FBD144, LPC2925FBD100; LPC2923FBD100; LPC2921FBD100; LPC2919FBD144/01, LPC2917FBD144/01
<b>Abstract</b>	Characterization results of Murata resonators for LPC2900



## Revision history

Rev	Date	Description
1.1	20131121	Corrected link, added LPC2926FBD144
1	20100421	Initial release

## Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

## 1. Introduction

The LPC2900 series microcontrollers are based on the ARM968E-S core operating at frequencies up to 125 MHz. On-chip peripherals include USB Host/Device/OTG, Motor Control PWM/QEI,  $2 \times 3$  V and  $1 \times 5$  V ADC, EEPROM, I<sup>2</sup>C, Q-SPI and external memory interfaces. The microcontrollers are designed for use in general-purpose and specialty embedded applications such as high speed document printers/scanners, industrial control and motor control.

The LPC2900 devices have an integrated IRC oscillator. On the LPC2900, the oscillator range is 0.4 MHz to 0.6 MHz over temperature and voltage. Many applications can utilize the IRC as the clock source; others may use a suitable crystal for more accuracy, particularly for USB applications. The LPC2900 device can also use a resonator as a clock source.

## 2. Characterization results

Based on characterization results, the following tables detail the most suitable devices available from Murata. Note that devices from other manufacturers can also be used.

**Table 1. Recommended devices (for consumer) [1]**

$V_{DD(CORE)}$ : 1.71 V to 1.89 V; -40 to +85 °C

Device	Freq. [MHz]	Type	Part number	Supply voltage range	Temp. range
LPC2927	12	SMD	CSTCE12M0G55-R0	1.71 to 1.89	-40 to +85 °C
LPC2929	16	SMD	CSTCE16M0V53-R0		
	20	SMD	CSTCE20M0V53-R0		

- [1] These resonators have load capacitors included so external load capacitors are not necessary.  
 Suffix indicates packaging style.  
 SMD type[ -R0:Plastic tape package( $\varnothing$  = 180mm), -B0:Bulk]

For USB applications, the following resonators are recommended.

**Table 2. Recommended devices (for consumer) [1]**

$V_{DD(CORE)}$ : 1.71 V to 1.89 V; -40 to +85 °C

Device	Freq. [MHz]	Type	Part number	Supply voltage range	Temp. range
LPC2927	12	SMD	CSTCE12M0GH5L**-R0	1.71 to 1.89	-40 to +85 °C
LPC2929	16	SMD	CSTCE16M0VH3L**-R0		

- [1] These resonators have load capacitors included so external load capacitors are not necessary.  
 "\*\*\*\*" means temporary part number; formal part number will be applied after the frequency measurement process on actual board by Murata.  
 Suffix indicates packaging style.  
 SMD type[ -R0:Plastic tape package( $\varnothing$  = 180mm), -B0:Bulk]

For more information and a detailed report please go to the Murata website <http://search.murata.co.jp/Ceramy/ICsearchAction.do?sLang=en> and search for 'LPC'.

## 3. Legal information

### 3.1 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

### 3.2 Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

### 3.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

4. Contents

1	Introduction .....	3
2	Characterization results .....	3
3	Legal information.....	4
3.1	Definitions.....	4
3.2	Disclaimers.....	4
3.3	Trademarks.....	4
4	Contents .....	5

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.