

FR2A THRU FR2K

SURFACE MOUNT ULTRAFAST RECTIFIER

VOLTAGE - 50 to 800 Volts CURRENT - 2.0 Amperes

FEATURES

- For surface mounted applications
- Low profile package
- Built-in strain relief
- Easy pick and place
- Fast recovery times for high efficiency
- Plastic package has Underwriters Laboratory Flammability Classification 94V-O
- Glass passivated junction
- High temperature soldering:
260 °C/10 seconds at terminals

MECHANICAL DATA

Case: JEDEC DO-214AA molded plastic


Terminals: Solder plated, solderable per
MIL-STD-750, Method 2026

Polarity: Indicated by cathode band

Standard packaging: 12mm tape (EIA-481)

Weight: 0.003 ounce, 0.093 gram

SMB/DO-214AA



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 °C ambient temperature unless otherwise specified.

Resistive or inductive load.

For capacitive load, derate current by 20%.

	SYMBOLS	FR2A	FR2B	FR2D	FR2G	FR2J	FR2K	UNITS
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	Volts
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	Volts
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	Volts
Maximum Average Forward Rectified Current, at $T_J=90^{\circ}\text{C}$	I_{AV}	2.0						Amps
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load(JEDEC method)	I_{FSM}	50.0						Amps
Maximum Instantaneous Forward Voltage at 2.0A	V_F	1.30						Volts
Maximum DC Reverse Current $T_A=25^{\circ}\text{C}$ At Rated DC Blocking Voltage $T_A=125^{\circ}\text{C}$	I_R	5.0 200						µA
Maximum Reverse Recovery Time (Note 1) $T_J=25^{\circ}\text{C}$	T_{RR}	150				250	500	nS
Typical Junction capacitance (Note 2)	C_J	40						pF
Maximum Thermal Resistance (Note 3)	$R_{\theta KJL}$	20.0						°C/W
Operating and Storage Temperature Range	T_J, T_{STG}	-50 to +150						°C

NOTES:

1. Reverse Recovery Test Conditions: $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{rr}=0.25\text{A}$
2. Measured at 1 MHz and Applied reverse voltage of 4.0 volts

RATING AND CHARACTERISTIC CURVES

FR2A THRU FR2K




Fig. 1-FORWARD CURRENT DERATING CURVE




Fig. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




Fig. 3-FORWARD CHARACTERISTICS




Fig. 4-TYPICAL REVERSE CHARACTERISTICS




Fig. 5-TYPICAL JUNCTION CHARACTERISTICS




Fig. 6-REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM

