




14.4	15.6	16.42	15.0	16.95	503566-5100	51
12.6	13.8	14.62	13.2	15.15	503566-4500	45
12.0	13.2	14.02	12.6	14.55	503566-4300	43
11.4	12.6	13.42	12.0	13.95	503566-4100	41
10.8	12.0	12.82	11.4	13.35	503566-3900	39
10.2	11.4	12.22	10.8	12.75	503566-3700	37
9.6	10.8	11.62	10.2	12.15	503566-3500	35
9.0	10.2	11.02	9.6	11.55	503566-3300	33
8.4	9.6	10.42	9.0	10.95	503566-3100	31
7.2	8.4	9.22	7.8	9.75	503566-2700	27
6.6	7.8	8.62	7.2	9.15	503566-2500	25
6.0	7.2	8.02	6.6	8.55	503566-2300	23
5.4	6.6	7.42	6.0	7.95	503566-2100	21
4.8	6.0	6.82	5.4	7.35	503566-1900	19
4.2	5.4	6.22	4.8	6.75	503566-1700	17
3.6	4.8	5.62	4.2	6.15	503566-1500	15
3.0	4.2	5.02	3.6	5.55	503566-1300	13
2.4	3.6	4.42	3.0	4.95	503566-1100	11
1.8	3.0	3.82	2.4	4.35	503566-0900	9
E	D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER NO.	極数 CIRCUITS
CONNECTOR SERIES NO. 503566-***8						

10

9

8

7

6

5

4

3

2

1

F



E

D


C

B

A




DETAIL "C"



注記 NOTES

- 製品詳細寸法については図面 SD-503566-001 を参照下さい。
RE DETAILED DIMENSION, SEE SD-503566-001
- 梱包数量：3000個/リール
NUMBER OF CONNECTORS：3000 PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH



- 材料 MATERIAL
キャリアテープ (CARRIER TAPE)：ポリスチレン (POLYSTYRENE)
トップテープ (TOP TAPE)：PET, PE, PEF
リール (REEL)：ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- トップテープの剥離強度については、IEC60286-3に準拠
TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3.

REVISED EC NO: J2011-1637 DRWN:HMIYAMOTO CHKD:HIJIMA APPR:KMORIKAWA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		10 UNDER	±0.2	DRAWN BY HIJIMA	DATE 2010/05/20	TITLE 0.3 FPC CONN. E/O TAPING PACKAGE (503566-**08 SERIES)			
		10 OVER 30 UNDER	±0.25	CHECKED BY NMATSUURA	DATE 2010/05/20				
		30 OVER	±0.3	APPROVED BY KMORIKAWA	DATE 2010/06/11				MOLEX INCORPORATED
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-503566-002		1 OF 2		
	REV	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

9

8

7

6

5

4

3

2

F

E

D

C

B

A

F




E

D

C

B

A



DETAIL "T"

SECTION X-X

SECTION Y-Y

32±0.3	28.4	14.2	33.4	17.25	503566-5100	51
24±0.3	≡	11.5	25.4	15.45	503566-4500	45
				14.85	503566-4300	43
				14.25	503566-4100	41
				13.65	503566-3900	39
				13.05	503566-3700	37
				12.45	503566-3500	35
				11.85	503566-3300	33
				11.25	503566-3100	31
				10.05	503566-2700	27
				9.45	503566-2500	25
16±0.3	≡	7.5	17.4	8.85	503566-2300	23
				8.25	503566-2100	21
				7.65	503566-1900	19
				7.05	503566-1700	17
				6.45	503566-1500	15
				5.85	503566-1300	13
				5.25	503566-1100	11
				4.65	503566-0900	9
E キャリアテープ幅 EMBOSSED TAPE WIDTH	D	C	B	A	EMBOSSED TAPE PACKAGE オーダー番号 ORDER NO.	極 数 CIRCUITS

SEE SHEET 1 OF 2
EC NO: J2011-1637
DRAWN: H. IYAMOTO 2011/05/31
CHECKED: H. IYAMA 2011/05/31
APPR: K. MORIKAWA 2011/06/02

GENERAL TOLERANCES
(UNLESS SPECIFIED)

10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGULAR	±3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE
MM ONLY

DRAWN BY H. IYAMA	DATE 2010/05/20
CHECKED BY NMATSUURA	DATE 2010/05/20
APPROVED BY K. MORIKAWA	DATE 2010/06/11
MATERIAL NO.	

SCALE

DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
0.3 FPC CONN. E/O
TAPING PACKAGE
(503566-**08 SERIES)

MOLEX INCORPORATED

SD-503566-002

DOCUMENT NO.

SHEET NO.
2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION