







Copyright FCI.

PRODUCT NUMBER	Teril Type	DIM "A"	PCB THICKNESS ±0.20	LOADING CONFIGURATION
10084576-X02LF	PRESS-FIT	2.90	1.6	FULLY LOADED
10084576-X12LF	PRESS-FIT	3.53	2.4	FULLY LOADED

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YYLF	TELCORDIA CO



- NOTES:
1. BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 2. TERMINAL MATERIAL: PHOSPHOR BRONZE.
 3. INDICATED HOLES ARE UNPLATED.
 4. PRODUCT MARKING: PART NUMBER & BATCH ID.
 5. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 6. ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 240 DEGREE FOR
60 SECONDS IN A CONVECTION, INFRARED OR VAPOR PHASE REFLOW OVEN.
 7. TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING
THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
 8. PRESS FIT ACCORDING PRODUCT SPECIFICATION GS-12-002




TABLE 1	
PLATED THRU HOLE REQUIREMENT	
HOLE DIAMETER AFTER PLATING	0.65 - 0.80
DRILLED HOLE	0.81 - 0.86 (0.85 DRILL)
COPPER PLATING	0.025 - 0.05
Sn PLATING	0.005 - 0.015

rev	ecn no	dr	date
A	0G08-007	Cenh	26/11/07
B	0G09-008	Cenh	2/23/09
C	0G09-012	Cenh	03/18/09
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ☒		tolerance std		projection 		 MM			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	Heaven Cen	26/11/07	ANGULAR		LINEAR		0.X		± 0.3		size A4	Scale 1:1
Eng	Collins Lu	26/11/07					0.XX		± 0.13			
Chr	Gary Hsieh	26/11/07	0° ±2°				0.XXX		± 0.051		ECN	
Appr	Joseph Hsieh	26/11/07	Product family						Spec ref			
		title B SERIES SIGNAL ASSEM SPECIAL HSG					dwg no 10084576		Rev. C			
		R/A 5R 1M PF										
		catalog no					Customer		sheet 1 of 1			