


Standard Power Integrated Module with PFC and Shunts

flow PIM® 1 + P; 600V, 5A

V23990-P301-_10-PM



Maximum Ratings / Höchstzulässige Werte

at T_J=25°C, unless otherwise specified

Parameter	Condition		Symbol	Value	Unit
Input Rectifier Bridge Gleichrichter					
Repetitive peak reverse voltage Periodische Rückw. Spitzensperrspannung			VRRM	1200	V
Forward average current Dauergrenzstrom	sine d=0.5	TC=80°C	IFAV	25	A
Surge forward current Stoßstrom Grenzwert	tp=10ms	TJ=25°C	IFSM	200	A
I2t-value Grenzlastintegral	tp=10ms	TJ=25°C	I2t	200	A2s
Power dissipation per Diode Verlustleistung pro Diode	Tj=150°C	TC=80°C	Ptot	15	W
Transistor Inverter Transistor Wechselrichter					
Collector-emitter break down voltage Kollektor-Emitter-Sperrspannung			VCE	600	V
DC collector current Kollektor-Dauergleichstrom	Tj=150°C	TC=80°C	IC	7	A
Repetitive peak collector current Periodischer Kollektorspitzenstrom	Tj=150°C tp=1ms	TC=80°C	Icpuls	14	A
Power dissipation per IGBT Verlustleistung pro IGBT	Tj=150°C	TC=80°C	Ptot	22	W
Gate-emitter peak voltage Gate-Emitter-Spitzenspannung			VGE	±20	V
Diode Inverter Diode Wechselrichter					
DC forward current Dauergleichstrom	Tj=150°C	TC=80°C	IF	10	A
Repetitive peak forward current Periodischer Spitzenstrom	Tj=150°C tp=1ms	TC=80°C	IFRM	20	A
Power dissipation per Diode Verlustleistung pro Diode	Tj=150°C	TC=80°C	Ptot	17	W
PFC Transistor PFC Transistor					
Drain to source breakdown voltage Drai-Source Sperrspannung			Vbr	500	V
DC drain current Drain-Dauergleichstrom	Tj=150°C	TC=25°C TC=80°C	Id	8 6	A
Pulsed drain current Periodischer Drainstrom	Tj=150°C tp=1ms	TC=25°C TC=80°C	Idpuls	16 12	A
Power dissipation Verlustleistung	Tj=150°C	TC=25°C TC=80°C	Ptot	77 43	W
Gate-source peak voltage Gate-Source-Spitzenspannung			Vgs	±20	V

PFC Diode					
PFC Diode					
DC forward current Dauergleichstrom	Tj=150°C	TC=80°C	IF	8	A
Repetitive peak forward current Periodischer Spitzenstrom	Tj=150°C tp=1ms	TC=80°C	IFRM	20	A
Power dissipation per Diode Verlustleistung pro Diode	Tj=150°C	TC=80°C	Ptot	16	W
Thermal properties					
Thermische Eigenschaften					
max. Chip temperature max. Chiptemperatur			Tjmax	150	°C
Storage temperature Lagertemperatur			Tstg	-40...+125	°C
Operation temperature Betriebstemperatur			Top	-40...+125	°C
Thermal resistance, chip to case (Tcase is measured under the chip) Wärmewiderstand Chip-Bodenplatte per chip (Tcase ist unter den chip gemessen)	Diode Rectifier		RthJC	1,50	K/W
	Transistor Inverter		RthJC	3,10	K/W
	Diode Inverter		RthJC	3,20	K/W
	Transistor PFC		RthJC	1,60	K/W
	Diode PFC		RthJC	3,10	K/W
Insulation properties					
Modulisation					
Insulation test voltage Isolationsspannung	t=1min		Vis	4000	Vdc
Creepage distance Kriechstrecke				12,7	mm
Clearance Luftstrecke				12,7	mm

Standard Power Integrated Module with PFC and Shunts

flow PIM® 1 + P; 600V, 5A

V23990-P301-_10-PM

→ B: with PFC/ mit PFC
→ D: w/o PFC/ ohne PFC

Characteristic values / Charakteristische Werte
at T_J=25°C, unless otherwise specified

Parameter	Symbol	Condition:	T	RG	VGE	VCE	IF	IC	Value			Unit
FET Parameter			(°C)	RG	VGS	VDS		Id				
				(W)	(V)	(V)	(A)	(A)	min.	typ.	max.	
Input Rectifier Bridge												
Gleichrichter												
Forward voltage	VF		TJ=25°C				5			0,92		V
Durchlaßspannung												
Threshold voltage (for power loss calc. only)	Vto		TJ=25°C				5			0,84		V
Schleusenspannung												
Slope resistance (for power loss calc. only)	rt		TJ=25°C				5			16		mΩ
Ersatzwiderstand												
Reverse current	Ir	VR=VRmax	TJ=25°C								0,01	mA
Sperrstrom												
Transistor Inverter, inductive load												
Transistor Wechselrichter												
Gate emitter threshold voltage	VGE(th)	Vge=Vce	TJ=25°C					200μ	3	4	5	V
Gate-Schwellenspannung												
Collector-emitter saturation voltage	VCE(sat)		TC=25°C		15			4,0	1,6	2	2,5	V
Kollektor-Emitter Sättigungsspannung												
Collector-emitter cut-off current incl. FRED	ICES		TC=25°C		0	600					25	μA
Kollektor-Emitter Reststrom inkl. FRED												
Gate-emitter leakage current	IGES		TJ=25°C		30	0					120	nA
Gate-Emitter Reststrom												
Turn-on delay time	td(on)	Rg(on)=Rg(off)	TJ=25°C	62	15	400		5,0		10	24	ns
Einschaltverzögerungszeit			TJ=125°C							9	22	
Rise time	tr	Rg(on)=Rg(off)	TJ=25°C	62	15	400		5,0		7	20	ns
Anstiegszeit			TJ=125°C							8	18	
Turn-off delay time	td(off)	Rg(on)=Rg(off)	TJ=25°C	62	15	400		5,0		182	372	ns
Abschaltverzögerungszeit			TJ=125°C							193	394	
Fall time	tf	Rg(on)=Rg(off)	TJ=25°C	62	15	400		5,0		11	56	ns
Fallzeit			TJ=125°C							12	66	
Turn-on energy loss per pulse	Eon	Rg(on)=Rg(off)	TJ=125°C		15	400		5,0		181		mWs
Einschaltverlustenergie pro Puls												
Turn-off energy loss per pulse	Eoff	Rg(on)=Rg(off)	TJ=125°C		25	400		5,0		143		mWs
Abschaltverlustenergie pro Puls												
SC withstand time	tSC	@ 10*Id(max)	TJ≤125°C								10	μs
Kurzschlußverhalten												
Input capacitance	Cies	f=1MHz	TJ=25°C		0	25				0,26		nF
Eingangskapazität												
Reverse transfer capacitance	Crss	VCE=25V VGE=0V	f=1MHz									nF
Diode Inverter												
Diode Wechselrichter												
Diode forward voltage	VF		TJ=25°C				5			1,89		V
Durchlaßspannung												
Peak reverse recovery current	IRM	dIF/dt=-200A/ms	TJ=125°C			400	5			5		A
Rückstromspitze												
Reverse recovery time	trr	dIF/dt=-200A/ms	TJ=125°C			400	5			55		ns
Sperreverzögerungszeit												
Reverse recovered charge	Qrr		TJ=125°C			400	5			0,17		μC
Sperrverzögerungsladung		dif/dt=200 A/ms										

Transistor PFC													
Transistor PFC													
Static drain to source ON resistance Statische drain-source Widerstand	Rds(on)	TJ=25°C			10		4,6		0,54	0,6	Ω		
Gate threshold voltage Gate Spitzenspannung	V(GS)th	VDS=VGS VDS=VGS, ID=250 A	TJ=25°C					3,5	4,5	5,5	V		
Drain to Source breakdown voltage Drain source Leckstrom	V(BR)DSS	ID=350μA	TJ=25°C		0		0,25m	600			V		
Drain to Source Leakage Current Drain source Leckstrom	Igss	TJ=25°C		20	0					100	nA		
Turn On Delay Time Einschaltverzögerung	td(ON)	VDD=350V	TJ=25°C	12	10		7,3		45		ns		
Rise Time Anstiegszeit	tr	VDD=350V	TJ=25°C	12			7,3		30		ns		
Turn off delay time Abschaltverzögerung	td(OFF)	VDD=350V	TJ=25°C	12			7,3		70		ns		
Fall time Abstiegszeit	tf	VDD=350V	TJ=25°C	12			7,3		30		ns		
Total gate charge Gate Ladung	Qg	VDD=350V	TJ=25°C		10		7,3		27		nC		
Gate to source charge Gate source Ladung	Qgs	TJ=25°C		10			7,3		6,7		nC		
Input capacitance Eingangskapazität	Ciss	f=1MHz	TJ=25°C		0	25			970		pF		
Output capacitance Ausgangskapazität	Coss	f=1MHz	TJ=25°C		0	25			510		pF		
Diode PFC													
Diode PFC													
Forward voltage Durchlaßspannung	VF	TJ=25°C TJ=25°C TJ=125°C				8 16 8			1,4 1,7 1,4	1,7 2,1 1,7	V V V		
Breakdown voltage Sperrspannung	Vr	Ir=100μA								600	V		
Reverse leakage current Leckstrom	Irm	Vr=Vr rated Vr=0.8*Vr rated	TJ=25°C TJ=125°C						0,3 100	5 500	μA		
Reverse recovery time Sperrverzögerungszeit	trr	Vr=200V dif/dt=200A/μs	TJ=25°C TJ=125°C			8			37 55	55 90	ns		
Peak recovery current Rückstromspitze	Irrm	Vr=200V dif/dt=200A/μs	TJ=25°C TJ=125°C			8			3,5 4,5	5 8	A		
Reverse recovery charge Sperrverzögerungsladung	Qrr	Vr=200V dif/dt=200A/μs	TJ=25°C TJ=125°C			8			65 124	138 360	nC		
Peak rate of fall of recovery current Sitzensteilheit von Rückstrom	di(rec)max/ dt	Vr=200V dif/dt=200A/μs	TJ=25°C TJ=125°C			8			240 210		A/μs		
NTC-Thermistor													
NTC-Widerstand													
Rated resistance Nennwiderstand	R25	Tc=25°C							22		kΩ		
Rated resistance Nennwiderstand	R100	Tol. ±5%	Tc=100°C						1486		%/K		
Power dissipation Verlustleistung	P	Tc=25°C								210	mW		
B-value B-Wert	B(25/100)	Tol. ±3%							4000		K		
Shunts													
Shuntwiderstände													
R1 value R1 Wert	R	Tol. 1%	Tc=25°C						68		mΩ		
Power dissipation Verlustleistung	P	Tc=25°C								3	W		
R2 value R2 Wert	R	Tol. 1%	Tc=25°C						100		mΩ		
Power dissipation Verlustleistung	P	Tc=25°C								3	W		
R3 value R3 Wert	R	Tol. 1%	Tc=25°C						200		mΩ		
Power dissipation Verlustleistung	P	Tc=25°C								3	W		


Output inverter

Typ. output characteristics

Output inverter IGBT

$$I_C = f(V_{CE})$$

parameter: $t_p = 250 \mu s$, $T_j = 25^\circ C$




Typ. output characteristics

Output inverter IGBT

$$I_C = f(V_{CE})$$

parameter: $t_p = 250 \mu s$, $T_j = 125^\circ C$




Typ. transfer characteristics

Output inverter IGBT

$$I_C = f(V_{GE})$$

parameter: $t_p = 250 \mu s$, $V_{CE} = 10 V$




Typ. diode characteristics

Output inverter FRED

$$I_F = f(V_F)$$

parameter: $t_p = 250 \mu s$




Output inverter

Typ. Switching losses

Output inverter IGBT

$E = f(I_C)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 62\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching losses

Output inverter IGBT

$E = f(R_G)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 5\text{ A}$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(I_C)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 62\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(R_G)$, inductive load, $T_j = 25^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 5\text{ A}$, $R_{Gon} = R_{Goff}$




Output inverter

Typ. Switching losses

Output inverter IGBT

$E = f(I_C)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 62\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching losses

Output inverter IGBT

$E = f(R_G)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 5\text{ A}$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(I_C)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 62\ \Omega$, $R_{Gon} = R_{Goff}$




Typ. Switching time

Output inverter IGBT

$t = f(R_G)$, inductive load, $T_j = 125^\circ\text{C}$

par.: $V_{CE} = 400\text{ V}$, $V_{GE} = 15\text{ V}$, $I_C = 5\text{ A}$, $R_{Gon} = R_{Goff}$




FRED diode

Typ. Reverse recovery time

Output inverter FRED diode

$$t_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$




Typ. Reverse recovery current

Output inverter FRED diode

$$I_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$




Typ. Reverse stored charge

Output inverter FRED diode

$$Q_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$




Typ. di_{rec} / dt





Output inverter FRED diode

$$I_{rr} = f(di_f / dt)$$

par.: $V_R = 400 \text{ V}$, $T_J = 125^\circ \text{C}$



Output inverter




Output inverter

Power dissipation

Output inverter FRED

$$P_{tot} = f(T_c)$$

parameter: $T_j = 125^\circ\text{C}$




Forward current

Output inverter FRED

$$I_F = f(T_c)$$

parameter: $T_j = 125^\circ\text{C}$




Short circuit safe operating area

Output inverter IGBT

$$I_{CSC} = f(V_{CE}), T_j = 125^\circ\text{C}$$

parameter: $V_{GE} \leq 15\text{ V}$, $t_{SC} \leq 10\text{ }\mu\text{s}$, $L < 50\text{ nH}$




PFC

Typ. output characteristics

PFC FET

$$I_C = f(V_{CE})$$

parameter: $t_p = 250 \mu s$, $T_j = 25^\circ C$




Typ. output characteristics

PFC FET

$$I_C = f(V_{CE})$$

parameter: $t_p = 250 \mu s$, $T_j = 125^\circ C$




Typ. transfer characteristics

PFC FET

$$I_C = f(V_{GE})$$

parameter: $t_p = 250 \mu s$, $V_{CE} = 10 V$




Typ. diode characteristics





PFC FRED

$$I_F = f(V_F)$$



parameter: $t_p = 250 \mu s$




PFC



PFC



Thermistor




Input rectifier bridge

Typ. diode characteristics

Input rectifier Bridge

$$I_F = f(V_F)$$

parameter: $t_p = 250 \mu s$




Transient thermal impedance

Input Rectifier Bridge

$$Z_{thJC} = f(t_p)$$

Parameter: $D = t_p / T$




Power dissipation

Rectifier

$$P_{tot} = f(T_C)$$

parameter: $T_j = 125 \text{ °C}$



Forward current

Rectifier

$$I_F = f(T_C)$$

parameter: $T_j = 125 \text{ °C}$

