





NOTES:

1. MATERIAL: NYLON, UL 94V-2, WHITE
2. FINISH: N/A
3. PRODUCT SPECIFICATION: PS-172160-0001
4. PACKAGING SPECIFICATION: PK-172159-0001
5. COSMETIC SPEC: PS-45499-002 CLASS B
6. HOUSING ACCEPTS TERMINAL: 172160
7. THIS PART WITHOUT THE HOOK SEE SD-172159-0000
8. DIMENSION TO BE 2.54-2.79/.100-.110 TO POLARIZE HOUSING AND PCB.


TERMINAL 172160
SHOWN FOR
REF ONLY



SECTION Z-Z



CKTS	MATERIAL NO	HOOK	POL RIB	DIM A	DIM B	DIM C	DIM E
02	172159-0502	1-2	N/A	$\frac{15.70}{.618}$	$\frac{20.24}{.797}$	$\frac{16.05}{.632}$	$\frac{7.92}{.312}$
03	172159-0503	1-2	N/A	$\frac{19.66}{.774}$	$\frac{22.30}{.878}$	$\frac{20.02}{.788}$	$\frac{11.89}{.468}$
04	172159-0604	3-4	2-3	$\frac{23.42}{.922}$	$\frac{26.26}{1.034}$	$\frac{23.98}{.944}$	$\frac{15.85}{.624}$
05	172159-0605	3-4	2-3	$\frac{27.38}{1.078}$	$\frac{30.23}{1.190}$	$\frac{27.94}{1.100}$	$\frac{19.81}{.780}$
06	172159-0606	3-4	2-3	$\frac{31.29}{1.232}$	$\frac{34.19}{1.346}$	$\frac{31.90}{1.256}$	$\frac{23.77}{.936}$
07	172159-0607	4-5	3-4	$\frac{35.26}{1.388}$	$\frac{38.15}{1.502}$	$\frac{35.86}{1.412}$	$\frac{27.74}{1.092}$
08	172159-0608	4-5	3-4, 6-7	$\frac{39.22}{1.544}$	$\frac{42.11}{1.658}$	$\frac{39.83}{1.568}$	$\frac{31.70}{1.248}$
09	172159-0609	4-5	3-4, 5-6	$\frac{43.18}{1.700}$	$\frac{46.08}{1.814}$	$\frac{43.79}{1.724}$	$\frac{35.66}{1.404}$
10	172159-0610	4-5	3-4, 6-7	$\frac{47.09}{1.854}$	$\frac{50.04}{1.970}$	$\frac{47.75}{1.880}$	$\frac{39.62}{1.560}$
11	172159-0611	4-5	3-4, 7-8	$\frac{51.05}{2.010}$	$\frac{54.00}{2.126}$	$\frac{51.71}{2.036}$	$\frac{43.59}{1.716}$
12	172159-0612	5-6	3-4, 8-9	$\frac{54.97}{2.164}$	$\frac{57.96}{2.282}$	$\frac{55.68}{2.192}$	$\frac{47.55}{1.872}$



REV	DESCRIPTION
B7	DIMENSION E REF. EC NO: UCP2015-4221 DRW:MKIPPER 2015/02/11 CHKD:JBELL 2015/02/11 APPR:FSMITH 2015/04/16

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	$\pm .005$	$\pm .0005$
3 PLACES	$\pm .005$	$\pm .0010$
2 PLACES	± 0.25	$\pm .015$
1 PLACE	± 0.38	$\pm .015$
0 PLACE	$\pm .005$	$\pm .0005$

ANGULAR $\pm 1/2^\circ$

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE MM/IN

DRAWN BY	DATE
KSAMIEC	2014/05/05
CHECKED BY	DATE

APPROVED BY	DATE
JCOMERC I	2014/05/19

MATERIAL NO.
SEE CHART

SIZE
B

SCALE 3:1

DESIGN UNITS INCH

THIRD ANGLE PROJECTION

EDGEMATE CONNECTOR
3.96/.156 CENTER
WITH HOOK



moLEX

DOCUMENT NO.

SD-172159-0002

SHEET NO.

1 OF 2



SEE SHEET 1
EC NO: UCP2015-4221
DRAWN: KIPPER 2015/02/11
CHKD: JELL 2015/02/11
APPR: FSMITH 2015/04/16
REV DESCRIPTION

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES	± --- ± ---
3 PLACES	± --- ± .010
2 PLACES	± 0.25 ± .015
1 PLACE	± 0.38 ± ---
0 PLACE	± --- ± ---
ANGULAR ± 1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
KSAMIEC	2014/05/05
CHECKED BY	DATE
APPROVED BY	DATE
JCOMERC I	2014/05/19
MATERIAL NO.	
SEE CHART	
SIZE B	

SCALE 1.5:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
TITLE EDGEMATE CONNECTOR 3.96/.156 CENTER WITH HOOK		
DOCUMENT NO. SD-172159-0002		
SHEET NO. 2 OF 2		