


PC911223KA Product Details

[Share](#) [Print](#) [Email](#)



PC911223KA

(1625940-9)

TE Internal Number: 1625940-9

[Active](#)

Variable Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K Ω
- Resistance = 22K Ω
- Power Rating = 1.00 W

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [Professional Trimmers - Type PC910 Series - Tyco Ele...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Potentiometer
- [Element](#) = Carbon
- [Series](#) = PC910
- [Sealed](#) = No
- [Mount Angle](#) = Horizontal
- [Termination Type](#) = PCB Terminations

Electrical Characteristics:

- Resistance Selection (Ω) = K
- [Resistance \(\$\Omega\$ \)](#) = 22K
- [Power Rating \(W\)](#) = 1.00
- [Tolerance \(%\)](#) = 10

Termination Features:

- [Termination Post Orientation](#) = In Line

Body Features:

- [Shaft Style](#) = Knurled, 16mm
- [Package, Component Size](#) = 16

Configuration Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Top
- [Adjustment Style](#) = Spindle
- [Operating Function](#) = Single Turn

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Citec

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address



Provide Website Feedback