

NOTES:

MATERIAL:

HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.

TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.

SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.

ELECTRICAL:

UL CLASS C: 20A, 150V.

UL CLASS D: 10A, 300V.

CSA TYPE B: 20A, 300V.

CSA TYPE C: 20A, 300V.

CSA TYPE D: 10A, 300V.

CSA TYPE E: 20A, 300V.

WIRE RANGE: 12–22 AWG

MECHANICAL:

MAXIMUM TORQUE RATING: 7 IN-LBS.

RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS

OTHERWISE STATED.

1 SCREWS ARE BOTTOMED, NO THREAD INTERRUPT.

△ SCREWS ARE NICKEL PLATED BRASS.

△₃ SCREWS ARE CAPTIVE.








4 SEE FIGURE.

5 PRELIMINARY PART NUMBER.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

△₇ TERMINAL FINISH: MATTE TIN

8 OBSOLETE



2-796658-4

		8 5	.160	4DB-P108-04-SPCL	1.365	4	3-796658-0
		8 5	.160	4DB-P108-03-SPCL	1.040	3	2-796658-9
		8	.160	4DB-P108-30	9.815	30	5-1437667-5
		8	.160	4DB-P108-29	9.490	29	796658-9
		8	.160	4DB-P108-28	9.165	28	5-1437667-3
		8	.160	4DB-P108-27	8.840	27	796658-8
		8	.160	4DB-P108-26	8.515	26	5-1437667-2
		8	.160	4DB-P108-25	8.190	25	796658-7
		8	.160	4DB-P108-24	7.865	24	5-1437667-0
		8	.160	4DB-P108-23	7.540	23	796658-6
RUPT.		8	.160	4DB-P108-22	7.215	22	4-1437667-8
		8	.160	4DB-P108-21	6.890	21	796658-2
		8	.160	4DB-P108-20	6.565	20	4-1437667-6
		8	.160	4DB-P108-19	6.240	19	4-1437667-5
		8	.160	4DB-P108-18	5.915	18	4-1437667-4
	8 5	4	.160	4DB-P108-16-105	5.590	17	2-796628-4
		8	.160	4DB-P108-17	5.590	17	4-1437667-2
		8	.160	4DB-P108-16	5.265	16	4-1437667-0
ING PER		8	.160	4DB-P108-15	4.940	15	3-1437667-9
	2 1		.160	4DB-P108-14-102	4.615	14	2-796658-5
	2		.160	4DB-P108-14-102	4.615	14	2-796658-3
			.160	4DB-P108-14	4.615	14	3-1437667-8
			.160	4DB-P108-13	4.290	13	3-1437667-7
			.160	4DB-P108-12	3.965	12	3-1437667-6
			.160	4DB-P108-11	3.640	11	3-1437667-5
			.160	4DB-P108-10	3.315	10	3-1437667-3
	8 5 2		.160	4DB-P106-09-094	2.990	9	1-796658-7
			.160	4DB-P108-09	2.990	9	3-1437667-2
6 1	OBSOLETE		.160	4DB-P108-08-091	2.665	8	-1-796658-4
			.160	4DB-P108-08	2.665	8	3-1437667-1
	8 5 3 2		.160	4DB-P106-07-100	2.340	7	2-796658-2
			.160	4DB-P106-07-093	2.340	7	1-796658-6
			.160	4DB-P108-07	2.340	7	3-1437667-0
	8 5 3 2		.160	4DB-P106-06-099	2.015	6	2-796658-1
6 1	OBSOLETE		.160	4DB-P108-06-090	2.015	6	-1-796658-3
	8 5		.200	4DB-P108-06	2.015	6	2-796658-6
			.160	4DB-P108-06	2.015	6	2-1437667-9
	8 5 3 2		.160	4DB-P106-05-098	1.690	5	2-796658-0
6 4	OBSOLETE		.160	4DB-P108-05-093	1.690	5	-1-796658-5
			.160	4DB-P108-05	1.690	5	2-1437667-8
	8 5 3 2		.160	4DB-P106-04-097	1.365	4	1-796658-9
	1		.160	4DB-P108-04-089	1.365	4	1-796658-2
			.160	4DB-P108-04	1.365	4	2-1437667-6
	8 5 3 2		.160	4DB-P106-03-096	1.040	3	1-796658-8
	6 1		.160	4DB-P108-03-088	1.040	3	-1-796658-1
			.160	4DB-P108-03	1.040	3	2-1437667-5
	7		.142	4DB-P108-02-143	.715	2	2-796658-8
			.142	4DB-P108-02-142	.715	2	2-796658-7
			.160	4DB-P108-02	.715	2	2-1437667-4
			DIM B	CATALOG NUMBER	DIM A	NO OF POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S WELDON		01MAY2003		 TE Connectivity								
			CHK S YODER		5/1/03										
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD S YODER		5/1/03		NAME							
		0 PLC ± -		PRODUCT SPEC		ASSEMBLY, DUAL BARRIER 4DB P108 XX									
		1 PLC ± .01		—											
		2 PLC ± .005		APPLICATION SPEC											
		3 PLC ± -		—											
4 PLC ± ± 1°						SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2		00779		C-2-1437667-4		—			
-		-		—											
CUSTOMER DRAWING						SCALE		NTS		SHEET		1 OF 1		REV N8	