

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

BD

36

P

LTR

DESCRIPTION

DATE

DWN

APVD

F

REDRAWN PER EC 0020-930-95


20 SEP 95

-

-

4.06 MAX DIA
[.160]2.92 DIA
[.115]0.64 [.025] X
7.62±0.38 [.300±.015] DEEP
4 SLOTS8.38
[.330]10.29
[.405]20.45
20.07
[.805]
[.790]SCREWDRIVER SLOT
0.79 [.031] WIDE
X 1.27 [.050] DEEP4.57 DIA
[.180]4-40 UNC-2A
THREADLOCKWASHER
MATERIAL: TIN-BRASS ALLOY
FINISH: 0.38µm [.000015] MIN GOLD OVER
1.27µm [.000050] MIN NICKELCORNER GUIDE SOCKET
MATERIAL: BERYLLIUM COPPER
FINISH: 0.38µm [.000015] MIN GOLD OVER
1.27µm [.000050] MIN NICKELHEX NUT
MATERIAL: BRASS
FINISH: 0.38µm [.000015] MIN GOLD OVER
1.27µm [.000050] MIN NICKEL

202512-1

PART
NUMBERTHIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
mm [INCHES]

MATERIAL

SEE CALLOUTS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.13 [.005]
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

SEE CALLOUTS

DWN

C.DORWART

20 SEP 95

CHK

R.STONE

25 SEP 95

APVD

G.STEINHAEUER

04 OCT 95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMPAMP Incorporated
Harrisburg, PA 17105-3608

NAME

CORNER GUIDE SOCKET ASSEMBLY,
UNASSEMBLED, M SERIES

SIZE

CAGE CODE

DRAWING NO

A3

00779

C=202512

SCALE
5:1SHEET
1 OF 1REV
F