




DESIGNED FOR USE WITH	
RG-188/U	
CABLE ENTRY DIAMETER	
MINIMUM	
CONTACT	.021
DIELECTRIC	.023
SLEEVE	.066
FERRULE	.125

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₂	REVISED	9/13/86	AMP

HOUSING CLAMP NUT SLEEVE	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
O-RING	SILICONE RUBBER PER ZZ-R-765	N/A
SHRINK TUBING	HEAT SHRINKABLE POLYOLEFIN COMPOUND MIL-I-23053/4	N/A
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	GOLD PLATE PER MIL-G-45204

COMPONENT	MATERIAL	FINISH
-----------	----------	--------

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES			DRAWN BY		DATE			AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599
			FMC		9/15/77			
			CHECKED BY		9/21/77			
KWW								
FRAC.			DEC.		ANGLES			
± 1/64			±.005		± 1°			
APPD BY			RMF		9/21/77			

USE ASSY PROCEDURE		TITLE "OSM" STRAIGHT CABLE JACK CRIMP-CLAMP ATTACHMENT		
408-04808 (20-057)		SIZE B	CODE IDENT NO. 26805	REV 01 ₂
NO. A.P.		SCALE 5:1	2032-5003-02	SHEET 1 OF 1

NOTES:
1. CAPTURED CENTER CONTACT

.XXX = in
XX.X = mm (REF)