

REV. T

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES


TOLERANCES ARE:

ONE PLACE DECIMALS  $\pm .1$  [.3] THREE PLACE DECIMALS  $\pm .005$  [.13]  
 TWO PLACE DECIMALS  $\pm .01$  [.3] FOUR PLACE DECIMALS  $\pm .0020$  [.051]

ANGLES  
 $\pm 2^\circ$

TITLE:  
 LOW PROFILE  
 SOCKET STRIP

DWG NO:  
 SLW-1XX-01-X-X  
 SHEET 1 OF 1



POSITION SPECIFICATION  
 -01 THRU -50 PER ROW  
 "A" = NO. OF POS. x .100 [2.54]




ROW SPECIFICATION  
 -D: DOUBLE (USE SLW-50-D)  
 -S: SINGLE (USE SLW-50-S)

CONTACT STYLE  
 -01: USE C-28-X

PLATING SPECIFICATION  
 -G: GOLD-SPECIFY -G IN CONTACT SUFFIX -X  
 -T: TIN-SPECIFY -T IN CONTACT SUFFIX -X  
 -S: SELECTIVE-SPECIFY -S IN CONTACT SUFFIX -X  
 -F: FLASH SELECTIVE GOLD-SPECIFY -F IN CONTACT SUFFIX -X  
 -H: HEAVY GOLD-SPECIFY -H IN CONTACT SUFFIX -X

## NOTES:

1. MIN PUSHOUT FORCE: 1 lb.
  2. MAX BOW: .005 in/in [mm/mm], .025 [.64]
  3. CUT END WALLS TO BE .012 [.30] MIN.
  4. ( $\text{C}_1$ ) REPRESENTS CRITICAL DIM.
- FOR STATISTICAL PROCESS CONTROL.
5. .010 [.25] MAX CUT FLASH
  6. NO TUBE PACKAGING REQUIRED



PLOT SCALE: 1=.1

Do not scale  
 from this print

**PROPRIETARY NOTE**

THIS DOCUMENT CONTAINS INFORMATION  
 CONFIDENTIAL AND PROPRIETARY TO  
 SAMTEC INC. AND SHALL NOT BE  
 REPRODUCED OR TRANSMITTED TO  
 OTHER DOCUMENTS OR DISCLOSED TO  
 OTHERS OR USED FOR ANY PURPOSE  
 OTHER THAN THAT FOR WHICH IT WAS  
 OBTAINED WITHOUT THE EXPRESSED  
 WRITTEN CONSENT OF SAMTEC INC.

**samtec**

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150  
 PHONE (812) 944-6733 P.O. BOX 1147  
 CODE 55322

MADE BY: PURVIS 9-4-87  
 CHECKED BY: MCCARTIN

ENG.  
 APPROVAL  
 DEM

SLW-1XX-01-X-X  
 SHEET 1 OF 1