

10 9 8 7 6 5 4 3 2 1

F

E

D


C

B

A

7132-1283

PART NO. SEE CHART
Dwg. NO. SD-92316-001



ORDERING INFORMATION

92316-****

CIRCUIT SIZE
LENGTH L IN CENTIMETRES

LENGTHS AVAILABLE FROM 6 CM TO 120 CM

e.g. 92316-1208 = 12 CIRCUIT
WITH LENGTH L OF 8 CM.

NOTE : FOR LENGTHS OF
100 CM , THE PART NO. IS 92316-***01
105 CM , THE PART NO. IS 92316-***02
110 CM , THE PART NO. IS 92316-***03
115 CM , THE PART NO. IS 92316-***04
120 CM , THE PART NO. IS 92316-***05

90327 CONNECTOR

CIRCUIT SIZE	DIMENSION W
4	7.59
6	10.13
8	12.67
10	15.21
12	17.75
14	20.29
16	22.83
18	25.37
20	27.91
22	30.45
24	32.99
26	35.53

90584 CONNECTOR

CIRCUIT SIZE	DIMENSION W
4	7.59
6	10.13
8	12.67
10	15.21
12	17.75
14	20.29
16	22.83
18	25.37
20	27.91
22	30.45
24	32.99
26	35.53

CABLE DETAILS:

28 AWG , 1.27 MM PITCH , 7 STRANDS WITH TINNED COPPER ,
GREY PVC INSULATION WITH A COLOURED POLARITY STRIPE
INDICATING CIRCUIT NO. 1 , UL 2651.

NOTES:

1. SEE PRODUCT SPECIFICATIONS PS-99020-0011.
2. SEE TERMINATION SPECIFICATION ES-99033-0001.
3. SEE TERMINATION SPECIFICATION ES-99033-0002.
4. SEE CABLE SPECIFICATION ES-99027-0006.
5. HARNESSES WILL BE 100% ELECTRICALLY TESTED FOR SHORTS AND DISCONTINUITIES.

REF DIM ADDED EC NO. 2003-0374 DRAWN: P.FINN 02/10/21 CHK: / / / APP: / / /	QUALITY SYMBOLS MAJOR CRITICAL	DESCRIPTION REV	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 4 : 1	DESIGN UNITS ☒ mm ☐ INCH	THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY		SHT	REV
			4 PLACES ±0. ±.	DRAWN BY & DATE MCURRAN 98/06/19	TITLE: PICO FLEX IDT TO BOARD-IN STANDARD ASSEMBLIES			MATERIAL NO. DRAWING NO. SHEET NO.	SIZE		
			3 PLACES ±0. ±.	CHECKED BY & DATE AMcCANN 98/06/19	MOLEX INCORPORATED						
			2 PLACES ±0. ±.	APPROVED BY & DATE MWILHITE 98/06/19	CAD FILENAME S92316X1.DGN					SD-92316-001	
C			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.						

10 9 8 7 6 5 4 3 2 1