

Continued from preceding page.

SWITCHING APPLICATIONS

(Classified by VCE0 and arranged in order of package. Minus sign for PNP is omitted due to space limitations.)

Type Number	Case	Applications	Absolute Maximum Ratings/Ta=25°C						Electrical Characteristics/Ta=25°C						
			VCE0	VCE0	VEBO	IC	PC *TC=25°C	Tj	VCE	IC	hFE	VCE	IC	fT	tf (max) [μs]
			[V]	[V]	[V]	[A]	[W]	[°C]				[V]	[A]	[MHz]	
2 SC 3 1 5 2	T03PB	Switching Regulator	900	800	7	3.0	80*	150	5	0.2	>10	10	0.2	15	0.7
2 SC 3 4 5 8	T03PB	Switching Regulator (High-Speed)	1100	800	7	3.0	80*	150	5	0.2	>10	10	0.2	15	0.3
2 SC 3 4 5 9	T03PB	Switching Regulator (High-Speed)	1100	800	7	4.5	90*	150	5	0.3	>10	10	0.3	15	0.3
2 SC 3 1 5 3	T03PB	Switching Regulator	900	800	7	6.0	100*	150	5	0.4	>10	10	0.4	15	0.7
2 SC 3 4 6 0	T03PB	Switching Regulator (High-Speed)	1100	800	7	6.0	100*	150	5	0.4	>8	10	0.4	15	0.3
2 SC 3 4 6 1	T03PB	Switching Regulator (High-Speed)	1100	800	7	8.0	120*	150	5	0.8	>10	10	0.8	15	0.3
2 SC 3 5 5 2	T03PB	Switching Regulator	1100	800	7	12	150*	150	5	0.8	>10	10	0.8	15	0.3
2 SC 3 4 6 5	T03	Switching Regulator	1100	800	7	12	160	150	5	4.0	>8	10	0.8	15	0.3

TV/CRT DISPLAY APPLICATIONS(I)

(Classified by package and arranged in order of increasing PC. Minus sign for PNP is omitted due to space limitation.)

Type Number	Case	Applications	Absolute Maximum Ratings/Ta=25°C						Electrical Characteristics/Ta=25°C							
			VCBO	VCEO	VEBO	IC	PC *TC=25°C	Tj	VCB [V]	ICBO (max) [A]	VCE [V]	IC [A]	hFE	fT		
			[V]	[V]	[V]	[A]	[W]	[°C]						VCE [V]	IC [A]	[MHz]
2 S C 2 8 5 7	NP	Color TV Ver., Sound Driver	180	180	5	50m	500m	150	180	1.0 μ	10	10m	40~320	30	10m	>50
2 S C 3 5 0 4	MP	High-Definition CRT Display, Video Output	70	60	4	50m	900m	150	40	0.1 μ	10	10m	60~320	10	10m	500
2 S C 2 2 2 8 Y	MP	TV Video Output	160	160	5	50m	900m	150	160	1.0 μ	10	10m	40~320	30	10m	>50
2 S C 2 2 2 8 A	MP	TV Video Output	200	200	5	50m	900m	150	200	1.0 μ	10	10m	40~320	30	10m	>50
2 S C 2 2 7 1	MP	Chroma Output, HoriDef. Driver	300	300	6	100m	900m	150	200	1.0 μ	10	10m	40~200	30	10m	>50
2 S A 1 3 7 0	MP	High-Definition CRT Display, Video Output	200	200	5	100m	1	150	150	0.1 μ	10	10m	40~320	30	10m	150
2 S C 3 4 6 7	MP	High-Definition CRT Display, Video Output	200	200	5	100m	1	150	150	0.1 μ	10	10m	40~320	30	10m	150
2 S A 1 3 7 1	MP	High-Definition CRT Display, Video Output	300	300	5	100m	1	150	200	0.1 μ	10	10m	40~320	30	10m	150
2 S C 3 4 6 8	MP	High-Definition CRT Display, Video Output	300	300	5	100m	1	150	200	0.1 μ	10	10m	40~320	30	10m	150
2 S A 1 3 5 2	T0126	High-Definition CRT Display, Video Output	200	200	5	100m	5*	150	150	0.1 μ	10	10m	40~320	30	10m	70
2 S C 3 4 1 6	T0126	High-Definition CRT Display, Video Output	200	200	5	100m	5*	150	150	0.1 μ	10	10m	40~320	30	10m	70
2 S A 1 3 8 0	T0126	High-Definition CRT Display, Video Output	200	200	5	100m	5*	150	150	0.1 μ	10	10m	40~320	30	10m	150
2 S C 3 5 0 2	T0126	High-Definition CRT Display, Video Output	200	200	5	100m	5*	150	150	0.1 μ	10	10m	40~320	30	10m	150
2 S A 1 3 8 1	T0126	High-Definition CRT Display, Video Output	300	300	5	100m	7*	150	200	0.1 μ	10	10m	40~320	30	10m	150
2 S C 3 5 0 3	T0126	High-Definition CRT Display, Video Output	300	300	5	100m	7*	150	200	0.1 μ	10	10m	40~320	30	10m	150
2 S A 1 3 5 3	T0126	High-Definition CRT Display, Video Output	300	300	5	100m	10*	150	200	0.1 μ	10	10m	40~320	30	10m	70
2 S C 3 4 1 7	T0126	High-Definition CRT Display, Video Output	300	300	5	100m	10*	150	200	0.1 μ	10	10m	40~320	30	10m	70
2 S C 2 6 2 1	T0126	High-Definition CRT Display, Video Output	300	300	6.5	200m	10*	150	200	1.0 μ	10	10m	40~200	30	10m	>50