







- 1

MATERIAL;
CONTACTS - BRASS.
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR; BLACK.
- 2

PLATING;
CONTACTS - 2.54 μ m MINIMUM TIN-LEAD OVER 1.27 μ m MINIMUM NICKEL ALL OVER.
- 4

RECOMMENDED PC BOARD THICKNESS OF 1.57.



36.86	28.70	33.00	40.00	24	2-794618-4
33.86	25.70	30.00	37.00	22	2-794618-2
30.86	22.70	27.00	34.00	20	2-794618-0
27.86	19.70	24.00	31.00	18	1-794618-8
24.86	16.70	21.00	28.00	16	1-794618-6
21.86	13.70	18.00	25.00	14	1-794618-4
18.86	10.70	15.00	22.00	12	1-794618-2
15.86	7.70	12.00	19.00	10	1-794618-0
12.86	4.70	9.00	16.00	8	794618-8
9.86	-	6.00	13.00	6	794618-6
6.86	-	3.00	10.00	4	794618-4
3.86	-	-	7.00	2	794618-2
DIM Y	DIM W	DIM Z	DIM X	NO. OF POSN.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±.0
1 PLC	±.0
2 PLC	±0.13
3 PLC	±.0
4 PLC	±.0
ANGLES	±
FINISH	±

2

DWN: B. HAYMAKER 12AUG99
CHK: K. COBLE 12AUG99
APVD: K. COBLE 12AUG99

PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

AMP Incorporated
Harrisburg, PA 17105-3608

NAME: THRU-HOLE, R/A, TIN HEADER, PLASTIC BOARDLOCK, DUAL ROW, MICRO MATE-N-LOK™

SIZE: A2
CAGE CODE: 00779
DRAWING NO: 794618

SCALE: 4:1
SHEET: 1 OF 1
REV: D

AMP 1471-9 REV 09MAY94

Pro/ENGINEER DRAWING

794618