






POS 2,4,6,8,10,12,14,16,18,20



POS 3,5,7,9,11,13,15,17,19



ASSEMBLY LAYOUT
TOP ENTRY TYPE

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family Minitek			
ltr	ecn no	dr	date	tolerances unless otherwise specified				title 1.0mm Vertical Header					
				angles	linear	.0±.30							
						.00±.20							
				0°±x'		.000±.10							
				dr	TONY LENG	2018-03-19				dwg no		sheet 2 of 2	size
				enr	TONY LENG	2018-03-19				10147605		A3	
				chr	ZK HU	2018-03-19							
				appd	TIM YAO	2018-03-19							
sheet index	revision sheet	A	A	1	2								