






SUGGESTED MATING TAB





- 1
- MATL: 1/2H BRASS OR NICKEL PL STEEL.
- 2
- NO BURRS PERMISSIBLE AT HOLE.
- 3
- MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4
- TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F
- 5
- HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



SECTION B-B

- 1
- DIMENSIONS IN BRACKETS ARE IN INCHES.
- 2
- CONTINUOUS STRIP ON REELS.
- 3
- THE 1.40 [.055] / 1.27 [.050] DIMENSION MUST BE MAINTAINED BY THE APPLICATOR CUT-OFF TO ENSURE THE PROPER LOCKING FUNCTION OF THE RECEPTACLE.



SECTION C-C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
BRASS

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.25 [.010]
4 PLC ± -
ANGLES ± -
FINISH
TIN

DWN
JR RUTH
7/28/86

CHK
G YETTER
1/23/87

APVD
R KUZO
1/23/87

PRODUCT SPEC
-

APPLICATION SPEC
114-2074

WEIGHT
-

CUSTOMER DRAWING

INSULATION RANGE
3.81-5.08 [.150-.200]

WIRE SIZE
3.0-6.0 mm² [12-10]

PART NO
63239-1

TE Connectivity

NAME
RECPT, POSITIVE LOCK,
.250 SERIES

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=63239

RESTRICTED TO
-

SCALE
NTS

SHEET
1 OF 1

REV
L