



MACRONIX  
INTERNATIONAL Co., LTD.

**MX29LV640E T/B**

---

**MX29LV640E T/B**

**DATASHEET**

## Contents

|                                                                                     |           |
|-------------------------------------------------------------------------------------|-----------|
| <b>FEATURES .....</b>                                                               | <b>5</b>  |
| <b>PIN CONFIGURATION .....</b>                                                      | <b>6</b>  |
| <b>PIN DESCRIPTION .....</b>                                                        | <b>7</b>  |
| <b>BLOCK DIAGRAM.....</b>                                                           | <b>8</b>  |
| <b>BLOCK STRUCTURE.....</b>                                                         | <b>9</b>  |
| Table 1-1. MX29LV640ET SECTOR GROUP ARCHITECTURE .....                              | 9         |
| Top Boot Security Sector Addresses .....                                            | 12        |
| Table 1-2. MX29LV640EB SECTOR GROUP ARCHITECTURE .....                              | 13        |
| Bottom Boot Security Sector Addresses .....                                         | 16        |
| <b>BUS OPERATION .....</b>                                                          | <b>17</b> |
| Table 2-1. BUS OPERATION .....                                                      | 17        |
| Table 2-2. BUS OPERATION .....                                                      | 18        |
| <b>FUNCTIONAL OPERATION DESCRIPTION .....</b>                                       | <b>19</b> |
| WRITE COMMANDS/COMMAND SEQUENCES .....                                              | 19        |
| REQUIREMENTS FOR READING ARRAY DATA.....                                            | 19        |
| ACCELERATED PROGRAM OPERATION .....                                                 | 19        |
| RESET# OPERATION .....                                                              | 20        |
| SECTOR GROUP PROTECT OPERATION .....                                                | 20        |
| CHIP UNPROTECT OPERATION.....                                                       | 20        |
| TEMPORARY SECTOR GROUP UNPROTECT OPERATION .....                                    | 20        |
| WRITE PROTECT (WP#) .....                                                           | 21        |
| AUTOMATIC SELECT OPERATION.....                                                     | 21        |
| VERIFY SECTOR GROUP PROTECT STATUS OPERATION.....                                   | 21        |
| SECURITY SECTOR FLASH MEMORY REGION .....                                           | 21        |
| Factory Locked: Security Sector Programmed and Protected at the Factory .....       | 21        |
| Customer Lockable: Security Sector NOT Programmed or Protected at the Factory ..... | 22        |
| DATA PROTECTION .....                                                               | 22        |
| LOW VCC WRITE INHIBIT .....                                                         | 22        |
| WRITE PULSE "GLITCH" PROTECTION.....                                                | 22        |
| LOGICAL INHIBIT .....                                                               | 22        |
| POWER-UP SEQUENCE .....                                                             | 22        |
| POWER-UP WRITE INHIBIT .....                                                        | 23        |
| POWER SUPPLY DECOUPLING .....                                                       | 23        |
| <b>COMMAND OPERATIONS.....</b>                                                      | <b>24</b> |
| TABLE 3. MX29LV640E T/B COMMAND DEFINITIONS .....                                   | 24        |
| RESET .....                                                                         | 25        |
| AUTOMATIC SELECT COMMAND SEQUENCE .....                                             | 25        |
| AUTOMATIC PROGRAMMING .....                                                         | 26        |
| CHIP ERASE.....                                                                     | 27        |

|                                                                                |           |
|--------------------------------------------------------------------------------|-----------|
| SECTOR ERASE .....                                                             | 27        |
| SECTOR ERASE SUSPEND .....                                                     | 28        |
| SECTOR ERASE RESUME .....                                                      | 28        |
| <b>COMMON FLASH MEMORY INTERFACE (CFI) MODE .....</b>                          | <b>29</b> |
| QUERY COMMAND AND COMMON FLASH INTERFACE (CFI) MODE .....                      | 29        |
| Table 4-1. CFI mode: Identification Data Values .....                          | 29        |
| Table 4-2. CFI Mode: System Interface Data Values .....                        | 29        |
| Table 4-3. CFI Mode: Device Geometry Data Values .....                         | 30        |
| Table 4-4. CFI Mode: Primary Vendor-Specific Extended Query Data Values .....  | 31        |
| <b>ELECTRICAL CHARACTERISTICS .....</b>                                        | <b>32</b> |
| ABSOLUTE MAXIMUM STRESS RATINGS .....                                          | 32        |
| OPERATING TEMPERATURE AND VOLTAGE .....                                        | 32        |
| DC CHARACTERISTICS .....                                                       | 33        |
| SWITCHING TEST CIRCUITS .....                                                  | 34        |
| SWITCHING TEST WAVEFORMS .....                                                 | 34        |
| AC CHARACTERISTICS .....                                                       | 35        |
| <b>WRITE COMMAND OPERATION .....</b>                                           | <b>36</b> |
| Figure 1. COMMAND WRITE OPERATION .....                                        | 36        |
| <b>READ/RESET OPERATION .....</b>                                              | <b>37</b> |
| Figure 2. READ TIMING WAVEFORMS .....                                          | 37        |
| Figure 3. RESET# TIMING WAVEFORM .....                                         | 38        |
| <b>ERASE/PROGRAM OPERATION .....</b>                                           | <b>39</b> |
| Figure 4. AUTOMATIC CHIP ERASE TIMING WAVEFORM .....                           | 39        |
| Figure 5. AUTOMATIC CHIP ERASE ALGORITHM FLOWCHART .....                       | 40        |
| Figure 6. AUTOMATIC SECTOR ERASE TIMING WAVEFORM .....                         | 41        |
| Figure 7. AUTOMATIC SECTOR ERASE ALGORITHM FLOWCHART .....                     | 42        |
| Figure 8. ERASE SUSPEND/RESUME FLOWCHART .....                                 | 43        |
| Figure 9. AUTOMATIC PROGRAM TIMING WAVEFORMS .....                             | 44        |
| Figure 10. ACCELERATED PROGRAM TIMING DIAGRAM .....                            | 44        |
| Figure 11. CE# CONTROLLED WRITE TIMING WAVEFORM .....                          | 45        |
| Figure 12. AUTOMATIC PROGRAMMING ALGORITHM FLOWCHART .....                     | 46        |
| <b>SECTOR GROUP PROTECT/CHIP UNPROTECT .....</b>                               | <b>47</b> |
| Figure 13. SECTOR GROUP PROTECT/CHIP UNPROTECT WAVEFORM (RESET# Control) ..... | 47        |
| Figure 14-1. IN-SYSTEM SECTOR GROUP PROTECT WITH RESET#=Vhv .....              | 48        |
| Figure 14-2. CHIP UNPROTECT ALGORITHMS WITH RESET#=Vhv .....                   | 49        |
| Table 5. TEMPORARY SECTOR GROUP UNPROTECT .....                                | 50        |
| Figure 15. TEMPORARY SECTOR GROUP UNPROTECT WAVEFORMS .....                    | 50        |
| Figure 16. TEMPORARY SECTOR GROUP UNPROTECT FLOWCHART .....                    | 51        |
| Figure 17. SILICON ID READ TIMING WAVEFORM .....                               | 52        |
| <b>WRITE OPERATION STATUS .....</b>                                            | <b>53</b> |
| Figure 18. DATA# POLLING TIMING WAVEFORMS (DURING AUTOMATIC ALGORITHMS) .....  | 53        |
| Figure 19. DATA# POLLING ALGORITHM .....                                       | 54        |



|                                                                                                          |           |
|----------------------------------------------------------------------------------------------------------|-----------|
| Figure 20. TOGGLE BIT TIMING WAVEFORMS (DURING AUTOMATIC ALGORITHMS) .....                               | 55        |
| Figure 21. TOGGLE BIT ALGORITHM.....                                                                     | 56        |
| Figure 22. BYTE# TIMING WAVEFORM FOR READ OPERATIONS (BYTE# switching from byte mode to word mode) ..... | 57        |
| <b>RECOMMENDED OPERATING CONDITIONS.....</b>                                                             | <b>58</b> |
| <b>ERASE AND PROGRAMMING PERFORMANCE .....</b>                                                           | <b>59</b> |
| <b>DATA RETENTION .....</b>                                                                              | <b>59</b> |
| <b>LATCH-UP CHARACTERISTICS .....</b>                                                                    | <b>59</b> |
| <b>PIN CAPACITANCE.....</b>                                                                              | <b>59</b> |
| <b>ORDERING INFORMATION .....</b>                                                                        | <b>60</b> |
| <b>PART NAME DESCRIPTION.....</b>                                                                        | <b>61</b> |
| <b>PACKAGE INFORMATION.....</b>                                                                          | <b>62</b> |
| <b>REVISION HISTORY .....</b>                                                                            | <b>64</b> |

## 64M-BIT [8M x 8/4M x 16] SINGLE VOLTAGE 3V ONLY FLASH MEMORY

### FEATURES

#### GENERAL FEATURES

- 8,388,608 x 8 / 4,194,304 x 16 switchable
- Sector Structure
  - 8KB(4KW) x 8 and 64KB(32KW) x 127
- Extra 128-word sector for security
  - Features factory locked and identifiable, and customer lockable
- Sector Groups Protection / Chip Unprotect
  - Provides sector group protect function to prevent program or erase operation in the protected sector group
  - Provides chip unprotect function to allow code changing
  - Provides temporary sector group unprotect function for code changing in previously protected sector groups
- Single Power Supply Operation
  - 2.7 to 3.6 volt for read, erase, and program operations
- Latch-up protected to 100mA from -1V to 1.5 x Vcc
- Low Vcc write inhibit : Vcc ≤ Vlko
- Compatible with JEDEC standard
  - Pinout and software compatible to single power supply Flash

#### PERFORMANCE

- High Performance
  - Fast access time: 70ns
  - Fast program time: 11us/word (typical)
  - Fast erase time: 0.5s/sector, 45s/chip (typical)
- Low Power Consumption
  - Low active read current: 9mA (typical) at 5MHz
  - Low standby current: 5uA (typical)
- 100,000 erase/program cycle (typical)
- 20 years data retention

#### SOFTWARE FEATURES

- Erase Suspend/ Erase Resume
  - Suspends sector erase operation to read data from or program data to another sector which is not being erased
- Status Reply
  - Data# Polling & Toggle bits provide detection of program and erase operation completion
- Support Common Flash Interface (CFI)

#### HARDWARE FEATURES


- Ready/Busy# (RY/BY#) Output
  - Provides a hardware method of detecting program and erase operation completion
- Hardware Reset (RESET#) Input
  - Provides a hardware method to reset the internal state machine to read mode
- WP#/ACC input pin
  - Provides accelerated program capability

## PACKAGE


- 48-Pin TSOP
- 48-Ball FBGA
- All devices are RoHS Compliant

## PIN CONFIGURATION

### 48 TSOP



### 48-Ball FBGA 6mm x 8mm (Ball Pitch=0.8mm), Top View, Balls Facing Down




## PIN DESCRIPTION


| SYMBOL  | PIN NAME                                              |
|---------|-------------------------------------------------------|
| A0~A21  | Address Input                                         |
| Q0~Q14  | Data Inputs/Outputs                                   |
| Q15/A-1 | Q15(Word Mode)/LSB addr(Byte Mode)                    |
| CE#     | Chip Enable Input                                     |
| WE#     | Write Enable Input                                    |
| OE#     | Output Enable Input                                   |
| RESET#  | Hardware Reset Pin, Active Low                        |
| BYTE#   | Word/Byte Selection Input                             |
| WP#/ACC | Hardware Write Protect/Programming Acceleration Input |
| RY/BY#  | Ready/Busy Output                                     |
| VCC     | +3.0V single power supply                             |
| GND     | Device Ground                                         |

Note: The WP#/ACC has an internal pull-up when unconnected, WP#/ACC is at Vih.

## LOGIC SYMBOL



### BLOCK DIAGRAM



## BLOCK STRUCTURE

Table 1-1. MX29LV640ET SECTOR GROUP ARCHITECTURE

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                 |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|-----------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16) |
| 1            | 64                 | 32                 | SA0    | 0000000xxx             | 000000h-00FFFFh | 000000h-07FFFFh |
| 1            | 64                 | 32                 | SA1    | 0000001xxx             | 010000h-01FFFFh | 008000h-0FFFFh  |
| 1            | 64                 | 32                 | SA2    | 0000010xxx             | 020000h-02FFFFh | 010000h-17FFFFh |
| 1            | 64                 | 32                 | SA3    | 0000011xxx             | 030000h-03FFFFh | 018000h-01FFFFh |
| 2            | 64                 | 32                 | SA4    | 0000100xxx             | 040000h-04FFFFh | 020000h-027FFFh |
| 2            | 64                 | 32                 | SA5    | 0000101xxx             | 050000h-05FFFFh | 028000h-02FFFFh |
| 2            | 64                 | 32                 | SA6    | 0000110xxx             | 060000h-06FFFFh | 030000h-037FFFh |
| 2            | 64                 | 32                 | SA7    | 0000111xxx             | 070000h-07FFFFh | 038000h-03FFFFh |
| 3            | 64                 | 32                 | SA8    | 0001000xxx             | 080000h-08FFFFh | 040000h-047FFFh |
| 3            | 64                 | 32                 | SA9    | 0001001xxx             | 090000h-09FFFFh | 048000h-04FFFFh |
| 3            | 64                 | 32                 | SA10   | 0001010xxx             | 0A0000h-0AFFFFh | 050000h-057FFFh |
| 3            | 64                 | 32                 | SA11   | 0001011xxx             | 0B0000h-0BFFFFh | 058000h-05FFFFh |
| 4            | 64                 | 32                 | SA12   | 0001100xxx             | 0C0000h-0CFFFFh | 060000h-067FFFh |
| 4            | 64                 | 32                 | SA13   | 0001101xxx             | 0D0000h-0DFFFFh | 068000h-06FFFFh |
| 4            | 64                 | 32                 | SA14   | 0001110xxx             | 0E0000h-0EFFFFh | 070000h-077FFFh |
| 4            | 64                 | 32                 | SA15   | 0001111xxx             | 0F0000h-0FFFFFh | 078000h-07FFFFh |
| 5            | 64                 | 32                 | SA16   | 0010000xxx             | 100000h-10FFFFh | 080000h-087FFFh |
| 5            | 64                 | 32                 | SA17   | 0010001xxx             | 110000h-11FFFFh | 088000h-08FFFFh |
| 5            | 64                 | 32                 | SA18   | 0010010xxx             | 120000h-12FFFFh | 090000h-097FFFh |
| 5            | 64                 | 32                 | SA19   | 0010011xxx             | 130000h-13FFFFh | 098000h-09FFFFh |
| 6            | 64                 | 32                 | SA20   | 0010100xxx             | 140000h-14FFFFh | 0A0000h-0A7FFFh |
| 6            | 64                 | 32                 | SA21   | 0010101xxx             | 150000h-15FFFFh | 0A8000h-0AFFFFh |
| 6            | 64                 | 32                 | SA22   | 0010110xxx             | 160000h-16FFFFh | 0B0000h-0B7FFFh |
| 6            | 64                 | 32                 | SA23   | 0010111xxx             | 170000h-17FFFFh | 0B8000h-0BFFFFh |
| 7            | 64                 | 32                 | SA24   | 0011000xxx             | 180000h-18FFFFh | 0C0000h-0C7FFFh |
| 7            | 64                 | 32                 | SA25   | 0011001xxx             | 190000h-19FFFFh | 0C8000h-0CFFFFh |
| 7            | 64                 | 32                 | SA26   | 0011010xxx             | 1A0000h-1AFFFFh | 0D0000h-0D7FFFh |
| 7            | 64                 | 32                 | SA27   | 0011011xxx             | 1B0000h-1BFFFFh | 0D8000h-0DFFFFh |
| 8            | 64                 | 32                 | SA28   | 0011100xxx             | 1C0000h-1CFFFFh | 0E0000h-0E7FFFh |
| 8            | 64                 | 32                 | SA29   | 0011101xxx             | 1D0000h-1DFFFFh | 0E8000h-0EFFFFh |
| 8            | 64                 | 32                 | SA30   | 0011110xxx             | 1E0000h-1EFFFFh | 0F0000h-0F7FFFh |
| 8            | 64                 | 32                 | SA31   | 0011111xxx             | 1F0000h-1FFFFFh | 0F8000h-0FFFFFh |
| 9            | 64                 | 32                 | SA32   | 0100000xxx             | 200000h-20FFFFh | 100000h-107FFFh |
| 9            | 64                 | 32                 | SA33   | 0100001xxx             | 210000h-21FFFFh | 108000h-10FFFFh |
| 9            | 64                 | 32                 | SA34   | 0100010xxx             | 220000h-22FFFFh | 110000h-117FFFh |
| 9            | 64                 | 32                 | SA35   | 0100011xxx             | 230000h-23FFFFh | 118000h-11FFFFh |
| 10           | 64                 | 32                 | SA36   | 0100100xxx             | 240000h-24FFFFh | 120000h-127FFFh |
| 10           | 64                 | 32                 | SA37   | 0100101xxx             | 250000h-25FFFFh | 128000h-12FFFFh |
| 10           | 64                 | 32                 | SA38   | 0100110xxx             | 260000h-26FFFFh | 130000h-137FFFh |
| 10           | 64                 | 32                 | SA39   | 0100111xxx             | 270000h-27FFFFh | 138000h-13FFFFh |

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                 |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|-----------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16) |
| 11           | 64                 | 32                 | SA40   | 0101000xxx             | 280000h-28FFFFh | 140000h-147FFFh |
| 11           | 64                 | 32                 | SA41   | 0101001xxx             | 290000h-29FFFFh | 148000h-14FFFFh |
| 11           | 64                 | 32                 | SA42   | 0101010xxx             | 2A0000h-2AFFFFh | 150000h-157FFFh |
| 11           | 64                 | 32                 | SA43   | 0101011xxx             | 2B0000h-2BFFFFh | 158000h-15FFFFh |
| 12           | 64                 | 32                 | SA44   | 0101100xxx             | 2C0000h-2CFFFFh | 160000h-167FFFh |
| 12           | 64                 | 32                 | SA45   | 0101101xxx             | 2D0000h-2DFFFFh | 168000h-16FFFFh |
| 12           | 64                 | 32                 | SA46   | 0101110xxx             | 2E0000h-2EFFFFh | 170000h-177FFFh |
| 12           | 64                 | 32                 | SA47   | 0101111xxx             | 2F0000h-2FFFFFh | 178000h-17FFFFh |
| 13           | 64                 | 32                 | SA48   | 0110000xxx             | 300000h-30FFFFh | 180000h-187FFFh |
| 13           | 64                 | 32                 | SA49   | 0110001xxx             | 310000h-31FFFFh | 188000h-18FFFFh |
| 13           | 64                 | 32                 | SA50   | 0110010xxx             | 320000h-32FFFFh | 190000h-197FFFh |
| 13           | 64                 | 32                 | SA51   | 0110011xxx             | 330000h-33FFFFh | 198000h-19FFFFh |
| 14           | 64                 | 32                 | SA52   | 0110100xxx             | 340000h-34FFFFh | 1A0000h-1A7FFFh |
| 14           | 64                 | 32                 | SA53   | 0110101xxx             | 350000h-35FFFFh | 1A8000h-1AFFFFh |
| 14           | 64                 | 32                 | SA54   | 0110110xxx             | 360000h-36FFFFh | 1B0000h-1B7FFFh |
| 14           | 64                 | 32                 | SA55   | 0110111xxx             | 370000h-37FFFFh | 1B8000h-1BFFFFh |
| 15           | 64                 | 32                 | SA56   | 0111000xxx             | 380000h-38FFFFh | 1C0000h-1C7FFFh |
| 15           | 64                 | 32                 | SA57   | 0111001xxx             | 390000h-39FFFFh | 1C8000h-1CFFFFh |
| 15           | 64                 | 32                 | SA58   | 0111010xxx             | 3A0000h-3AFFFFh | 1D0000h-1D7FFFh |
| 15           | 64                 | 32                 | SA59   | 0111011xxx             | 3B0000h-3BFFFFh | 1D8000h-1DFFFFh |
| 16           | 64                 | 32                 | SA60   | 0111100xxx             | 3C0000h-3CFFFFh | 1E0000h-1E7FFFh |
| 16           | 64                 | 32                 | SA61   | 0111101xxx             | 3D0000h-3DFFFFh | 1E8000h-1EFFFFh |
| 16           | 64                 | 32                 | SA62   | 0111110xxx             | 3E0000h-3EFFFFh | 1F0000h-1F7FFFh |
| 16           | 64                 | 32                 | SA63   | 0111111xxx             | 3F0000h-3FFFFFh | 1F8000h-1FFFFFh |
| 17           | 64                 | 32                 | SA64   | 1000000xxx             | 400000h-40FFFFh | 200000h-207FFFh |
| 17           | 64                 | 32                 | SA65   | 1000001xxx             | 410000h-41FFFFh | 208000h-20FFFFh |
| 17           | 64                 | 32                 | SA66   | 1000010xxx             | 420000h-42FFFFh | 210000h-217FFFh |
| 17           | 64                 | 32                 | SA67   | 1000011xxx             | 430000h-43FFFFh | 218000h-21FFFFh |
| 18           | 64                 | 32                 | SA68   | 1000100xxx             | 440000h-44FFFFh | 220000h-227FFFh |
| 18           | 64                 | 32                 | SA69   | 1000101xxx             | 450000h-45FFFFh | 228000h-22FFFFh |
| 18           | 64                 | 32                 | SA70   | 1000110xxx             | 460000h-46FFFFh | 230000h-237FFFh |
| 18           | 64                 | 32                 | SA71   | 1000111xxx             | 470000h-47FFFFh | 238000h-23FFFFh |
| 19           | 64                 | 32                 | SA72   | 1001000xxx             | 480000h-48FFFFh | 240000h-247FFFh |
| 19           | 64                 | 32                 | SA73   | 1001001xxx             | 490000h-49FFFFh | 248000h-24FFFFh |
| 19           | 64                 | 32                 | SA74   | 1001010xxx             | 4A0000h-4AFFFFh | 250000h-257FFFh |
| 19           | 64                 | 32                 | SA75   | 1001011xxx             | 4B0000h-4BFFFFh | 258000h-25FFFFh |
| 20           | 64                 | 32                 | SA76   | 1001100xxx             | 4C0000h-4CFFFFh | 260000h-267FFFh |
| 20           | 64                 | 32                 | SA77   | 1001101xxx             | 4D0000h-4DFFFFh | 268000h-26FFFFh |
| 20           | 64                 | 32                 | SA78   | 1001110xxx             | 4E0000h-4EFFFFh | 270000h-277FFFh |
| 20           | 64                 | 32                 | SA79   | 1001111xxx             | 4F0000h-4FFFFFh | 278000h-27FFFFh |

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                 |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|-----------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16) |
| 21           | 64                 | 32                 | SA80   | 1010000xxx             | 500000h-50FFFFh | 280000h-287FFFh |
| 21           | 64                 | 32                 | SA81   | 1010001xxx             | 510000h-51FFFFh | 288000h-28FFFFh |
| 21           | 64                 | 32                 | SA82   | 1010010xxx             | 520000h-52FFFFh | 290000h-297FFFh |
| 21           | 64                 | 32                 | SA83   | 1010011xxx             | 530000h-53FFFFh | 298000h-29FFFFh |
| 22           | 64                 | 32                 | SA84   | 1010100xxx             | 540000h-54FFFFh | 2A0000h-2A7FFFh |
| 22           | 64                 | 32                 | SA85   | 1010101xxx             | 550000h-55FFFFh | 2A8000h-2AFFFFh |
| 22           | 64                 | 32                 | SA86   | 1010110xxx             | 560000h-56FFFFh | 2B0000h-2B7FFFh |
| 22           | 64                 | 32                 | SA87   | 1010111xxx             | 570000h-57FFFFh | 2B8000h-2BFFFFh |
| 23           | 64                 | 32                 | SA88   | 1011000xxx             | 580000h-58FFFFh | 2C0000h-2C7FFFh |
| 23           | 64                 | 32                 | SA89   | 1011001xxx             | 590000h-59FFFFh | 2C8000h-2CFFFFh |
| 23           | 64                 | 32                 | SA90   | 1011010xxx             | 5A0000h-5AFFFFh | 2D0000h-2D7FFFh |
| 23           | 64                 | 32                 | SA91   | 1011011xxx             | 5B0000h-5BFFFFh | 2D8000h-2DFFFFh |
| 24           | 64                 | 32                 | SA92   | 1011100xxx             | 5C0000h-5CFFFFh | 2E0000h-2E7FFFh |
| 24           | 64                 | 32                 | SA93   | 1011101xxx             | 5D0000h-5DFFFFh | 2E8000h-2EFFFFh |
| 24           | 64                 | 32                 | SA94   | 1011110xxx             | 5E0000h-5EFFFFh | 2F0000h-2F7FFFh |
| 24           | 64                 | 32                 | SA95   | 1011111xxx             | 5F0000h-5FFFFFh | 2F8000h-2FFFFFh |
| 25           | 64                 | 32                 | SA96   | 1100000xxx             | 600000h-60FFFFh | 300000h-307FFFh |
| 25           | 64                 | 32                 | SA97   | 1100001xxx             | 610000h-61FFFFh | 308000h-30FFFFh |
| 25           | 64                 | 32                 | SA98   | 1100010xxx             | 620000h-62FFFFh | 310000h-317FFFh |
| 25           | 64                 | 32                 | SA99   | 1100011xxx             | 630000h-63FFFFh | 318000h-31FFFFh |
| 26           | 64                 | 32                 | SA100  | 1100100xxx             | 640000h-64FFFFh | 320000h-327FFFh |
| 26           | 64                 | 32                 | SA101  | 1100101xxx             | 650000h-65FFFFh | 328000h-32FFFFh |
| 26           | 64                 | 32                 | SA102  | 1100110xxx             | 660000h-66FFFFh | 330000h-337FFFh |
| 26           | 64                 | 32                 | SA103  | 1100111xxx             | 670000h-67FFFFh | 338000h-33FFFFh |
| 27           | 64                 | 32                 | SA104  | 1101000xxx             | 680000h-68FFFFh | 340000h-347FFFh |
| 27           | 64                 | 32                 | SA105  | 1101001xxx             | 690000h-69FFFFh | 348000h-34FFFFh |
| 27           | 64                 | 32                 | SA106  | 1101010xxx             | 6A0000h-6AFFFFh | 350000h-357FFFh |
| 27           | 64                 | 32                 | SA107  | 1101011xxx             | 6B0000h-6BFFFFh | 358000h-35FFFFh |
| 28           | 64                 | 32                 | SA108  | 1101100xxx             | 6C0000h-6CFFFFh | 360000h-367FFFh |
| 28           | 64                 | 32                 | SA109  | 1101101xxx             | 6D0000h-6DFFFFh | 368000h-36FFFFh |
| 28           | 64                 | 32                 | SA110  | 1101110xxx             | 6E0000h-6EFFFFh | 370000h-377FFFh |
| 28           | 64                 | 32                 | SA111  | 1101111xxx             | 6F0000h-6FFFFFh | 378000h-37FFFFh |
| 29           | 64                 | 32                 | SA112  | 1110000xxx             | 700000h-70FFFFh | 380000h-387FFFh |
| 29           | 64                 | 32                 | SA113  | 1110001xxx             | 710000h-71FFFFh | 388000h-38FFFFh |
| 29           | 64                 | 32                 | SA114  | 1110010xxx             | 720000h-72FFFFh | 390000h-397FFFh |
| 29           | 64                 | 32                 | SA115  | 1110011xxx             | 730000h-73FFFFh | 398000h-39FFFFh |
| 30           | 64                 | 32                 | SA116  | 1110100xxx             | 740000h-74FFFFh | 3A0000h-3A7FFFh |
| 30           | 64                 | 32                 | SA117  | 1110101xxx             | 750000h-75FFFFh | 3A8000h-3AFFFFh |
| 30           | 64                 | 32                 | SA118  | 1110110xxx             | 760000h-76FFFFh | 3B0000h-3B7FFFh |
| 30           | 64                 | 32                 | SA119  | 1110111xxx             | 770000h-77FFFFh | 3B8000h-3BFFFFh |



MACRONIX  
INTERNATIONAL Co., LTD.

## MX29LV640E T/B

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                  |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|------------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16)  |
| 31           | 64                 | 32                 | SA120  | 1111000xxx             | 780000h-78FFFFh | 3C0000h-3C7FFFh  |
| 31           | 64                 | 32                 | SA121  | 1111001xxx             | 790000h-79FFFFh | 3C8000h-3CFFFFh  |
| 31           | 64                 | 32                 | SA122  | 1111010xxx             | 7A0000h-7AFFFFh | 3D0000h-3D7FFFh  |
| 31           | 64                 | 32                 | SA123  | 1111011xxx             | 7B0000h-7BFFFFh | 3D8000h-3DFFFFh  |
| 32           | 64                 | 32                 | SA124  | 1111100xxx             | 7C0000h-7CFFFFh | 3E0000h-3E7FFFh  |
| 32           | 64                 | 32                 | SA125  | 1111101xxx             | 7D0000h-7DFFFFh | 3E8000h-3EFFFFh  |
| 32           | 64                 | 32                 | SA126  | 1111110xxx             | 7E0000h-7EFFFFh | 3F0000h-3F7FFFh  |
| 33           | 8                  | 4                  | SA127  | 1111111000             | 7F0000h-7F1FFFh | 3F8000h-3FFFFFh  |
| 34           | 8                  | 4                  | SA128  | 1111111001             | 7F2000h-7F3FFFh | 3F9000h-3F9FFFh  |
| 35           | 8                  | 4                  | SA129  | 1111111010             | 7F4000h-7F5FFFh | 3FA000h-3FAFFFh  |
| 36           | 8                  | 4                  | SA130  | 1111111011             | 7F6000h-7F7FFFh | 3FB000h-3FBFFFh  |
| 37           | 8                  | 4                  | SA131  | 1111111100             | 7F8000h-7F9FFFh | 3FC000h-3FCFFFh  |
| 38           | 8                  | 4                  | SA132  | 1111111101             | 7FA000h-7FBFFFh | 3FD000h-3FDFFFh  |
| 39           | 8                  | 4                  | SA133  | 1111111110             | 7FC000h-7FDFFFh | 3FE000h-3FEFFFh  |
| 40           | 8                  | 4                  | SA134  | 1111111111             | 7FE000h-7FFFFFh | 3FF000h-3FFFFFFh |

### Top Boot Security Sector Addresses

| Sector Size       |                   | Sector Address A21~A12 | Address Range    |                  |
|-------------------|-------------------|------------------------|------------------|------------------|
| Byte Mode (bytes) | Word Mode (words) |                        | Byte Mode (x8)   | Word Mode (x16)  |
| 256               | 128               | 1111111111             | 7FFF00h-7FFFFFFh | 3FFF80h-3FFFFFFh |

Table 1-2. MX29LV640EB SECTOR GROUP ARCHITECTURE

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                 |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|-----------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16) |
| 1            | 8                  | 4                  | SA0    | 0000000000             | 000000h-001FFFh | 000000h-000FFFh |
| 2            | 8                  | 4                  | SA1    | 0000000001             | 002000h-003FFFh | 001000h-001FFFh |
| 3            | 8                  | 4                  | SA2    | 0000000010             | 004000h-005FFFh | 002000h-002FFFh |
| 4            | 8                  | 4                  | SA3    | 0000000011             | 006000h-007FFFh | 003000h-003FFFh |
| 5            | 8                  | 4                  | SA4    | 0000000100             | 008000h-009FFFh | 004000h-004FFFh |
| 6            | 8                  | 4                  | SA5    | 0000000101             | 00A000h-00BFFFh | 005000h-005FFFh |
| 7            | 8                  | 4                  | SA6    | 0000000110             | 00C000h-00DFFFh | 006000h-006FFFh |
| 8            | 8                  | 4                  | SA7    | 0000000111             | 00E000h-00FFFFh | 007000h-007FFFh |
| 9            | 64                 | 32                 | SA8    | 0000001xxx             | 010000h-01FFFFh | 008000h-00FFFFh |
| 9            | 64                 | 32                 | SA9    | 0000010xxx             | 020000h-02FFFFh | 010000h-017FFFh |
| 9            | 64                 | 32                 | SA10   | 0000011xxx             | 030000h-03FFFFh | 018000h-01FFFFh |
| 10           | 64                 | 32                 | SA11   | 0000100xxx             | 040000h-04FFFFh | 020000h-027FFFh |
| 10           | 64                 | 32                 | SA12   | 0000101xxx             | 050000h-05FFFFh | 028000h-02FFFFh |
| 10           | 64                 | 32                 | SA13   | 0000110xxx             | 060000h-06FFFFh | 030000h-037FFFh |
| 10           | 64                 | 32                 | SA14   | 0000111xxx             | 070000h-07FFFFh | 038000h-03FFFFh |
| 11           | 64                 | 32                 | SA15   | 0001000xxx             | 080000h-08FFFFh | 040000h-047FFFh |
| 11           | 64                 | 32                 | SA16   | 0001001xxx             | 090000h-09FFFFh | 048000h-04FFFFh |
| 11           | 64                 | 32                 | SA17   | 0001010xxx             | 0A0000h-0AFFFFh | 050000h-057FFFh |
| 11           | 64                 | 32                 | SA18   | 0001011xxx             | 0B0000h-0BFFFFh | 058000h-05FFFFh |
| 12           | 64                 | 32                 | SA19   | 0001100xxx             | 0C0000h-0CFFFFh | 060000h-067FFFh |
| 12           | 64                 | 32                 | SA20   | 0001101xxx             | 0D0000h-0DFFFFh | 068000h-06FFFFh |
| 12           | 64                 | 32                 | SA21   | 0001110xxx             | 0E0000h-0EFFFFh | 070000h-077FFFh |
| 12           | 64                 | 32                 | SA22   | 0001111xxx             | 0F0000h-0FFFFFh | 078000h-07FFFFh |
| 13           | 64                 | 32                 | SA23   | 0010000xxx             | 100000h-10FFFFh | 080000h-087FFFh |
| 13           | 64                 | 32                 | SA24   | 0010001xxx             | 110000h-11FFFFh | 088000h-08FFFFh |
| 13           | 64                 | 32                 | SA25   | 0010010xxx             | 120000h-12FFFFh | 090000h-097FFFh |
| 13           | 64                 | 32                 | SA26   | 0010011xxx             | 130000h-13FFFFh | 098000h-09FFFFh |
| 14           | 64                 | 32                 | SA27   | 0010100xxx             | 140000h-14FFFFh | 0A0000h-0A7FFFh |
| 14           | 64                 | 32                 | SA28   | 0010101xxx             | 150000h-15FFFFh | 0A8000h-0AFFFFh |
| 14           | 64                 | 32                 | SA29   | 0010110xxx             | 160000h-16FFFFh | 0B0000h-0B7FFFh |
| 14           | 64                 | 32                 | SA30   | 0010111xxx             | 170000h-17FFFFh | 0B8000h-0BFFFFh |
| 15           | 64                 | 32                 | SA31   | 0011000xxx             | 180000h-18FFFFh | 0C0000h-0C7FFFh |
| 15           | 64                 | 32                 | SA32   | 0011001xxx             | 190000h-19FFFFh | 0C8000h-0CFFFFh |
| 15           | 64                 | 32                 | SA33   | 0011010xxx             | 1A0000h-1AFFFFh | 0D0000h-0D7FFFh |
| 15           | 64                 | 32                 | SA34   | 0011011xxx             | 1B0000h-1BFFFFh | 0D8000h-0DFFFFh |
| 16           | 64                 | 32                 | SA35   | 0011100xxx             | 1C0000h-1CFFFFh | 0E0000h-0E7FFFh |
| 16           | 64                 | 32                 | SA36   | 0011101xxx             | 1D0000h-1DFFFFh | 0E8000h-0EFFFFh |
| 16           | 64                 | 32                 | SA37   | 0011110xxx             | 1E0000h-1EFFFFh | 0F0000h-0F7FFFh |
| 16           | 64                 | 32                 | SA38   | 0011111xxx             | 1F0000h-1FFFFFh | 0F8000h-0FFFFFh |

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                 |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|-----------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16) |
| 17           | 64                 | 32                 | SA39   | 0100000xxx             | 200000h-20FFFFh | 100000h-107FFFh |
| 17           | 64                 | 32                 | SA40   | 0100001xxx             | 210000h-21FFFFh | 108000h-10FFFFh |
| 17           | 64                 | 32                 | SA41   | 0100010xxx             | 220000h-22FFFFh | 110000h-117FFFh |
| 17           | 64                 | 32                 | SA42   | 0100011xxx             | 230000h-23FFFFh | 118000h-11FFFFh |
| 18           | 64                 | 32                 | SA43   | 0100100xxx             | 240000h-24FFFFh | 120000h-127FFFh |
| 18           | 64                 | 32                 | SA44   | 0100101xxx             | 250000h-25FFFFh | 128000h-12FFFFh |
| 18           | 64                 | 32                 | SA45   | 0100110xxx             | 260000h-26FFFFh | 130000h-137FFFh |
| 18           | 64                 | 32                 | SA46   | 0100111xxx             | 270000h-27FFFFh | 138000h-13FFFFh |
| 19           | 64                 | 32                 | SA47   | 0101000xxx             | 280000h-28FFFFh | 140000h-147FFFh |
| 19           | 64                 | 32                 | SA48   | 0101001xxx             | 290000h-29FFFFh | 148000h-14FFFFh |
| 19           | 64                 | 32                 | SA49   | 0101010xxx             | 2A0000h-2AFFFFh | 150000h-157FFFh |
| 19           | 64                 | 32                 | SA50   | 0101011xxx             | 2B0000h-2BFFFFh | 158000h-15FFFFh |
| 20           | 64                 | 32                 | SA51   | 0101100xxx             | 2C0000h-2CFFFFh | 160000h-167FFFh |
| 20           | 64                 | 32                 | SA52   | 0101101xxx             | 2D0000h-2DFFFFh | 168000h-16FFFFh |
| 20           | 64                 | 32                 | SA53   | 0101110xxx             | 2E0000h-2EFFFFh | 170000h-177FFFh |
| 20           | 64                 | 32                 | SA54   | 0101111xxx             | 2F0000h-2FFFFFh | 178000h-17FFFFh |
| 21           | 64                 | 32                 | SA55   | 0110000xxx             | 300000h-30FFFFh | 180000h-187FFFh |
| 21           | 64                 | 32                 | SA56   | 0110001xxx             | 310000h-31FFFFh | 188000h-18FFFFh |
| 21           | 64                 | 32                 | SA57   | 0110010xxx             | 320000h-32FFFFh | 190000h-197FFFh |
| 21           | 64                 | 32                 | SA58   | 0110011xxx             | 330000h-33FFFFh | 198000h-19FFFFh |
| 22           | 64                 | 32                 | SA59   | 0110100xxx             | 340000h-34FFFFh | 1A0000h-1A7FFFh |
| 22           | 64                 | 32                 | SA60   | 0110101xxx             | 350000h-35FFFFh | 1A8000h-1AFFFFh |
| 22           | 64                 | 32                 | SA61   | 0110110xxx             | 360000h-36FFFFh | 1B0000h-1B7FFFh |
| 22           | 64                 | 32                 | SA62   | 0110111xxx             | 370000h-37FFFFh | 1B8000h-1BFFFFh |
| 23           | 64                 | 32                 | SA63   | 0111000xxx             | 380000h-38FFFFh | 1C0000h-1C7FFFh |
| 23           | 64                 | 32                 | SA64   | 0111001xxx             | 390000h-39FFFFh | 1C8000h-1CFFFFh |
| 23           | 64                 | 32                 | SA65   | 0111010xxx             | 3A0000h-3AFFFFh | 1D0000h-1D7FFFh |
| 23           | 64                 | 32                 | SA66   | 0111011xxx             | 3B0000h-3BFFFFh | 1D8000h-1DFFFFh |
| 24           | 64                 | 32                 | SA67   | 0111100xxx             | 3C0000h-3CFFFFh | 1E0000h-1E7FFFh |
| 24           | 64                 | 32                 | SA68   | 0111101xxx             | 3D0000h-3DFFFFh | 1E8000h-1EFFFFh |
| 24           | 64                 | 32                 | SA69   | 0111110xxx             | 3E0000h-3EFFFFh | 1F0000h-1F7FFFh |
| 24           | 64                 | 32                 | SA70   | 0111111xxx             | 3F0000h-3FFFFFh | 1F8000h-1FFFFFh |
| 25           | 64                 | 32                 | SA71   | 1000000xxx             | 400000h-40FFFFh | 200000h-207FFFh |
| 25           | 64                 | 32                 | SA72   | 1000001xxx             | 410000h-41FFFFh | 208000h-20FFFFh |
| 25           | 64                 | 32                 | SA73   | 1000010xxx             | 420000h-42FFFFh | 210000h-217FFFh |
| 25           | 64                 | 32                 | SA74   | 1000011xxx             | 430000h-43FFFFh | 218000h-21FFFFh |
| 26           | 64                 | 32                 | SA75   | 1000100xxx             | 440000h-44FFFFh | 220000h-227FFFh |
| 26           | 64                 | 32                 | SA76   | 1000101xxx             | 450000h-45FFFFh | 228000h-22FFFFh |
| 26           | 64                 | 32                 | SA77   | 1000110xxx             | 460000h-46FFFFh | 230000h-237FFFh |
| 26           | 64                 | 32                 | SA78   | 1000111xxx             | 470000h-47FFFFh | 238000h-23FFFFh |

| Sector Group | Sector Size        |                    | Sector | Sector Address A21-A12 | Address Range   |                 |
|--------------|--------------------|--------------------|--------|------------------------|-----------------|-----------------|
|              | Byte Mode (Kbytes) | Word Mode (Kwords) |        |                        | Byte Mode (x8)  | Word Mode (x16) |
| 27           | 64                 | 32                 | SA79   | 1001000xxx             | 480000h-48FFFFh | 240000h-247FFFh |
| 27           | 64                 | 32                 | SA80   | 1001001xxx             | 490000h-49FFFFh | 248000h-24FFFFh |
| 27           | 64                 | 32                 | SA81   | 1001010xxx             | 4A0000h-4AFFFFh | 250000h-257FFFh |
| 27           | 64                 | 32                 | SA82   | 1001011xxx             | 4B0000h-4BFFFFh | 258000h-25FFFFh |
| 28           | 64                 | 32                 | SA83   | 1001100xxx             | 4C0000h-4CFFFFh | 260000h-267FFFh |
| 28           | 64                 | 32                 | SA84   | 1001101xxx             | 4D0000h-4DFFFFh | 268000h-26FFFFh |
| 28           | 64                 | 32                 | SA85   | 1001110xxx             | 4E0000h-4EFFFFh | 270000h-277FFFh |
| 28           | 64                 | 32                 | SA86   | 1001111xxx             | 4F0000h-4FFFFFh | 278000h-27FFFFh |
| 29           | 64                 | 32                 | SA87   | 1010000xxx             | 500000h-50FFFFh | 280000h-287FFFh |
| 29           | 64                 | 32                 | SA88   | 1010001xxx             | 510000h-51FFFFh | 288000h-28FFFFh |
| 29           | 64                 | 32                 | SA89   | 1010010xxx             | 520000h-52FFFFh | 290000h-297FFFh |
| 29           | 64                 | 32                 | SA90   | 1010011xxx             | 530000h-53FFFFh | 298000h-29FFFFh |
| 30           | 64                 | 32                 | SA91   | 1010100xxx             | 540000h-54FFFFh | 2A0000h-2A7FFFh |
| 30           | 64                 | 32                 | SA92   | 1010101xxx             | 550000h-55FFFFh | 2A8000h-2AFFFFh |
| 30           | 64                 | 32                 | SA93   | 1010110xxx             | 560000h-56FFFFh | 2B0000h-2B7FFFh |
| 30           | 64                 | 32                 | SA94   | 1010111xxx             | 570000h-57FFFFh | 2B8000h-2BFFFFh |
| 31           | 64                 | 32                 | SA95   | 1011000xxx             | 580000h-58FFFFh | 2C0000h-2C7FFFh |
| 31           | 64                 | 32                 | SA96   | 1011001xxx             | 590000h-59FFFFh | 2C8000h-2CFFFFh |
| 31           | 64                 | 32                 | SA97   | 1011010xxx             | 5A0000h-5AFFFFh | 2D0000h-2D7FFFh |
| 31           | 64                 | 32                 | SA98   | 1011011xxx             | 5B0000h-5BFFFFh | 2D8000h-2DFFFFh |
| 32           | 64                 | 32                 | SA99   | 1011100xxx             | 5C0000h-5CFFFFh | 2E0000h-2E7FFFh |
| 32           | 64                 | 32                 | SA100  | 1011101xxx             | 5D0000h-5DFFFFh | 2E8000h-2EFFFFh |
| 32           | 64                 | 32                 | SA101  | 1011110xxx             | 5E0000h-5EFFFFh | 2F0000h-2F7FFFh |
| 32           | 64                 | 32                 | SA102  | 1011111xxx             | 5F0000h-5FFFFFh | 2F8000h-2FFFFFh |
| 33           | 64                 | 32                 | SA103  | 1100000xxx             | 600000h-60FFFFh | 300000h-307FFFh |
| 33           | 64                 | 32                 | SA104  | 1100001xxx             | 610000h-61FFFFh | 308000h-30FFFFh |
| 33           | 64                 | 32                 | SA105  | 1100010xxx             | 620000h-62FFFFh | 310000h-317FFFh |
| 33           | 64                 | 32                 | SA106  | 1100011xxx             | 630000h-63FFFFh | 318000h-31FFFFh |
| 34           | 64                 | 32                 | SA107  | 1100100xxx             | 640000h-64FFFFh | 320000h-327FFFh |
| 34           | 64                 | 32                 | SA108  | 1100101xxx             | 650000h-65FFFFh | 328000h-32FFFFh |
| 34           | 64                 | 32                 | SA109  | 1100110xxx             | 660000h-66FFFFh | 330000h-337FFFh |
| 34           | 64                 | 32                 | SA110  | 1100111xxx             | 670000h-67FFFFh | 338000h-33FFFFh |
| 35           | 64                 | 32                 | SA111  | 1101000xxx             | 680000h-68FFFFh | 340000h-347FFFh |
| 35           | 64                 | 32                 | SA112  | 1101001xxx             | 690000h-69FFFFh | 348000h-34FFFFh |
| 35           | 64                 | 32                 | SA113  | 1101010xxx             | 6A0000h-6AFFFFh | 350000h-357FFFh |
| 35           | 64                 | 32                 | SA114  | 1101011xxx             | 6B0000h-6BFFFFh | 358000h-35FFFFh |
| 36           | 64                 | 32                 | SA115  | 1101100xxx             | 6C0000h-6CFFFFh | 360000h-367FFFh |
| 36           | 64                 | 32                 | SA116  | 1101101xxx             | 6D0000h-6DFFFFh | 368000h-36FFFFh |
| 36           | 64                 | 32                 | SA117  | 1101110xxx             | 6E0000h-6EFFFFh | 370000h-377FFFh |
| 36           | 64                 | 32                 | SA118  | 1101111xxx             | 6F0000h-6FFFFFh | 378000h-37FFFFh |

| Sector Group | Sector Size           |                       | Sector | Sector Address<br>A21-A12 | Address Range    |                  |
|--------------|-----------------------|-----------------------|--------|---------------------------|------------------|------------------|
|              | Byte Mode<br>(Kbytes) | Word Mode<br>(Kwords) |        |                           | Byte Mode (x8)   | Word Mode (x16)  |
| 37           | 64                    | 32                    | SA119  | 1110000xxx                | 700000h-70FFFFh  | 380000h-387FFFh  |
| 37           | 64                    | 32                    | SA120  | 1110001xxx                | 710000h-71FFFFh  | 388000h-38FFFFh  |
| 37           | 64                    | 32                    | SA121  | 1110010xxx                | 720000h-72FFFFh  | 390000h-397FFFh  |
| 37           | 64                    | 32                    | SA122  | 1110011xxx                | 730000h-73FFFFh  | 398000h-39FFFFh  |
| 38           | 64                    | 32                    | SA123  | 1110100xxx                | 740000h-74FFFFh  | 3A0000h-3A7FFFh  |
| 38           | 64                    | 32                    | SA124  | 1110101xxx                | 750000h-75FFFFh  | 3A8000h-3AFFFFh  |
| 38           | 64                    | 32                    | SA125  | 1110110xxx                | 760000h-76FFFFh  | 3B0000h-3B7FFFh  |
| 38           | 64                    | 32                    | SA126  | 1110111xxx                | 770000h-77FFFFh  | 3B8000h-3BFFFFh  |
| 39           | 64                    | 32                    | SA127  | 1111000xxx                | 780000h-78FFFFh  | 3C0000h-3C7FFFh  |
| 39           | 64                    | 32                    | SA128  | 1111001xxx                | 790000h-79FFFFh  | 3C8000h-3CFFFFh  |
| 39           | 64                    | 32                    | SA129  | 1111010xxx                | 7A0000h-7AFFFFh  | 3D0000h-3D7FFFh  |
| 39           | 64                    | 32                    | SA130  | 1111011xxx                | 7B0000h-7BFFFFh  | 3D8000h-3DFFFFh  |
| 40           | 64                    | 32                    | SA131  | 1111100xxx                | 7C0000h-7CFFFFh  | 3E0000h-3E7FFFh  |
| 40           | 64                    | 32                    | SA132  | 1111101xxx                | 7D0000h-7DFFFFh  | 3E8000h-3EFFFFh  |
| 40           | 64                    | 32                    | SA133  | 1111110xxx                | 7E0000h-7EFFFFh  | 3F0000h-3F7FFFh  |
| 40           | 64                    | 32                    | SA134  | 1111111xxx                | 7F0000h-7FFFFFFh | 3F8000h-3FFFFFFh |

## Bottom Boot Security Sector Addresses

| Sector Size          |                      | Sector Address<br>A21~A12 | Address Range   |                 |
|----------------------|----------------------|---------------------------|-----------------|-----------------|
| Byte Mode<br>(bytes) | Word Mode<br>(words) |                           | Byte Mode (x8)  | Word Mode (x16) |
| 256                  | 128                  | 0000000xxx                | 000000h-0000FFh | 000000h-00007Fh |

## BUS OPERATION

Table 2-1. BUS OPERATION

| Mode Select                      | RE-SET#  | CE#      | WE# | OE# | Address                             | Data (I/O)<br>Q7~Q0 | Byte#                    |        | WP#/ACC |
|----------------------------------|----------|----------|-----|-----|-------------------------------------|---------------------|--------------------------|--------|---------|
|                                  |          |          |     |     |                                     |                     | Vil                      | Vih    |         |
|                                  |          |          |     |     |                                     |                     | Data (I/O)               | Q15~Q8 |         |
| Device Reset                     | L        | X        | X   | X   | X                                   | HighZ               | HighZ                    | HighZ  | L/H     |
| Standby Mode                     | Vcc±0.3V | Vcc±0.3V | X   | X   | X                                   | HighZ               | HighZ                    | HighZ  | H       |
| Output Disable                   | H        | L        | H   | H   | X                                   | HighZ               | HighZ                    | HighZ  | L/H     |
| Read Mode                        | H        | L        | H   | L   | AIN                                 | DOUT                | Q8-Q14=HighZ,<br>Q15=A-1 | DOUT   | L/H     |
| Write(Note1)                     | H        | L        | L   | H   | AIN                                 | DIN                 |                          | DIN    | Note3   |
| Accelerate Program               | H        | L        | L   | H   | AIN                                 | DIN                 |                          | DIN    | Vhv     |
| Temporary Sector-Group Unprotect | Vhv      | X        | X   | X   | AIN                                 | DIN                 | HighZ                    | DIN    | Note3   |
| Sector-Group Protect (Note2)     | Vhv      | L        | L   | H   | Sector Address,<br>A6=L, A1=H, A0=L | DIN, DOUT           | X                        | X      | L/H     |
| Chip Unprotect (Note2)           | Vhv      | L        | L   | H   | Sector Address,<br>A6=H, A1=H, A0=L | DIN, DOUT           | X                        | X      | Note3   |

Notes:

1. All sectors will be unprotected if WP#/ACC=Vhv.
2. The two outmost boot sectors are protected if WP#/ACC=Vil.
3. When WP#/ACC = Vih, the protection conditions of the two outmost boot sectors depend on previous protection conditions."Sector/Sector Block Protection and Unprotection" describes the protect and unprotect method.
4. Q0~Q15 are input (DIN) or output (DOUT) pins according to the requests of command sequence, sector protection, or data polling algorithm.
5. In Word Mode (Byte#=Vih), the addresses are AM to A0.  
In Byte Mode (Byte#=Vil), the addresses are AM to A-1 (Q15).
6. AM: MSB of address.

**Table 2-2. BUS OPERATION**

| Item                                              | Control Input |     |     | AM<br>to<br>A12 | A11<br>to<br>A10 | A9              | A8<br>to<br>A7 | A6 | A5<br>to<br>A2 | A1 | A0 | Q7~Q0                 | Q15~Q8    |
|---------------------------------------------------|---------------|-----|-----|-----------------|------------------|-----------------|----------------|----|----------------|----|----|-----------------------|-----------|
|                                                   | CE#           | WE# | OE# |                 |                  |                 |                |    |                |    |    |                       |           |
| Sector Lock Status Verification                   | L             | H   | L   | SA              | x                | V <sub>hv</sub> | x              | L  | x              | H  | L  | 01h or 00h<br>(Note1) | x         |
| Read Silicon ID<br>Manufacturer Code              | L             | H   | L   | x               | x                | V <sub>hv</sub> | x              | L  | x              | L  | L  | C2h                   | x         |
| Read Silicon ID<br>MX29LV640ET                    | L             | H   | L   | x               | x                | V <sub>hv</sub> | x              | L  | x              | L  | H  | C9h                   | 22h(Word) |
|                                                   |               |     |     |                 |                  |                 |                |    |                |    |    |                       | XXh(Byte) |
| Read Silicon ID<br>MX29LV640EB                    | L             | H   | L   | x               | x                | V <sub>hv</sub> | x              | L  | x              | L  | H  | CBh                   | 22h(Word) |
|                                                   |               |     |     |                 |                  |                 |                |    |                |    |    |                       | XXh(Byte) |
| Read Indicator Bit<br>(Q7) For Security<br>Sector | L             | H   | L   | x               | x                | V <sub>hv</sub> | x              | L  | x              | H  | H  | (Note2)               | x         |

Notes:

1. Sector unprotected code:00h. Sector protected code:01h.
2. Factory locked code: 88h.  
Factory unlocked code: 08h.
3. AM: MSB of address.

## FUNCTIONAL OPERATION DESCRIPTION

### WRITE COMMANDS/COMMAND SEQUENCES

To write a command to the device, system must drive WE# and CE# to Vil, and OE# to Vih. In a command cycle, all address are latched at the later falling edge of CE# and WE#, and all data are latched at the earlier rising edge of CE# and WE#.

Figure 1 illustrates the AC timing waveform of a write command, and Table 3 defines all the valid command sets of the device. System is not allowed to write invalid commands not defined in this datasheet. Writing an invalid command will bring the device to an undefined state.

### REQUIREMENTS FOR READING ARRAY DATA

Read array action is to read the data stored in the array. While the memory device is in powered up or has been reset, it will automatically enter the status of read array. If the microprocessor wants to read the data stored in the array, it has to drive CE# (device enable control pin) and OE# (Output control pin) as Vil, and input the address of the data to be read into address pin at the same time. After a period of read cycle (Tce or Taa), the data being read out will be displayed on output pin for microprocessor to access. If CE# or OE# is Vih, the output will be in tri-state, and there will be no data displayed on output pin at all.

After the memory device completes embedded operation (automatic Erase or Program), it will automatically return to the status of read array, and the device can read the data in any address in the array. In the process of erasing, if the device receives the Erase suspend command, erase operation will be stopped temporarily after a period of time no more than Tready and the device will return to the status of read array. At this time, the device can read the data stored in any address except the sector being erased in the array. In the status of erase suspend, if user wants to read the data in the sectors being erased, the device will output status data onto the output. Similarly, if program command is issued after erase suspend, after program operation is completed, system can still read array data in any address except the sectors to be erased.

The device needs to issue reset command to enable read array operation again in order to arbitrarily read the data in the array in the following two situations:

1. In program or erase operation, the programming or erasing failure causes Q5 to go high.
2. The device is in auto select mode or CFI mode.

In the two situations above, if reset command is not issued, the device is not in read array mode and system must issue reset command before reading array data.

### ACCELERATED PROGRAM OPERATION

The accelerated program can improve programming performance compared with word/byte program. By applying Vhv on WP#/ACC pin, the device will enter accelerated program and draw current no more than Icp1 from WP#/ACC pin. Removing the Vhv from WP#/ACC pin will put the device back to normal operation (not accelerated).

## RESET# OPERATION

Driving RESET# pin low for a period more than  $T_{rp}$  will reset the device back to read mode. If the device is in program or erase operation, the reset operation will take at most a period of  $T_{ready}$  for the device to return to read array mode. Before the device returns to read array mode, the RY/BY# pin remains low (busy status).

When RESET# pin is held at  $GND \pm 0.3V$ , the device consumes standby current ( $I_{sb}$ ). However, device draws larger current if RESET# pin is held at  $V_{il}$  but not within  $GND \pm 0.3V$ .

It is recommended that the system to tie its reset signal to RESET# pin of flash memory, so that the flash memory will be reset during system reset and allows system to read boot code from flash memory.

## SECTOR GROUP PROTECT OPERATION

When a sector group is protected, program or erase operation will be disabled on these sectors. MX29LV640E T/B provides two methods for sector group protection.

Once the sector group is protected, the sector group remains protected until next chip unprotect, or is temporarily unprotected by asserting RESET# pin at  $V_{hv}$ . Refer to temporary sector group unprotect operation for further details.

The first method is by applying  $V_{hv}$  on RESET# pin. Refer to Figure 13 for timing diagram and Figure 14 for the algorithm for this method.

The other method is asserting  $V_{hv}$  on A9 and OE# pins, with A6 and CE# at  $V_{il}$ . The protection operation begins at the falling edge of WE# and terminates at the rising edge. Contact Macronix for details.

## CHIP UNPROTECT OPERATION

MX29LV640E T/B provides two methods for chip unprotect. The chip unprotect operation unprotects all sectors within the device. It is recommended to protect all sectors before activating chip unprotect mode. All sectors groups are unprotected when shipped from the factory.

The first method is by applying  $V_{hv}$  on RESET# pin. Refer to Figure 13 for timing diagram and Figure 14 for algorithm of the operation.

The other method is asserting  $V_{hv}$  on A9 and OE# pins, with A6 at  $V_{ih}$  and CE# at  $V_{il}$ . The unprotect operation begins at the falling edge of WE# and terminates at the rising edge. Contact Macronix for details.

## TEMPORARY SECTOR GROUP UNPROTECT OPERATION

System can apply RESET# pin at  $V_{hv}$  to place the device in temporary unprotect mode. In this mode, previously protected sectors can be programmed or erased just as it is unprotected. The device returns to normal operation once  $V_{hv}$  is removed from RESET# pin and previously protected sectors are again protected.

**WRITE PROTECT (WP#)**

Another function of the WP#/ACC pin is to provide write protection function on the two outermost 8 Kbyte boot sectors. When  $V_{IL}$  is asserted on WP#/ACC pin, the two boot sectors are protected regardless of the previous state of protection implemented by aforementioned Sector Group Protect/Chip Unprotect. For MX29LV640ET, the two outermost sectors are the two boot sectors of the highest addresses. For MX29LV640EB, the two outermost sectors are the two boot sectors of the lowest addresses.

**AUTOMATIC SELECT OPERATION**

When the device is in Read array mode, erase-suspended read array mode or CFI mode, user can issue read silicon ID command to enter read silicon ID mode. After entering read silicon ID mode, user can query several silicon IDs continuously and does not need to issue read silicon ID mode again. When A0 is Low, device will output Macronix Manufacture ID C2H. When A0 is high, device will output Device ID. In read silicon ID mode, issuing reset command will reset device back to read array mode or erase-suspended read array mode.

Another way to enter read silicon ID is to apply high voltage on A9 pin with CE#, OE#, A6 and A1 at  $V_{IL}$ . While the high voltage of A9 pin is discharged, device will automatically leave read silicon ID mode and go back to read array mode or erase-suspended read array mode. When A0 is Low, device will output Macronix Manufacture ID C2. When A0 is high, device will output Device ID.

**VERIFY SECTOR GROUP PROTECT STATUS OPERATION**

MX29LV640E T/B provides hardware sector protection against Program and Erase operation for protected sectors. The sector protect status can be read through Sector Protect Verify command. This method requires  $V_{HV}$  on A9 pin,  $V_{IH}$  on WE# and A1 pins,  $V_{IL}$  on CE#, OE#, A6 and A0 pins, and sector address on A12 to A21 pins. If the read out data is 01H, the designated sector is protected. Oppositely, if the read out data is 00H, the designated sector is not protected.

**SECURITY SECTOR FLASH MEMORY REGION**

The Security Sector region is an extra OTP memory space of 128 words in length. The security sectors can be locked upon shipping from factory, or it can be locked by customer after shipping. Customer can issue Security Sector Factory Protect Verify and/or Security Sector Protect Verify to query the lock status of the device.

In factory-locked device, security sector region is protected when shipped from factory and the security silicon sector indicator bit is set to "1". In customer lockable device, security sector region is unprotected when shipped from factory and the security silicon indicator bit is set to "0".

**Factory Locked: Security Sector Programmed and Protected at the Factory**

In a factory locked device, the security silicon region is permanently locked after shipping from factory. The device will have a 16-byte (8-word) ESN in the security region. In bottom boot device : 000000h - 000007h (for MX29LV640EB). In Top boot device : 3FFF70h - 3FFF77h (for MX29LV640ET).

### **Customer Lockable: Security Sector NOT Programmed or Protected at the Factory**

When the security feature is not required, the security region can act as an extra memory space.

Security silicon sector can also be protected by two methods. Note that once the security silicon sector is protected, there is no way to unprotect the security silicon sector and the content of it can no longer be altered.

The first method is to write a three-cycle command of Enter Security Region, and then follow the sector group protect algorithm as illustrated in Figure 14, except that RESET# pin may at either Vih or Vhv.

The other method is to write a three-cycle command of Enter Security Region, and then follow the alternate method of sector protect with A9, OE# at Vhv.

After the security silicon is locked and verified, system must write Exit Security Sector Region, go through a power cycle, or issue a hardware reset to return the device to read normal array mode.

### **DATA PROTECTION**

To avoid accidental erasure or programming of the device, the device is automatically reset to read array mode during power up. Besides, only after successful completion of the specified command sets will the device begin its erase or program operation.

Other features to protect the data from accidental alternation are described as followed.

### **LOW VCC WRITE INHIBIT**

The device refuses to accept any write command when Vcc is less than V<sub>lko</sub>. This prevents data from spuriously altered. The device automatically resets itself when Vcc is lower than V<sub>lko</sub> and write cycles are ignored until Vcc is greater than V<sub>lko</sub>. System must provide proper signals on control pins after Vcc is larger than V<sub>lko</sub> to avoid unintentional program or erase operation

### **WRITE PULSE "GLITCH" PROTECTION**

CE#, WE#, OE# pulses shorter than 5ns are treated as glitches and will not be regarded as an effective write cycle.

### **LOGICAL INHIBIT**

A valid write cycle requires both CE# and WE# at Vil with OE# at Vih. Write cycle is ignored when either CE# at Vih, WE# a Vih, or OE# at Vil.

### **POWER-UP SEQUENCE**

Upon power up, MX29LV640E T/B is placed in read array mode. Furthermore, program or erase operation will begin only after successful completion of specified command sequences.



MACRONIX  
INTERNATIONAL Co., LTD.

**MX29LV640E T/B**

---

#### **POWER-UP WRITE INHIBIT**

When WE#, CE# is held at Vil and OE# is held at Vih during power up, the device ignores the first command on the rising edge of WE#.

#### **POWER SUPPLY DECOUPLING**

A 0.1uF capacitor should be connected between the Vcc and GND to reduce the noise effect.

## COMMAND OPERATIONS

**TABLE 3. MX29LV640E T/B COMMAND DEFINITIONS**

| Command       |      | Read Mode | Reset Mode | Automatic Select |      |           |      |                |       |                       |              | Enter Security Sector Region Enable |      |
|---------------|------|-----------|------------|------------------|------|-----------|------|----------------|-------|-----------------------|--------------|-------------------------------------|------|
|               |      |           |            | Manufacture ID   |      | Device ID |      | Sector Factory |       | Sector Protect Verify |              |                                     |      |
|               |      |           |            | Word             | Byte | Word      | Byte | Word           | Byte  | Word                  | Byte         | Word                                | Byte |
| 1st Bus Cycle | Addr | Addr      | XXX        | 555              | AAA  | 555       | AAA  | 555            | AAA   | 555                   | AAA          | 555                                 | AAA  |
|               | Data | Data      | F0         | AA               | AA   | AA        | AA   | AA             | AA    | AA                    | AA           | AA                                  | AA   |
| 2nd Bus Cycle | Addr |           |            | 2AA              | 555  | 2AA       | 555  | 2AA            | 555   | 2AA                   | 555          | 2AA                                 | 555  |
|               | Data |           |            | 55               | 55   | 55        | 55   | 55             | 55    | 55                    | 55           | 55                                  | 55   |
| 3rd Bus Cycle | Addr |           |            | 555              | AAA  | 555       | AAA  | 555            | AAA   | 555                   | AAA          | 555                                 | AAA  |
|               | Data |           |            | 90               | 90   | 90        | 90   | 90             | 90    | 90                    | 90           | 88                                  | 88   |
| 4th Bus Cycle | Addr |           |            | X00              | X00  | X01       | X02  | X03            | X06   | (Sector) X02          | (Sector) X04 |                                     |      |
|               | Data |           |            | C2h              | C2h  | ID        | ID   | 88/08          | 88/08 | 00/01                 | 00/01        |                                     |      |
| 5th Bus Cycle | Addr |           |            |                  |      |           |      |                |       |                       |              |                                     |      |
|               | Data |           |            |                  |      |           |      |                |       |                       |              |                                     |      |
| 6th Bus Cycle | Addr |           |            |                  |      |           |      |                |       |                       |              |                                     |      |
|               | Data |           |            |                  |      |           |      |                |       |                       |              |                                     |      |

| Command       |      | Exit Security Sector |      | Program |      | Chip Erase |      | Sector Erase |        | CFI Read |      | Erase Suspend | Erase Resume |
|---------------|------|----------------------|------|---------|------|------------|------|--------------|--------|----------|------|---------------|--------------|
|               |      | Word                 | Byte | Word    | Byte | Word       | Byte | Word         | Byte   | Word     | Byte | Byte/Word     | Byte/Word    |
| 1st Bus Cycle | Addr | 555                  | AAA  | 555     | AAA  | 555        | AAA  | 555          | AAA    | 55       | AA   | XXX           | XXX          |
|               | Data | AA                   | AA   | AA      | AA   | AA         | AA   | AA           | AA     | 98       | 98   | B0            | 30           |
| 2nd Bus Cycle | Addr | 2AA                  | 555  | 2AA     | 555  | 2AA        | 555  | 2AA          | 555    |          |      |               |              |
|               | Data | 55                   | 55   | 55      | 55   | 55         | 55   | 55           | 55     |          |      |               |              |
| 3rd Bus Cycle | Addr | 555                  | AAA  | 555     | AAA  | 555        | AAA  | 555          | AAA    |          |      |               |              |
|               | Data | 90                   | 90   | A0      | A0   | 80         | 80   | 80           | 80     |          |      |               |              |
| 4th Bus Cycle | Addr | XXX                  | XXX  | Addr    | Addr | 555        | AAA  | 555          | AAA    |          |      |               |              |
|               | Data | 00                   | 00   | Data    | Data | AA         | AA   | AA           | AA     |          |      |               |              |
| 5th Bus Cycle | Addr |                      |      |         |      | 2AA        | 555  | 2AA          | 555    |          |      |               |              |
|               | Data |                      |      |         |      | 55         | 55   | 55           | 55     |          |      |               |              |
| 6th Bus Cycle | Addr |                      |      |         |      | 555        | AAA  | Sector       | Sector |          |      |               |              |
|               | Data |                      |      |         |      | 10         | 10   | 30           | 30     |          |      |               |              |

## RESET

In the following situations, executing reset command will reset device back to read array mode:

- Among erase command sequence (before the full command set is completed)
- Sector erase time-out period
- Erase fail (while Q5 is high)
- Among program command sequence (before the full command set is completed, erase-suspended program included)
- Program fail (while Q5 is high, and erase-suspended program fail is included)
- Read silicon ID mode
- Sector protect verify
- CFI mode

While device is at the status of program fail or erase fail (Q5 is high), user must issue reset command to reset device back to read array mode. While the device is in read silicon ID mode, sector protect verify or CFI mode, user must issue reset command to reset device back to read array mode.

When the device is in the progress of programming (not program fail) or erasing (not erase fail), device will ignore reset command.

## AUTOMATIC SELECT COMMAND SEQUENCE

Automatic Select mode is used to access the manufacturer ID, device ID and to verify whether or not secured silicon is locked and whether or not a sector is protected. The automatic select mode has four command cycles. The first two are unlock cycles, and followed by a specific command. The fourth cycle is a normal read cycle, and user can read at any address any number of times without entering another command sequence. The reset command is necessary to exit the Automatic Select mode and back to read array. The following table shows the identification code with corresponding address.

|                       |      | Address               | Data (Hex) | Representation          |
|-----------------------|------|-----------------------|------------|-------------------------|
| Manufacturer ID       | Word | X00                   | C2         |                         |
|                       | Byte | X00                   | C2         |                         |
| Device ID             | Word | X01                   | 22C9/22CB  | Top/Bottom Boot Sector  |
|                       | Byte | X02                   | C9/CB      | Top/Bottom Boot Sector  |
| Secured Silicon       | Word | X03                   | 88/08      | Factory locked/unlocked |
|                       | Byte | X06                   | 88/08      | Factory locked/unlocked |
| Sector Protect Verify | Word | (Sector address) X 02 | 00/01      | Unprotected/protected   |
|                       | Byte | (Sector address) X 04 | 00/01      | Unprotected/protected   |

There is an alternative method to that shown in Table 2, which is intended for EPROM programmers and requires V<sub>h</sub> on address bit A9.

## **AUTOMATIC PROGRAMMING**

The MX29LV640E T/B can provide the user program function by the form of Byte-Mode or Word-Mode. As long as the users enter the right cycle defined in the Table.3 (including 2 unlock cycles and A0H), any data user inputs will automatically be programmed into the array.

Once the program function is executed, the internal write state controller will automatically execute the algorithms and timings necessary for program and verification, which includes generating suitable program pulse, verifying whether the threshold voltage of the programmed cell is high enough and repeating the program pulse if any of the cells does not pass verification. Meanwhile, the internal control will prohibit the programming to cells that pass verification while the other cells fail in verification in order to avoid over-programming. With the internal write state controller, the device requires the user to write the program command and data only.

Programming will only change the bit status from "1" to "0". That is to say, it is impossible to convert the bit status from "0" to "1" by programming. Meanwhile, the internal write verification only detects the errors of the "1" that is not successfully programmed to "0".

Any command written to the device during programming will be ignored except hardware reset, which will terminate the program operation after a period of time no more than Tready. When the embedded program algorithm is complete or the program operation is terminated by hardware reset, the device will return to the reading array data mode.

The typical chip program time at room temperature of the MX29LV640E T/B is less than 45 seconds.

When the embedded program operation is on going, user can confirm if the embedded operation is finished or not by the following methods:

| <b>Status</b>     | <b>Q7</b> | <b>Q6</b>     | <b>Q5</b> | <b>RY/BY#*2</b> |
|-------------------|-----------|---------------|-----------|-----------------|
| In progress*1     | Q7#       | Toggling      | 0         | 0               |
| Finished          | Q7        | Stop toggling | 0         | 1               |
| Exceed time limit | Q7#       | Toggling      | 1         | 0               |

\*1: The status "in progress" means both program mode and erase-suspended program mode.

\*2: RY/BY# is an open drain output pin and should be weakly connected to VDD through a pull-up resistor.

\*3: When an attempt is made to program a protected sector, Q7 will output its complement data or Q6 continues to toggle for about 1us or less and the device returns to read array state without programing the data in the protected sector.

**CHIP ERASE**

Chip Erase is to erase all the data with "1" and "0" as all "1". It needs 6 cycles to write the action in, and the first two cycles are "unlock" cycles, the third one is a configuration cycle, the fourth and fifth are also "unlock" cycles, and the sixth cycle is the chip erase operation.

During chip erasing, all the commands will not be accepted except hardware reset or the working voltage is too low that chip erase will be interrupted. After Chip Erase, the chip will return to the state of Read Array.

When the embedded chip erase operation is on going, user can confirm if the embedded operation is finished or not by the following methods:

| Status            | Q7 | Q6            | Q5 | Q2       | RY/BY# |
|-------------------|----|---------------|----|----------|--------|
| In progress       | 0  | Toggling      | 0  | Toggling | 0      |
| Finished          | 1  | Stop toggling | 0  | 1        | 1      |
| Exceed time limit | 0  | Toggling      | 1  | Toggling | 0      |

**SECTOR ERASE**

Sector Erase is to erase all the data in a sector with "1" and "0" as all "1". It requires six command cycles to issue. The first two cycles are "unlock cycles", the third one is a configuration cycle, the fourth and fifth are also "unlock cycles" and the sixth cycle is the sector erase command. After the sector erase command sequence is issued, there is a time-out period of 50us counted internally. During the time-out period, additional sector address and sector erase command can be written multiply. Once user enters another sector erase command, the time-out period of 50us is recounted. If user enters any command other than sector erase or erase suspend during time-out period, the erase command would be aborted and the device is reset to read array condition. The number of sectors could be from one sector to all sectors. After time-out period passing by, additional erase command is not accepted and erase embedded operation begins.

During sector erasing, all commands will not be accepted except hardware reset and erase suspend and user can check the status as chip erase.

When the embedded erase operation is on going, user can confirm if the embedded operation is finished or not by the following methods:

| Status            | Q7 | Q6            | Q5 | Q3 | Q2       | RY/BY#*2 |
|-------------------|----|---------------|----|----|----------|----------|
| Time-out period   | 0  | Toggling      | 0  | 0  | Toggling | 0        |
| In progress       | 0  | Toggling      | 0  | 1  | Toggling | 0        |
| Finished          | 1  | Stop toggling | 0  | 1  | 1        | 1        |
| Exceed time limit | 0  | Toggling      | 1  | 1  | Toggling | 0        |

**Note :**

1. The status Q3 is the time-out period indicator. When Q3=0, the device is in time-out period and is acceptable to another sector address to be erased. When Q3=1, the device is in erase operation and only erase suspend is valid.

2. RY/BY# is open drain output pin and should be weakly connected to VDD through a pull-up resistor.
3. When an attempt is made to erase a protected sector, Q7 will output its complement data or Q6 continues to toggle for 100us or less and the device returned to read array status without erasing the data in the protected sector.
4. Q2 is a localized indicator showing a specified sector is undergoing erase operation or not. Q2 toggles when user reads at addresses where the sectors are actively being erased (in erase mode) or to be erased (in erase suspend mode). When a sector has been completely erased, Q2 stops toggling at the sector even when the device is still in erase operation for remaining selected sectors. At that circumstance, Q2 will still toggle when device is read at any other sector that remains to be erased.

## SECTOR ERASE SUSPEND

During sector erasure, sector erase suspend is the only valid command. If user issue erase suspend command in the time-out period of sector erasure, device time-out period will be over immediately and the device will go back to erase-suspended read array mode. If user issue erase suspend command during the sector erase is being operated, device will suspend the ongoing erase operation, and after the Tready1 ( $\leq 20\mu s$ ) suspend finishes and the device will enter erase-suspended read array mode. User can judge if the device has finished erase suspend through Q6, Q7, and RY/BY#.

After device has entered erase-suspended read array mode, user can read other sectors not at erase suspend by the speed of Taa; while reading the sector in erase-suspend mode, device will output its status. Whenever a suspend command is issued, user must issue a resume command and check Q6 toggle bit status, before issue another erase command. The system can use the status register bits shown in the following table to determine the current state of the device:

| Status                                              | Q7   | Q6        | Q5   | Q3   | Q2     | RY/BY# |
|-----------------------------------------------------|------|-----------|------|------|--------|--------|
| Erase suspend read in erase suspended sector        | 1    | No toggle | 0    | N/A  | Toggle | 1      |
| Erase suspend read in non-erase suspended sector    | Data | Data      | Data | Data | Data   | 1      |
| Erase suspend program in non-erase suspended sector | Q7#  | Toggle    | 0    | N/A  | N/A    | 0      |

When the device has suspended erasing, user can execute the command sets except sector erase and chip erase, such as read silicon ID, sector protect verify, program, CFI query and erase resume.

## SECTOR ERASE RESUME

Sector erase resume command is valid only when the device is in erase suspend state. After erase resume, user can issue another erase suspend command, but there should be a 4ms interval between erase resume and the next erase suspend. If user issue infinite suspend-resume loop, or suspend-resume exceeds 1024 times, the time for erasing will increase.

**COMMON FLASH MEMORY INTERFACE (CFI) MODE****QUERY COMMAND AND COMMON FLASH INTERFACE (CFI) MODE**

MX29LV640E T/B features CFI mode. Host system can retrieve the operating characteristics, structure and vendor-specified information such as identifying information, memory size, byte/word configuration, operating voltages and timing information of this device by CFI mode. The device enters the CFI Query mode when the system writes the CFI Query command, 98H, to address 55H/AAH (depending on Word/Byte mode) any time the device is ready to read array data. The system can read CFI information at the addresses given in Table 4. A reset command is required to exit CFI mode and go back to ready array mode or erase suspend mode. The system can write the CFI Query command only when the device is in read mode, erase suspend, standby mode or automatic select mode. The CFI unused area is Macronix's reserved.

**Table 4-1. CFI mode: Identification Data Values**

(All values in these tables are in hexadecimal)

| Description                                                | Address (h)<br>(Word Mode) | Address (h)<br>(Byte Mode) | Data (h) |
|------------------------------------------------------------|----------------------------|----------------------------|----------|
| Query-unique ASCII string "QRY"                            | 10                         | 20                         | 0051     |
|                                                            | 11                         | 22                         | 0052     |
|                                                            | 12                         | 24                         | 0059     |
| Primary vendor command set and control interface ID code   | 13                         | 26                         | 0002     |
|                                                            | 14                         | 28                         | 0000     |
| Address for primary algorithm extended query table         | 15                         | 2A                         | 0040     |
|                                                            | 16                         | 2C                         | 0000     |
| Alternate vendor command set and control interface ID code | 17                         | 2E                         | 0000     |
|                                                            | 18                         | 30                         | 0000     |
| Address for alternate algorithm extended query table       | 19                         | 32                         | 0000     |
|                                                            | 1A                         | 34                         | 0000     |

**Table 4-2. CFI Mode: System Interface Data Values**

| Description                                                              | Address (h)<br>(Word Mode) | Address (h)<br>(Byte Mode) | Data (h) |
|--------------------------------------------------------------------------|----------------------------|----------------------------|----------|
| Vcc supply minimum program/erase voltage                                 | 1B                         | 36                         | 0027     |
| Vcc supply maximum program/erase voltage                                 | 1C                         | 38                         | 0036     |
| VPP supply minimum program/erase voltage                                 | 1D                         | 3A                         | 0000     |
| VPP supply maximum program/erase voltage                                 | 1E                         | 3C                         | 0000     |
| Typical timeout per single word/byte write, 2 <sup>n</sup> us            | 1F                         | 3E                         | 0004     |
| Typical timeout for maximum-size buffer write, 2 <sup>n</sup> us         | 20                         | 40                         | 0000     |
| Typical timeout per individual block erase, 2 <sup>n</sup> ms            | 21                         | 42                         | 000A     |
| Typical timeout for full chip erase, 2 <sup>n</sup> ms                   | 22                         | 44                         | 0000     |
| Maximum timeout for word/byte write, 2 <sup>n</sup> times typical        | 23                         | 46                         | 0005     |
| Maximum timeout for buffer write, 2 <sup>n</sup> times typical           | 24                         | 48                         | 0000     |
| Maximum timeout per individual block erase, 2 <sup>n</sup> times typical | 25                         | 4A                         | 0004     |
| Maximum timeout for chip erase, 2 <sup>n</sup> times typical             | 26                         | 4C                         | 0000     |

**Table 4-3. CFI Mode: Device Geometry Data Values**

| Description                                                                                                                                                                | Address (h)<br>(Word Mode) | Address (h)<br>(Byte Mode) | Data (h) |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------|----------------------------|----------|
| Device size = 2 <sup>n</sup> in number of bytes                                                                                                                            | 27                         | 4E                         | 0017     |
| Flash device interface description (02=asynchronous x8/x16)                                                                                                                | 28                         | 50                         | 0002     |
|                                                                                                                                                                            | 29                         | 52                         | 0000     |
| Maximum number of bytes in buffer write = 2 <sup>n</sup> (not support)                                                                                                     | 2A                         | 54                         | 0000     |
|                                                                                                                                                                            | 2B                         | 56                         | 0000     |
| Number of erase regions within device<br>Index for Erase Bank Area 1<br>[2E,2D] = # of same-size sectors in region 1-1<br>[30, 2F] = sector size in multiples of 256-bytes | 2C                         | 58                         | 0002     |
|                                                                                                                                                                            | 2D                         | 5A                         | 0007     |
|                                                                                                                                                                            | 2E                         | 5C                         | 0000     |
|                                                                                                                                                                            | 2F                         | 5E                         | 0020     |
|                                                                                                                                                                            | 30                         | 60                         | 0000     |
|                                                                                                                                                                            | 31                         | 62                         | 007E     |
| Index for Erase Bank Area 2                                                                                                                                                | 32                         | 64                         | 0000     |
|                                                                                                                                                                            | 33                         | 66                         | 0000     |
|                                                                                                                                                                            | 34                         | 68                         | 0001     |
|                                                                                                                                                                            | 35                         | 6A                         | 0000     |
| Index for Erase Bank Area 3                                                                                                                                                | 36                         | 6C                         | 0000     |
|                                                                                                                                                                            | 37                         | 6E                         | 0000     |
|                                                                                                                                                                            | 38                         | 70                         | 0000     |
|                                                                                                                                                                            | 39                         | 72                         | 0000     |
| Index for Erase Bank Area 4                                                                                                                                                | 3A                         | 74                         | 0000     |
|                                                                                                                                                                            | 3B                         | 76                         | 0000     |
|                                                                                                                                                                            | 3C                         | 78                         | 0000     |
|                                                                                                                                                                            |                            |                            |          |

**Table 4-4. CFI Mode: Primary Vendor-Specific Extended Query Data Values**

| Description                                                                               | Address (h)<br>(Word Mode) | Address (h)<br>(Byte Mode) | Data (h)  |
|-------------------------------------------------------------------------------------------|----------------------------|----------------------------|-----------|
| Query - Primary extended table, unique ASCII string, PRI                                  | 40                         | 80                         | 0050      |
|                                                                                           | 41                         | 82                         | 0052      |
|                                                                                           | 42                         | 84                         | 0049      |
| Major version number, ASCII                                                               | 43                         | 86                         | 0031      |
| Minor version number, ASCII                                                               | 44                         | 88                         | 0031      |
| Unlock recognizes address (0= recognize, 1= don't recognize)                              | 45                         | 8A                         | 0000      |
| Erase suspend (2= to both read and program)                                               | 46                         | 8C                         | 0002      |
| Sector protect (N= # of sectors/group)                                                    | 47                         | 8E                         | 0004      |
| Temporary sector unprotect (1=supported)                                                  | 48                         | 90                         | 0001      |
| Sector protect/Chip unprotect scheme                                                      | 49                         | 92                         | 0004      |
| Simultaneous R/W operation (0=not supported)                                              | 4A                         | 94                         | 0000      |
| Burst mode (0=not supported)                                                              | 4B                         | 96                         | 0000      |
| Page mode (0=not supported)                                                               | 4C                         | 98                         | 0000      |
| Minimum ACC (acceleration) supply (0= not supported), [D7:D4] for volt, [D3:D0] for 100mV | 4D                         | 9A                         | 0095      |
| Maximum ACC (acceleration) supply (0= not supported), [D7:D4] for volt, [D3:D0] for 100mV | 4E                         | 9C                         | 00A5      |
| Top/Bottom boot block indicator<br>02h=bottom boot device 03h=top boot device             | 4F                         | 9E                         | 0002/0003 |

**ELECTRICAL CHARACTERISTICS****ABSOLUTE MAXIMUM STRESS RATINGS**

|                                                     |                    |                    |
|-----------------------------------------------------|--------------------|--------------------|
| Surrounding Temperature with Bias                   |                    | -65°C to +125°C    |
| Storage Temperature                                 |                    | -65°C to +150°C    |
| Voltage Range                                       | VCC                | -0.5V to +4.0 V    |
|                                                     | RESET#, A9 and OE# | -0.5V to +10.5 V   |
|                                                     | The other pins     | -0.5V to Vcc +0.5V |
| Output Short Circuit Current (less than one second) |                    | 200 mA             |

Note:

1. Minimum voltage may undershoot to -2V during transition and for less than 20ns during transitions.
2. Maximum voltage may overshoot to Vcc+2V during transition and for less than 20ns during transitions.


**OPERATING TEMPERATURE AND VOLTAGE**

|                             |                                           |                 |
|-----------------------------|-------------------------------------------|-----------------|
| <b>Industrial (I) Grade</b> | Surrounding Temperature (T <sub>A</sub> ) | -40°C to +85°C  |
| <b>VCC Supply Voltages</b>  | VCC range                                 | +2.7 V to 3.6 V |

**DC CHARACTERISTICS**


| Symbol            | Description                                                                                          | Min.     | Typ. | Max.     | Remark                                       |
|-------------------|------------------------------------------------------------------------------------------------------|----------|------|----------|----------------------------------------------|
| I <sub>ilk</sub>  | Input Leak                                                                                           |          |      | ± 1.0uA  |                                              |
| I <sub>ilk9</sub> | A9 Leak                                                                                              |          |      | 35uA     | A9=10.5V                                     |
| I <sub>olk</sub>  | Output Leak                                                                                          |          |      | ± 1.0uA  |                                              |
| I <sub>cr1</sub>  | Read Current(5MHz)                                                                                   |          | 9mA  | 16mA     | CE#=Vil, OE#=Vih                             |
| I <sub>cr2</sub>  | Read Current(1MHz)                                                                                   |          | 2mA  | 4mA      | CE#=Vil, OE#=Vih                             |
| I <sub>cw</sub>   | Write Current                                                                                        |          | 26mA | 30mA     | CE#=Vil, OE#=Vih, WE#=Vil                    |
| I <sub>sb</sub>   | Standby Current                                                                                      |          | 5uA  | 15uA     | Vcc=Vcc max, other pin disable               |
| I <sub>sbr</sub>  | Reset Current                                                                                        |          | 5uA  | 15uA     | Vcc=Vccmax, Reset# enable, other pin disable |
| I <sub>cp1</sub>  | Accelerated Pgm Current, WP#/ACC pin (Word/Byte)                                                     |          | 5mA  | 10mA     | CE#=Vil, OE#=Vih                             |
| I <sub>cp2</sub>  | Accelerated Pgm Current, Vcc pin (Word/Byte)                                                         |          | 15mA | 30mA     | CE#=Vil, OE#=Vih                             |
| V <sub>il</sub>   | Input Low Voltage                                                                                    | -0.5V    |      | 0.8V     |                                              |
| V <sub>ih</sub>   | Input High Voltage                                                                                   | 0.7xVcc  |      | Vcc+0.3V |                                              |
| V <sub>hv</sub>   | Very High Voltage for hardware Protect/Unprotect/Auto Select/Temporary Unprotect/Accelerated Program | 9.5V     |      | 10.5V    |                                              |
| V <sub>ol</sub>   | Output Low Voltage                                                                                   |          |      | 0.45V    | I <sub>ol</sub> =4.0mA                       |
| V <sub>oh1</sub>  | Output High Voltage                                                                                  | 0.85xVcc |      |          | I <sub>oh1</sub> =-2mA                       |
| V <sub>oh2</sub>  | Output High Voltage                                                                                  | Vcc-0.4V |      |          | I <sub>oh2</sub> =-100uA                     |
| V <sub>lko</sub>  | Low Vcc Lock-out Voltage                                                                             | 2.3V     |      | 2.5V     |                                              |

## SWITCHING TEST CIRCUITS



Test Condition  
Output Load : 1 TTL gate  
Output Load Capacitance, CL : 30pF  
Rise/Fall Times : 5ns  
In/Out reference levels :1.5V

## SWITCHING TEST WAVEFORMS




## AC CHARACTERISTICS

| Symbol | Description                                                         | Min.                   | Typ. | Max. | Unit |
|--------|---------------------------------------------------------------------|------------------------|------|------|------|
| Taa    | Valid data output after address                                     |                        |      | 70   | ns   |
| Tce    | Valid data output after CE# low                                     |                        |      | 70   | ns   |
| Toe    | Valid data output after OE# low                                     |                        |      | 30   | ns   |
| Tdf    | Data output floating after OE# high or CE# high (*Note 1)           |                        |      | 16   | ns   |
| Toh    | Output hold time from the earliest rising edge of address, CE#, OE# | 0                      |      |      | ns   |
| Trc    | Read period time                                                    | 70                     |      |      | ns   |
| Tsrw   | Latency Between Read and Write operation (*Note 1)                  | 45                     |      |      | ns   |
| Twc    | Write period time                                                   | 70                     |      |      | ns   |
| Tcwc   | Command write period time                                           | 70                     |      |      | ns   |
| Tas    | Address setup time                                                  | 0                      |      |      | ns   |
| Tah    | Address hold time                                                   | 45                     |      |      | ns   |
| Tds    | Data setup time                                                     | 45                     |      |      | ns   |
| Tdh    | Data hold time                                                      | 0                      |      |      | ns   |
| Tvcs   | Vcc setup time                                                      | 200                    |      |      | us   |
| Tcs    | Chip enable Setup time                                              | 0                      |      |      | ns   |
| Tch    | Chip enable hold time                                               | 0                      |      |      | ns   |
| Toes   | Output enable setup time                                            | 0                      |      |      | ns   |
| Toeh   | Output enable hold time                                             | Read                   | 0    |      | ns   |
|        |                                                                     | Toggle & Data# Polling | 10   |      | ns   |
| Tws    | WE# setup time                                                      | 0                      |      |      | ns   |
| Twh    | WE# hold time                                                       | 0                      |      |      | ns   |
| Tcep   | CE# pulse width                                                     | 35                     |      |      | ns   |
| Tceph  | CE# pulse width high                                                | 30                     |      |      | ns   |
| Twp    | WE# pulse width                                                     | 35                     |      |      | ns   |
| Twph   | WE# pulse width high                                                | 30                     |      |      | ns   |
| Tbusy  | Program/Erase active time by RY/BY#                                 |                        |      | 70   | ns   |
| Tghwl  | Read recover time before write                                      | 0                      |      |      | ns   |
| Tghel  | Read recover time before write                                      | 0                      |      |      | ns   |
| Twhwh1 | Program operation                                                   | Byte                   | 9    |      | us   |
| Twhwh1 | Program operation                                                   | Word                   | 11   |      | us   |
| Twhwh1 | Acc Program operation(Word/Byte)                                    |                        | 7    |      | us   |
| Twhwh2 | Sector Erase Operation                                              |                        | 0.7  |      | sec  |
| Tbal   | Sector Add hold time                                                |                        |      | 50   | us   |

\* Note 1: Sampled only, not 100% tested.


## WRITE COMMAND OPERATION

Figure 1. COMMAND WRITE OPERATION



## READ/RESET OPERATION


**Figure 2. READ TIMING WAVEFORMS**



## AC CHARACTERISTICS


| Item    | Description                                                       | Setup | Speed | Unit |
|---------|-------------------------------------------------------------------|-------|-------|------|
| Trp1    | RESET# Pulse Width (During Automatic Algorithms)                  | MIN   | 10    | us   |
| Trp2    | RESET# Pulse Width (NOT During Automatic Algorithms)              | MIN   | 500   | ns   |
| Trh     | RESET# High Time Before Read                                      | MIN   | 50    | ns   |
| Trb1    | RY/BY# Recovery Time (to CE#, OE# go low)                         | MIN   | 0     | ns   |
| Trb2    | RY/BY# Recovery Time (to WE# go low)                              | MIN   | 50    | ns   |
| Tready1 | RESET# PIN Low (During Automatic Algorithms) to Read or Write     | MAX   | 20    | us   |
| Tready2 | RESET# PIN Low (NOT During Automatic Algorithms) to Read or Write | MAX   | 500   | ns   |


**Figure 3. RESET# TIMING WAVEFORM**




## ERASE/PROGRAM OPERATION


Figure 4. AUTOMATIC CHIP ERASE TIMING WAVEFORM




**Figure 5. AUTOMATIC CHIP ERASE ALGORITHM FLOWCHART**


**Figure 6. AUTOMATIC SECTOR ERASE TIMING WAVEFORM**




**Figure 7. AUTOMATIC SECTOR ERASE ALGORITHM FLOWCHART**

**Figure 8. ERASE SUSPEND/RESUME FLOWCHART**


**Figure 9. AUTOMATIC PROGRAM TIMING WAVEFORMS**




**Figure 10. ACCELERATED PROGRAM TIMING DIAGRAM**



**Figure 11. CE# CONTROLLED WRITE TIMING WAVEFORM**



**Figure 12. AUTOMATIC PROGRAMMING ALGORITHM FLOWCHART**



## SECTOR GROUP PROTECT/CHIP UNPROTECT

Figure 13. SECTOR GROUP PROTECT/CHIP UNPROTECT WAVEFORM (RESET# Control)




Figure 14-1. IN-SYSTEM SECTOR GROUP PROTECT WITH RESET#=Vhv






Figure 14-2. CHIP UNPROTECT ALGORITHMS WITH RESET#=Vhv




**Table 5. TEMPORARY SECTOR GROUP UNPROTECT**

| Parameter | Alt   | Description                                         | Condition | Speed | Unit |
|-----------|-------|-----------------------------------------------------|-----------|-------|------|
| Trpvhh    | Tvidr | RESET# Rise Time to Vhv and Vhv Fall Time to RESET# | MIN       | 500   | ns   |
| Tvhhl     | Trsp  | RESET# Vhv to WE# Low                               | MIN       | 4     | us   |


**Figure 15. TEMPORARY SECTOR GROUP UNPROTECT WAVEFORMS**



**Figure 16. TEMPORARY SECTOR GROUP UNPROTECT FLOWCHART****Notes:**


1. Temporary unprotect all protected sectors Vhv=9.5~10.5V.
2. After leaving temporary unprotect mode, the previously protected sectors are again protected.


**Figure 17. SILICON ID READ TIMING WAVEFORM**



## WRITE OPERATION STATUS

**Figure 18. DATA# POLLING TIMING WAVEFORMS (DURING AUTOMATIC ALGORITHMS)**



**Figure 19. DATA# POLLING ALGORITHM****Notes:**

1. For programming, valid address means program address.  
For erasing, valid address means erase sectors address.
2. Q7 should be rechecked even Q5="1" because Q7 may change simultaneously with Q5.

**Figure 20. TOGGLE BIT TIMING WAVEFORMS (DURING AUTOMATIC ALGORITHMS)**





Figure 21. TOGGLE BIT ALGORITHM



Notes:


1. Read toggle bit twice to determine whether or not it is toggling.
2. Recheck toggle bit because it may stop toggling as Q5 changes to "1".

## AC CHARACTERISTICS

### WORD/BYTE CONFIGURATION (BYTE#)

| Parameter  | Description                   |     | Speed | Unit |
|------------|-------------------------------|-----|-------|------|
|            |                               |     | 70    |      |
| Telf/Telfh | CE# to BYTE# from L/H         | MAX | 5     | ns   |
| Tflqz      | BYTE# from L to Output Hiz    | MAX | 30    | ns   |
| Tfhqv      | BYTE# from H to Output Active | MIN | 70    | ns   |

Figure 22. BYTE# TIMING WAVEFORM FOR READ OPERATIONS (BYTE# switching from byte mode to word mode)



## RECOMMENDED OPERATING CONDITIONS

### At Device Power-Up

AC timing illustrated in Figure A is recommended for the supply voltages and the control signals at device power-up (e.g. Vcc and CE# ramp up simultaneously). If the timing in the figure is ignored, the device may not operate correctly.




Figure A. AC Timing at Device Power-Up

| Symbol | Parameter              | Min. | Max.   | Unit |
|--------|------------------------|------|--------|------|
| Tvr    | Vcc Rise Time          | 20   | 500000 | us/V |
| Tr     | Input Signal Rise Time |      | 20     | us/V |
| Tf     | Input Signal Fall Time |      | 20     | us/V |
| Tvcs   | Vcc Setup Time         | 200  |        | us   |

#### Notes:

1. Not test 100%.

## ERASE AND PROGRAMMING PERFORMANCE

| Parameter                          |           | Limits |         |      | Units  |
|------------------------------------|-----------|--------|---------|------|--------|
|                                    |           | Min.   | Typ.    | Max. |        |
| Chip Erase Time                    |           |        | 45      | 65   | sec    |
| Sector Erase Time                  |           |        | 0.5     | 2    | sec    |
| Erase/Program Cycles               |           |        | 100,000 |      | Cycles |
| Chip Programming Time              | Byte Mode |        | 50      | 160  | sec    |
|                                    | Word Mode |        | 45      | 140  | sec    |
| Accelerated Byte/Word Program Time |           |        | 7       | 210  | us     |
| Word Program Time                  |           |        | 11      | 360  | us     |
| Byte Programming Time              |           |        | 9       | 300  | us     |

Notes:

1. Typical program and erase times assume the following conditions: 25°C, 3.0V VCC. Programming specifications assume checkboard data pattern.
2. Maximum values are measured at VCC = 3.0 V, worst case temperature. Maximum values are valid up to and including 100,000 program/erase cycles.
3. Word/Byte programming specification is based upon a single word/byte programming operation not utilizing the write buffer.
4. Erase/Program cycles comply with JEDEC JESD-47 & JESD 22-A117 standard.

## DATA RETENTION

| Parameter      | Condition | Min. | Max. | Unit  |
|----------------|-----------|------|------|-------|
| Data retention | 55°C      | 20   |      | years |

## LATCH-UP CHARACTERISTICS

|                                                                     | Min.   | Max.       |
|---------------------------------------------------------------------|--------|------------|
| Input Voltage difference with GND on WP#/ACC, A9, OE, Reset# pins   | -1.0V  | 10.5V      |
| Input Voltage difference with GND on all normal pins input          | -1.0V  | Vcc x 1.5V |
| Input Current Pulse                                                 | -100mA | +100mA     |
| All pins included. Test conditions: Vcc = 3.0V, one pin per testing |        |            |

## PIN CAPACITANCE

| Parameter Symbol | Parameter Description   | Test Set | Typ. | Max. | Unit |
|------------------|-------------------------|----------|------|------|------|
| CIN2             | Control Pin Capacitance | VIN=0    | 7.5  | 9    | pF   |
| COUT             | Output Capacitance      | VOUT=0   | 8.5  | 12   | pF   |
| CIN              | Input Capacitance       | VIN=0    | 6    | 7.5  | pF   |



**MACRONIX**  
**INTERNATIONAL Co., LTD.**


## **MX29LV640E T/B**

---

### **ORDERING INFORMATION**


| <b>PART NO.</b>    | <b>ACCESS TIME<br/>(ns)</b> | <b>Ball Pitch/<br/>Ball size</b> | <b>PACKAGE</b>               | <b>Remark</b>     |
|--------------------|-----------------------------|----------------------------------|------------------------------|-------------------|
| MX29LV640ETXEI-70G | 70                          | 0.8mm/0.4mm                      | 48 Ball TFBGA                | RoHS<br>Compliant |
| MX29LV640EBXEI-70G | 70                          | 0.8mm/0.4mm                      | 48 Ball TFBGA                | RoHS<br>Compliant |
| MX29LV640ETTI-70G  | 70                          |                                  | 48 Pin TSOP<br>(Normal Type) | RoHS<br>Compliant |
| MX29LV640EBTI-70G  | 70                          |                                  | 48 Pin TSOP<br>(Normal Type) | RoHS<br>Compliant |

### PART NAME DESCRIPTION



## PACKAGE INFORMATION

Doc. Title: Package Outline for TSOP(I) 48L (12X20mm)NORMAL FORM




Dimensions (inch dimensions are derived from the original mm dimensions)

| SYMBOL |      | A     | A1    | A2    | b     | C     | D     | D1    | E     | e     | L     | L1    | θ |
|--------|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|---|
| UNIT   |      |       |       |       |       |       |       |       |       |       |       |       |   |
| mm     | Min. | ---   | 0.05  | 0.95  | 0.17  | 0.10  | 19.80 | 18.30 | 11.90 | ---   | 0.50  | 0.70  | 0 |
|        | Nom. | ---   | 0.10  | 1.00  | 0.20  | 0.13  | 20.00 | 18.40 | 12.00 | 0.50  | 0.60  | 0.80  | 5 |
|        | Max. | 1.20  | 0.15  | 1.05  | 0.27  | 0.21  | 20.20 | 18.50 | 12.10 | ---   | 0.70  | 0.90  | 8 |
| Inch   | Min. | ---   | 0.002 | 0.037 | 0.007 | 0.004 | 0.780 | 0.720 | 0.469 | ---   | 0.020 | 0.028 | 0 |
|        | Nom. | ---   | 0.004 | 0.039 | 0.008 | 0.005 | 0.787 | 0.724 | 0.472 | 0.020 | 0.024 | 0.031 | 5 |
|        | Max. | 0.047 | 0.006 | 0.041 | 0.011 | 0.008 | 0.795 | 0.728 | 0.476 | ---   | 0.028 | 0.035 | 8 |



| Dwg. No.  | Revision | Reference |      |  |  |
|-----------|----------|-----------|------|--|--|
|           |          | JEDEC     | EIAJ |  |  |
| 6110-1607 | 9        | MO-142    |      |  |  |

Doc. Title: Package Outline for CSP 48BALL(6X8X1.3MM,BALL PITCH 0.8MM,BALL DIAMETER 0.4MM)

TOP VIEW



BOTTOM VIEW



Dimensions (inch dimensions are derived from the original mm dimensions)

| SYMBOL |      | A     | A1    | A2    | b     | D     | D1    | E     | E1    | e     |
|--------|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| UNIT   |      |       |       |       |       |       |       |       |       |       |
| mm     | Min. | ---   | 0.25  | 0.65  | 0.35  | 5.90  |       | 7.90  |       |       |
|        | Nom. | ---   | 0.30  | ---   | 0.40  | 6.00  | 4.00  | 8.00  | 5.60  | 0.80  |
|        | Max. | 1.30  | 0.35  | ---   | 0.45  | 6.10  |       | 8.10  |       |       |
| Inch   | Min. | —     | 0.010 | 0.026 | 0.014 | 0.232 |       | 0.311 |       |       |
|        | Nom. | —     | 0.012 | —     | 0.016 | 0.236 | 0.157 | 0.315 | 0.220 | 0.031 |
|        | Max. | 0.051 | 0.014 | —     | 0.018 | 0.240 |       | 0.319 |       |       |

| Dwg. No.  | Revision | Reference |      |  |  |
|-----------|----------|-----------|------|--|--|
|           |          | JEDEC     | EIAJ |  |  |
| 6110-4202 | 5        | MO-219    |      |  |  |



## REVISION HISTORY

| Revision No. | Description                                                 | Page        | Date        |
|--------------|-------------------------------------------------------------|-------------|-------------|
| 1.0          | 1. Removed "Advanced Information"                           | P1          | OCT/21/2008 |
|              | 2. Removed 90ns option                                      | P1,31,53,56 |             |
|              |                                                             | P57         |             |
|              | 3. Revised high voltage value from 11.5V to 10.5V           | P28,55      |             |
|              | 4. Changed Tcep value from 45ns(min.) to 35ns(min.)         | P31         |             |
| 1.1          | 1. Modified Table 1. BLOCK STRUCTURE : SA44,45              | P6          | MAR/12/2009 |
| 1.2          | 1. Added Tsrw parameter                                     | P31,33      | MAY/19/2009 |
|              | 2. Changed data retention from 10 years to 20 years         | P1,55       |             |
| 1.3          | 1. Modified Factory locked/unlocked from 98/18 to 88/08     | P14,20,21   | JUL/07/2009 |
| 1.4          | 1. Modified SA44/SA45 address                               | P6          | OCT/02/2009 |
| 1.5          | 1. Modified "WRITE PROTECT" description                     | P21         | JUL/05/2011 |
|              | 2. Modified Figure 11. CE# controlled write timing waveform | P45         |             |
|              | 3. Modified description for RoHS compliance                 | P6,60,61    |             |
| 1.6          | 1. Modified Figure 10. Accelerated Program Timing Diagram   | P44         | JUL/27/2011 |
|              | 2. Added notes for Device Power-Up                          | P58         |             |
| 1.7          | 1. Modified sector erase time (typ.) from 0.7s to 0.5s      | P5,59       | DEC/27/2011 |
|              | 2. Added (e.g. Vcc and CE# ramp up simultaneously) wording  | P58         |             |



**MACRONIX**  
**INTERNATIONAL Co., LTD.**

## **MX29LV640E T/B**

---

Except for customized products which has been expressly identified in the applicable agreement, Macronix's products are designed, developed, and/or manufactured for ordinary business, industrial, personal, and/or household applications only, and not for use in any applications which may, directly or indirectly, cause death, personal injury, or severe property damages. In the event Macronix products are used in contradicted to their target usage above, the buyer shall take any and all actions to ensure said Macronix's product qualified for its actual use in accordance with the applicable laws and regulations; and Macronix as well as it's suppliers and/or distributors shall be released from any and all liability arisen therefrom.

Copyright© Macronix International Co., Ltd. 2008~2011. All rights reserved.

Macronix, MXIC, MXIC Logo, MX Logo, Integrated Solutions Provider, NBit, NBit, Macronix NBit, eLiteFlash, XtraROM, Phines, BE-SONOS, KSMC, Kingtech, MXSMIO, Macronix vEE are trademarks or registered trademarks of Macronix International Co., Ltd. The names and brands of other companies are for identification purposes only and may be claimed as the property of the respective companies.

For the contact and order information, please visit Macronix's Web site at: <http://www.macronix.com>