


4.20mm (.165") Pitch Mini-Fit Jr.™ Plug

5559
**Dual Row
With and without Panel Mount Ears**


Features and Benefits

- Wire-to-wire plug for panel-mounted or free-hanging applications
- Positive housing locks to mate with Mini-Fit Jr. receptacle
- Fully isolated terminals to protect contacts from damage

Reference Information

Packaging: Bag
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R75142
Mates With: 5557 dual row receptacle
Use With: 5558, 30490, 46134 or 46012 terminals
Panel Thickness: .079 to 2.00mm (.031 to 0.80")
Designed In: Millimeters

Mechanical


Contact Insertion Force: 1.5kg max.
Contact Retention to Housing: 3.0kg min.

Physical

Housing: 6/6 nylon, UL 94V-2 or 94V-0
Operating Temperature: -40 to +105°C

Circuits	Order No.			
	Panel Mount		Free Hanging	
	94V-2	94V-0	94V-2	94V-0
2	39-01-2021	39-01-2026	39-01-3023	39-01-3029
4	39-01-2041	39-01-2046	39-01-3043	39-01-3049
6	39-01-2061	39-01-2066	39-01-3063	39-01-3069
8	39-01-2081	39-01-2086	39-01-3083	39-01-3089
10	39-01-2101	39-01-2106	39-01-3103	39-01-3109
12	39-01-2121	39-01-2126	39-01-3123	39-01-3129
14	39-01-2141	39-01-2146	39-01-3143	39-01-3149
16	39-01-2161	39-01-2166	39-01-3163	39-01-3169
18	39-01-2181		39-01-3183	
20	39-01-2201			
22	39-01-2221			
24	39-01-2241	39-01-2246		

4.20mm (.165") Pitch Mini-Fit Jr.™ Header

5566
**Vertical, Dual Row
With Pegs, with Drain Holes**


Features and Benefits

- Board-mounting pegs provide polarization during placement on the PCB and increased retention during soldering process
- Positive housing locks to mate with Mini-Fit Jr. receptacle
- Fully isolated terminals to protect contacts from damage
- Drain holes are standard to allow washing of PCB after processing (contact Molex for headers without drain holes)

Reference Information

Packaging: Tray or tube
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R75142
Mates With: 5557 dual row receptacles
PCB Thickness: 1.60mm (.062")
Process: Wave solder
Designed In: Millimeters

Electrical

Voltage: 600V
Current: (Used with 16 AWG)

Series	Circuits			
	2-3	4-6	7-10	12-24
46083	9.0A	8.0A	7.0A	6.0A

Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Mechanical

Insertion Force to PCB: 5.0kg max.
Durability: 30 cycles

Physical

Housing: 6/6 nylon, UL 94V-2 or 94V-0
Contact: Brass
Plating: Tin or Select Gold
Underplating: Nickel
Operating Temperature: -40 to +105°C

Circuits	Order No.				Lead-free
	Tin Plated		Gold Plated (30μ")		
	94V-2	94V-0	94V-2	94V-0	
2	39-30-6027	39-30-6028	39-29-9024	39-28-9028	Yes
4	39-30-6047	39-30-6048	39-29-9044	39-28-9048	
6	39-30-6067	39-30-6068	39-29-9064	39-28-9068	
8	39-30-6087	39-30-6088	39-29-9084	39-28-9088	
10	39-30-6107	39-30-6108	39-29-9104	39-28-9108	
12	39-30-6127	39-30-6128	39-29-9124	39-28-9128	
14	39-30-6147	39-30-6148	39-29-9144	39-28-9148	
16	39-30-6167	39-30-6168	39-29-9164	39-28-9168	
18	39-30-6187	39-30-6188	39-29-9184	39-28-9188	
20	39-30-6207	39-30-6208	39-29-9204	39-28-9208	
22	39-30-6227	39-30-6228	39-29-9224		
24	39-30-6247	39-30-6248	39-29-9244	39-28-9248	