





Grommet Nut - Ac. Type 'EV'.**Style: ABB - ** - ** - EV.****BS Style: A2344.****Cable Clamp Assembly -****Accessory Type E/C (5MS Locking).****Style: SB - ** - ** - CCA. BS Style: A2345.**

ØT limits
of clamp
saddles
when
ØS max.

**Metric Imperial**How to order: **ABB - ** - ** - EV**

Shell size _____

Contact arrangement _____

Typical Example: **ABB - 10SL - 3 - EV**

(includes grommet & follower)

Shell size	ØT max	ØF Thread Class 2B	N max	ØS min	O _a min overlap access'y
10 SL	21.6 0.850	5/8" x 24 UNEF	20.83 0.820	8.6 0.339	6.1 0.240
14 S	24.8 0.976	3/4" x 20 UNEF	20.83 0.820	11.1 0.437	6.1 0.240
16 S	28.7 1.130	7/8" x 20 UNEF	20.83 0.820	14.3 0.563	6.1 0.240
16	28.7 1.130	7/8" x 20 UNEF	25.53 1.005	14.3 0.563	7.6 0.300
18	31.9 1.256	1" x 20 UNEF	25.53 1.005	16.7 0.657	7.6 0.300
20	34.9 1.374	1 1/8" x 18 UNEF	25.53 1.005	19.8 0.780	7.6 0.300
22	38.2 1.504	1 1/4" x 18 UNEF	25.53 1.005	21.34 0.840	7.6 0.300
24	41.4 1.630	1 3/8" x 18 UNEF	25.53 1.005	25.4 1.000	7.6 0.300
28	47.8 1.882	1 5/8" x 18 UNEF	25.53 1.005	30.13 1.186	7.6 0.300
32	54.1 2.130	1 7/8" x 16 UN	25.53 1.005	36.73 1.446	7.6 0.300
36	58.7 2.311	2 1/16" x 16 UNS	25.53 1.005	41.0 1.614	7.6 0.300
40	63.0 2.480	2 5/16" x 16 UN	25.64 1.009	45.9 1.807	7.6 0.300

How to order: **SB - ** - ** - CCA**

Shell size _____

Contact arrangement _____

Typical Example: **SB - 10SL - 3 - CCA**

(includes grommet & follower)

Shell size	ØA Thread Class 2B	B max	C max	ØS1 min	ØS1 max	ØT max	O _a min overlap access'y
10 SL	5/8" x 24 UNEF	33.02 1.300	21.47 0.845	5.08 0.200	7.92 0.312	24.61 0.969	6.1 0.240
14 S	3/4" x 20 UNEF	33.02 1.300	24.64 0.970	7.92 0.312	11.10 0.437	29.36 1.156	6.1 0.240
16 S	7/8" x 20 UNEF	33.02 1.300	28.71 1.130	9.14 0.360	14.27 0.562	31.75 1.250	6.1 0.240
16	7/8" x 20 UNEF	45.72 1.800	28.71 1.130	9.14 0.360	14.27 0.562	31.75 1.250	7.6 0.300
18	1" x 20 UNEF	45.72 1.800	31.88 1.255	10.72 0.422	15.87 0.625	34.14 1.344	7.6 0.300
20	1 1/8" x 18 UNEF	45.72 1.800	35.06 1.380	13.48 0.531	20.62 0.812	37.13 1.462	7.6 0.300
22	1 1/4" x 18 UNEF	45.72 1.800	38.23 1.505	13.48 0.531	20.62 0.812	40.49 1.549	7.6 0.300
24	1 3/8" x 18 UNEF	45.72 1.800	41.41 1.630	15.08 0.594	23.80 0.937	43.66 1.719	7.6 0.300
28	1 5/8" x 18 UNEF	45.72 1.800	47.76 1.880	15.08 0.594	23.80 0.937	50.01 1.969	7.6 0.300
32	1 7/8" x 16 UN	45.72 1.800	54.11 2.130	20.06 0.790	31.75 1.250	56.36 2.219	7.6 0.300
36	2 1/16" x 16 UNS	45.72 1.800	58.75 2.313	20.06 0.790	34.92 1.375	62.71 2.469	7.6 0.300