

8-Channel, Dual 4-Channel, Triple 2-Channel Multiplexers

DESCRIPTION

The DG9251, DG9252, and DG9253 are high precision single and dual supply CMOS analog multiplexers. DG9251 is an 8-channel multiplexer, the DG9252 is a dual 4-channel multiplexer, and the DG9253 is a triple 2-channel multiplexer or triple SPDT.

Designed to operate from a + 2.7 V to + 16 V single supply or from a ± 2.7 V to ± 5 V dual supplies, the DG9251, DG9252, and DG9253 are fully specified at + 16 V, + 5 V and ± 5 V. All control logic inputs have guaranteed 1.4 V high limit when operating from + 5 V or ± 5 V supplies and 1.65 V when operating from a + 16 V supply.

The DG9251, DG9252, and DG9253 are precision multiplexers of low leakage, low charge injection, and low parasitic capacitance. They conduct equally well in both directions, offer rail to rail analog signal handling and can be used both as multiplexers as well as de-multiplexers. The DG9251, DG9252, and DG9253 operating temperature is specified from - 40 °C to + 85 °C and are available in ultra compact 1.8 mm x 2.6 mm miniQFN16 packages.

FEATURES

• Halogen-free According to IEC 61249-2-21 Definition

- + 2.7 V to + 16 V single supply operation
- ± 2.7 V to ± 5 V dual supply operation
- Fully specified at + 16 V, + 5 V, ± 5 V
- Low charge injection (< 4.1 pC typ.)
- High bandwidth: 314 MHz (DG9251)
449 MHz (DG9252)
480 MHz (DG9253)

- Low switch capacitance ($C_{s(off)}$ 2.7 pF typ.)
- Good isolation and crosstalk performance (typ. - 45 dB at 100 MHz)
- MiniQFN16 package (1.8 mm x 2.6 mm)
- Compliant to RoHS Directive 2002/95/EC







RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Data acquisition
- Medical and healthcare devices
- Control and automation equipments
- Test instruments
- Touch panels
- Consumer

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



Device Marking: 8xx for DG9251
(miniQFN16) Hxx for DG9252
Jxx for DG9253
xx = Date/Lot Traceability Code

TRUTH TABLE						
Enable Input	Select Inputs			On Switches		
	C	B	A	DG9251	DG9252	DG9253
H	X	X	X	All Switches Open	All Switches Open	All Switches Open
L	L	L	L	X to X0	X to X0, Y to Y0	X to X0, Y to Y0, Z to Z0
L	L	L	H	X to X1	X to X1, Y to Y1	X to X1, Y to Y0, Z to Z0
L	L	H	L	X to X2	X to X2, Y to Y2	X to X0, Y to Y1, Z to Z0
L	L	H	H	X to X3	X to X3, Y to Y3	X to X1, Y to Y1, Z to Z0
L	H	L	L	X to X4	X to X0, Y to Y0	X to X0, Y to Y0, Z to Z1
L	H	L	H	X to X5	X to X1, Y to Y1	X to X1, Y to Y0, Z to Z1
L	H	H	L	X to X6	X to X2, Y to Y2	X to X0, Y to Y1, Z to Z1
L	H	H	H	X to X7	X to X3, Y to Y3	X to X1, Y to Y1, Z to Z1

ORDERING INFORMATION		
Temp. Range	Package	Part Number
DG9251, DG9252, DG9253		
- 40 °C to 125 °C ^a	16-Pin miniQFN	DG9251EN-T1-E4
		DG9252EN-T1-E4
		DG9253EN-T1-E4

Notes:

a. - 40 °C to 85 °C datasheet limits apply.

ABSOLUTE MAXIMUM RATINGS (T _A = 25 °C, unless otherwise noted)			
Parameter		Limit	Unit
V _{CC} to V _{EE}		18	V
GND to V-		9	
Digital Inputs ^a , V _S , V _D		(V-) - 0.3 to (V+) + 0.3 or 30 mA, whichever occurs first	
Continuous Current (Any terminal)		30	mA
Peak Current, S or D (Pulsed 1 ms, 10 % duty cycle)		100	
Storage Temperature		- 65 to 150	°C
Power Dissipation ^b	16-Pin miniQFN ^{c, d}	525	mW
Thermal Resistance ^b	16-Pin miniQFN ^d	152	°C/W
Latch-up (per JESD78)		> 300	mA

Notes:

a. Signals on SX, DX, or INX exceeding V+ or V- will be clamped by internal diodes. Limit forward diode current to maximum current ratings.

b. All leads welded or soldered to PC board.

c. Derate 6.6 mW/°C above 70 °C.

d. Manual soldering with iron is not recommended for leadless components. The miniQFN-16 is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper lip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection.



SPECIFICATIONS (for Dual Supplies)										
Parameter	Symbol	Test Conditions Unless Otherwise Specified V _{CC} = + 5 V, V _{EE} = - 5 V V _{IN} (A, B, C and ENABLE) = 1.4 V, 0.3 V ^a		Temp. ^b	Typ. ^c	- 40 °C to 125 °C		- 40 °C to 85 °C		Unit
						Min. ^d	Max. ^d	Min. ^d	Max. ^d	
Analog Switch										
Analog Signal Range ^e	V _{ANALOG}			Full		- 5	5	- 5	5	V
On-Resistance	R _{ON}	I _S = 1 mA, V _D = - 3 V, 0 V, + 3 V		Room Full	90		182 252		182 223	Ω
On-Resistance Match	ΔR _{ON}	I _S = 1 mA, V _D = ± 3 V		Room Full	3.1		6 10		6 8	
On-Resistance Flatness	R _{FLATNESS}	I _S = 1 mA, V _D = - 3 V, 0 V, + 3 V		Room Full	32.4		44 64		44 61	
Switch Off Leakage Current	I _{S(off)}	V _{CC} = 5.5 V, V _{EE} = - 5.5 V, V _D = ± 4.5 V, V _S = ± 4.5 V		Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	nA
	I _{D(off)}			Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	
Channel On Leakage Current	I _{D(on)}	V _{CC} = 5.5 V, V _{EE} = - 5.5 V, V _S = V _D = ± 4.5 V		Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	
Digital Control										
V _{IN} (A, B, C and ENABLE) Low	V _{IL}			Full			0.3		0.3	V
V _{IN} (A, B, C and ENABLE) High	V _{IH}			Full		1.4		1.4		
Input Current, V _{IN} Low	I _{IL}	V _{IN} (A, B, C and ENABLE) under test = 0.3 V		Full	0.01	- 1	1	- 1	1	μA
Input Current, V _{IN} High	I _{IH}	V _{IN} (A, B, C and ENABLE) under test = 1.4 V		Full	0.01	- 1	1	- 1	1	
Input Capacitance ^e	C _{IN}	f = 1 MHz		Room	2.4					pF
Dynamic Characteristics										
Transition Time	t _{TRANS}	R _L = 300 Ω, C _L = 35 pF see figure 1, 2, 3		Room Full	88		236 281		236 251	ns
Enable Turn-On Time	t _{ON}			Room Full	158		250 455		250 369	
Enable Turn-Off Time	t _{OFF}			Room Full	40		125 136		125 131	
Break-Before-Make Time Delay	t _D			Room Full	32	13		13		
Off Isolation ^e	OIRR	R _L = 50 Ω, C _L = 15 pF	f = 100 kHz	Room	< - 90					dB
Channel-to-Channel Crosstalk ^e	X _{TALK}		f = 10 MHz	Room	- 64					
			f = 100 MHz	Room	- 45					
			f = 100 kHz	Room	< - 90					
			f = 10 MHz	Room	- 67					
			f = 100 MHz	Room	- 48					
		Bandwidth, 3 dB	BW	R _L = 50 Ω	DG9251	Room	314			
DG9252	Room				449					
DG9253	Room				480					
Charge Injection ^e	Q	V _g = 0 V, R _g = 0 Ω, C _L = 1 nF		Room	4.1					pC
Source Off Capacitance ^e	C _{S(off)}	f = 1 MHz	DG9251	Room	2.7					pF
			DG9252	Room	2.2					
			DG9253	Room	2.0					
Drain Off Capacitance ^e	C _{D(off)}	f = 1 MHz	DG9251	Room	10.7					
			DG9252	Room	6.6					
			DG9253	Room	4.6					
Channel On Capacitance ^e	C _{D(on)}	f = 1 MHz	DG9251	Room	14.6					
			DG9252	Room	9.8					
			DG9253	Room	8.6					
Total Harmonic Distortion ^e	THD	Signal = 1 V _{RMS} , 20 Hz to 20 kHz, R _L = 600 Ω		Room	0.2					%

SPECIFICATIONS (for Dual Supplies)									
Parameter	Symbol	Test Conditions Unless Otherwise Specified V _{CC} = + 5 V, V _{EE} = - 5 V V _{IN(A, B, C and ENABLE)} = 1.4 V, 0.3 V ^a	Temp. ^b	Typ. ^c	- 40 °C to 125 °C		- 40 °C to 85 °C		Unit
					Min. ^d	Max. ^d	Min. ^d	Max. ^d	
Power Supplies									
Power Supply Current	I _{CC}	V _{CC} = + 5 V, V _{EE} = - 5 V V _{IN(A, B, C and ENABLE)} = 0 or 5 V	Room Full	0.05		1 10		1 10	μA
Negative Supply Current	I _{EE}		Room Full	- 0.05	- 1 - 10		- 1 - 10		
Ground Current	I _{GND}		Room Full	- 0.05	- 1 - 10		- 1 - 10		

SPECIFICATIONS (for Unipolar Supplies)									
Parameter	Symbol	Test Conditions Unless Otherwise Specified V _{CC} = + 5 V, V _{EE} = 0 V V _{IN} (A, B, C and ENABLE) = 1.4 V, 0.3 V ^a	Temp. ^b	Typ. ^c	- 40 °C to 125 °C		- 40 °C to 85 °C		Unit
					Min. ^d	Max. ^d	Min. ^d	Max. ^d	
Analog Switch									
Analog Signal Range ^e	V _{ANALOG}		Full		0	5	0	5	V
On-Resistance	R _{ON}	I _S = 1 mA, V _D = 0 V, + 3.5 V	Room Full	145		482 565		482 513	Ω
On-Resistance Match	ΔR _{ON}	I _S = 1 mA, V _D = + 3.5 V	Room Full	3.6		20 22		20 21	
On-Resistance Flatness	R _{FLATNESS}	I _S = 1 mA, V _D = 0 V, + 3 V	Room Full	113		151 254		151 231	
Switch Off Leakage Current	I _{S(off)}	V _{CC} = + 5.5 V, V _{EE} = 0 V V _D = 1 V/4.5 V, V _S = 4.5 V/1 V	Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	nA
	I _{D(off)}		Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	
Channel On Leakage Current	I _{D(on)}	V _{CC} = + 5.5 V, V _{EE} = 0 V V _D = V _S = 1 V/4.5 V	Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	
Digital Control									
V _{IN} (A, B, C and ENABLE) Low	V _{IL}		Full			0.3		0.3	V
V _{IN} (A, B, C and ENABLE) High	V _{IH}		Full		1.4		1.4		
Input Current, V _{IN} Low	I _L	V _{IN} (A, B, C and ENABLE) under test = 0.3 V	Full	0.01	- 1	1	- 1	1	μA
Input Current, V _{IN} High	I _H	V _{IN} (A, B, C and ENABLE) under test = 1.4 V	Full	0.01	- 1	1	- 1	1	
Dynamic Characteristics									
Transition Time	t _{TRANS}	R _L = 300 Ω, C _L = 35 pF see figure 1, 2, 3	Room Full	97		230 305		230 266	ns
Enable Turn-On Time	t _{ON}		Room Full	229		335 652		335 545	
Enable Turn-Off Time	t _{OFF}		Room Full	64		150 173		150 163	
Break-Before-Make Time Delay	t _D		Room Full	36	20		20		
Charge Injection ^e	Q	V _g = 0 V, R _g = 0 Ω, C _L = 1 nF	Full	0.44					pC
Off Isolation ^e	OIRR	R _L = 50 Ω, C _L = 15 pF f = 100 kHz	Room	< - 90					dB
Channel-to-Channel Crosstalk ^e	X _{TALK}		Room	< - 90					

**SPECIFICATIONS** (for Unipolar Supplies)

Parameter	Symbol	Test Conditions Unless Otherwise Specified V _{CC} = + 5 V, V _{EE} = 0 V V _{IN} (A, B, C and ENABLE) = 1.4 V, 0.3 V ^a		Temp. ^b	Typ. ^c	- 40 °C to 125 °C		- 40 °C to 85 °C		Unit
						Min. ^d	Max. ^d	Min. ^d	Max. ^d	
Dynamic Characteristics										
Source Off Capacitance ^e	C _{S(off)}	f = 1 MHz	DG9251	Room	2.9					pF
			DG9252	Room	2.2					
			DG9253	Room	2.1					
Drain Off Capacitance ^e	C _{D(off)}	f = 1 MHz	DG9251	Room	12.4					
			DG9252	Room	6.8					
			DG9253	Room	4.6					
Channel On Capacitance ^e	C _{D(on)}	f = 1 MHz	DG9251	Room	16					
			DG9252	Room	10.6					
			DG9253	Room	8.8					
Power Supplies										
Power Supply Current	I _{CC}	V _{IN} (A, B, C and ENABLE) = 0 V or 5 V		Room Full	0.05		1 10		1 10	μA
Negative Supply Current	I _{EE}			Room Full	- 0.05	- 1 - 10		- 1 - 10		
Ground Current	I _{GND}			Room Full	- 0.05	- 1 - 10		- 1 - 10		

SPECIFICATIONS (for Unipolar Supplies)

Parameter	Symbol	Test Conditions Unless Otherwise Specified V _{CC} = + 16 V, V _{EE} = 0 V V _{IN} (A, B, C and ENABLE) = 1.6 V, 0.5 V ^a	Temp. ^b	Typ. ^c	- 40 °C to 125 °C		- 40 °C to 85 °C		Unit
					Min. ^d	Max. ^d	Min. ^d	Max. ^d	
Analog Switch									
Analog Signal Range ^e	V _{ANALOG}		Full		0	16	0	16	V
On-Resistance	R _{ON}	I _S = 1 mA, V _D = 0.7 V, 8 V, 15.3 V	Room Full	69		152 171		152 158	Ω
On-Resistance Match	ΔR _{ON}	I _S = 1 mA, V _D = + 0.7 V	Room Full	2		7 10		7 8	
On-Resistance Flatness	R _{FLATNESS}	I _S = 1 mA, V _D = 0.7 V, + 15.3 V	Room Full	32		45 53		45 49	
Switch Off Leakage Current	I _{S(off)}	V _{CC} = + 16 V, V _{EE} = 0 V V _D = 1 V/15 V, V _S = 15 V/1 V	Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	nA
	I _{D(off)}		Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	
Channel On Leakage Current	I _{D(on)}	V _{CC} = + 16 V, V _{EE} = 0 V V _D = V _S = 1 V/15 V	Room Full	± 0.02	- 1 - 50	1 50	- 1 - 5	1 5	
Digital Control									
V _{IN} (A, B, C and ENABLE) Low	V _{IL}		Full			0.5		0.5	V
V _{IN} (A, B, C and ENABLE) High	V _{IH}		Full		1.6		1.6		
Input Current, V _{IN} Low	I _L	V _{IN} (A, B, C and ENABLE) under test = 0.5 V	Full	0.01	- 1	1	- 1	1	μA
Input Current, V _{IN} High	I _H	V _{IN} (A, B, C and ENABLE) under test = 1.6 V	Full	0.01	- 1	1	- 1	1	
Dynamic Characteristics									
Transition Time	t _{TRANS}	R _L = 300 Ω, C _L = 35 pF see figure 1, 2, 3	Room Full	56		130 160		130 150	ns
Enable Turn-On Time	t _{ON}		Room Full	98		175 256		175 221	
Enable Turn-Off Time	t _{OFF}		Room Full	37		120 134		120 127	
Break-Before-Make Time Delay	t _D		Room Full	31	12		12		

SPECIFICATIONS (for Unipolar Supplies)

Parameter	Symbol	Test Conditions Unless Otherwise Specified V _{CC} = + 16 V, V _{EE} = 0 V V _{IN} (A, B, C and ENABLE) = 1.6 V, 0.5 V ^a		Temp. ^b	Typ. ^c	- 40 °C to 125 °C		- 40 °C to 85 °C		Unit
						Min. ^d	Max. ^d	Min. ^d	Max. ^d	
Charge Injection ^e	Q	V _g = 0 V, R _g = 0 Ω, C _L = 1 nF		Room	4.5					pC
Dynamic Characteristics										
Off Isolation ^e	OIRR	R _L = 50 Ω, C _L = 15 pF f = 100 kHz		Room	< - 90					dB
Channel-to-Channel Crosstalk ^e	X _{TALK}			Room	< - 90					
Source Off Capacitance ^e	C _{S(off)}	f = 1 MHz	DG9251	Room	2.6					pF
			DG9252	Room	2.1					
			DG9253	Room	1.8					
Drain Off Capacitance ^e	C _{D(off)}	f = 1 MHz	DG9251	Room	10.4					
			DG9252	Room	5.8					
			DG9253	Room	4.2					
Channel On Capacitance ^e	C _{D(on)}	f = 1 MHz	DG9251	Room	15					
			DG9252	Room	9.5					
			DG9253	Room	8.2					
Power Supplies										
Power Supply Current	I _{CC}	V _{IN} (A, B, C and ENABLE) = 0 V or 16 V		Room Full	0.05		1 10		1 10	μA
Negative Supply Current	I _{EE}			Room Full	- 0.05	- 1 - 10		- 1 - 10		
Ground Current	I _{GND}			Room Full	- 0.05	- 1 - 10		- 1 - 10		

Notes:

a. V_{IN} = input voltage to perform proper function.

b. Room - 25 °C, full = as determined by the operating temperature suffix.


c. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.

d. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet.


e. Guaranteed by design, not subject to production test.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.







TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




R_{ON} vs. V_D and Single Supply Voltage




R_{ON} vs. V_D and Dual Supply Voltage

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

R_{ON} vs. Analog Voltage and Temperature

R_{ON} vs. Analog Voltage and Temperature

R_{ON} vs. Analog Voltage and Temperature

R_{ON} vs. Analog Voltage and Temperature

Leakage Current vs. Temperature

Leakage Current vs. Temperature


TYPICAL CHARACTERISTICS




DG9251 Insertion Loss, Off-Isolation, Crosstalk vs. Frequency




DG9251 Charge Injection vs. Analog Voltage




DG9252 Insertion Loss, Off-Isolation, Crosstalk vs. Frequency






DG9252 Charge Injection vs. Analog Voltage



DG9253 Insertion Loss, Off-Isolation, Crosstalk vs. Frequency



DG9253 Charge Injection vs. Analog Voltage

TYPICAL CHARACTERISTICS

Switching Time vs. Temperature

Switching Threshold vs. Supply Voltage

Supply Current vs. Input Switching Frequency

TEST CIRCUITS











Figure 1. Transition Time

TEST CIRCUITS

Figure 2. Enable Switching Time

TEST CIRCUITS







Figure 3. Break-Before-Make

TEST CIRCUITS




Figure 4. Charge Injection





Figure 5. Insertion Loss




Figure 6. Off Isolation




Figure 7. Crosstalk






Figure 8. Source, Drain Capacitance

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg267075.

MINI QFN-16L




BACK SIDE VIEW

DIM	MILLIMETERS			INCHES		
	MIN.	NAM	MAX.	MIN.	NAM	MAX.
A	0.70	0.75	0.80	0.0275	0.0295	0.0315
A1	0	-	0.05	0	-	0.002
b	0.15	0.20	0.25	0.0059	0.0078	0.0098
C	0.15	0.20	0.25	0.0059	0.0078	0.0098
D	2.60 BSC			0.1023 BSC		
E	1.80 BSC			0.0708 BSC		
e	0.40 BSC			0.0157 BSC		
L	0.35	0.40	0.45	0.0137	0.0157	0.0177
L1	0.45	0.50	0.55	0.0177	0.0196	0.0216

ECN T-06380-Rev. A, 14-Aug-06
DWG: 5954

RECOMMENDED MINIMUM PADS FOR MINI QFN 16L





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[DG9251EN-T1-E4](#) [DG9252EN-T1-E4](#) [DG9253EN-T1-E4](#)