






PRODUCT NUMBER	PCB THICKNESS
91877-001	1.6MM
91877-002	2.4MM
91877-003	2.4MM
91877-001LF	1.6MM
91877-002LF	2.4MM

OBSOLETE USE 91877-002



SEE NOTE 2



RECOMMENDED HOLE PATTERN
COMPONENT SIDE

NOTE:

- HOUSING SHOWN FOR APPLICATION CLARITY AND DOES NOT COME WITH R.A.RECEPTACLE POWER CONTACT
- 4 ROW HSG W/HEAT STAKE PEG: P/N 70292-101
4 ROW HSG W/PRESS PEG: P/N 89092-101
5 ROW HSG W/HEAT STAKE PEG: P/N 73477-101
5 ROW HSG W/PRESS PEG: P/N 73478-101
- RECEPTACLE CONTACT PLATING:
GOLD OVER NICKEL
- PLATING ON TAILS OF 91877-YYY IS SnPb
PLATING ON TAILS OF 91877-YYYLF IS Sn (LEAD FREE)
- IF P/N IS "LF" THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

mat'l. code				surface		tolerance		projection		product family							
-				ISO 1302		ISO 406 ISO 1101				METRAL (tm)							
ltr	ecn	no	dr	date		tolerances unless otherwise specified						title					
B	v31676	SCS		9/08/93		angles		linear		XX ±.01/.3							
C	v60188	CSC		2/02/96						XXX ±.005/.13							
D	v01818	JWS		7/17/00		0°±2'				XXXX ±.0020/.050		scale 1:1					
E	v02928	JWS		12/12/00		dr	STU STONER	11/01/91				dwg no		sheet1 of 1		size	
F	v04-1176	TAB		12/14/04		enr	R. DOUTRICH	11/01/91				91877		A.			
G	M06-0156	MHT		4/13/06		chr	STU STONER	11/01/91									
H	M06-0286	MNR		7/27/06		appd	STU STONER	11/01/91									
sheet		revision		H								type Product Customer Drawing					
index		sheet		1													