


| DCP # | REV | DESCRIPTION                | DRAWN | DATE    | CHECKD | DATE    | APPRVD | DATE    |
|-------|-----|----------------------------|-------|---------|--------|---------|--------|---------|
| 564   | C   | REVISED & ADDED MORE PARTS | HYO   | 4/3/00  | JC     | 6/5/00  | JC     | 6/5/00  |
| 1892  | D   | Update To RoHS Compliant   | EO    | 3/14/06 | HO     | 3/15/06 | HO     | 3/15/06 |


RoHS  
Compliant


| SPC Type No. | THREAD<br>SIZE | LENGTH<br>(INCHES) |
|--------------|----------------|--------------------|
| HTB-4-250-A  | 4-40           | 0.250              |
| HTB-4-375-A  |                | 0.375              |
| HTB-4-500-A  |                | 0.500              |
| 2747         |                | 0.625              |
| HTB-4-750-A  |                | 0.750              |
| 2748         |                | 0.875              |
| HTB-4-1000-A |                | 1.000              |
| 2749         |                | 1.500              |
| 2750         |                | 2.000              |
| HTB-6-250-A  | 6-32           | 0.250              |
| HTB-6-375-A  |                | 0.375              |
| HTB-6-500-A  |                | 0.500              |
| 2744         |                | 0.625              |
| HTB-6-750-A  |                | 0.750              |
| 2751         |                | 0.875              |
| HTB-6-1000-A |                | 1.000              |
| 2745         |                | 1.500              |
| 2746         | 8-32           | 2.000              |
| HTB-8-250-A  |                | 0.250              |
| HTB-8-375-A  |                | 0.375              |
| HTB-8-500-A  |                | 0.500              |
| 2752         |                | 0.625              |
| HTB-8-750-A  |                | 0.750              |
| 2753         |                | 0.875              |
| HTB-8-1000-A |                | 1.000              |
| 2754         |                | 1.500              |
| 2755         |                | 2.000              |

### NOTES:

1. MATERIAL: BRASS, ASTM-B16
2. FINISH: ZINC, PLATED PER QQ-Z-325B
3. SPACERS OVER 1.00 LONG ARE TAPPED 0.375 DEEP EACH END

SPC-F004.DWG

|                                                                                         |              |         |                                                        |          |                     |               |
|-----------------------------------------------------------------------------------------|--------------|---------|--------------------------------------------------------|----------|---------------------|---------------|
| TOLERANCES:<br><br>UNLESS OTHERWISE<br>SPECIFIED<br>DECIMALS<br>.XXX $\pm$ 0.005 [0.15] | DRAWN BY:    | DATE:   | DRAWING TITLE:<br><b>HEX STANDOFF, THREADED, BRASS</b> |          |                     |               |
|                                                                                         | J.P.         | 4/12/93 |                                                        |          |                     |               |
|                                                                                         | CHECKED BY:  | DATE:   | SIZE                                                   | DWG. NO. | ELECTRONIC FILE     | REV           |
|                                                                                         | J.C.         | 4/13/93 | A                                                      | TA-246   | TA-246.DWG          | D             |
|                                                                                         | APPROVED BY: | DATE:   | SCALE: NTS                                             |          | U.O.M.: INCHES [mm] | SHEET: 1 OF 1 |
|                                                                                         | K.D.         | 4/13/93 |                                                        |          |                     |               |

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.