


**FEATURES**

- Max. propagation delay of 1050ps
- IEE min. of -60mA
- Extended supply voltage option:  
VEE = -4.2V to -5.5V
- Voltage and temperature compensation for improved noise immunity
- Internal 75kΩ input pull-down resistors
- 40% faster than Fairchild 300K at lower power
- Function and pinout compatible with Fairchild F100K
- Available in 28-pin PLCC package

**DESCRIPTION**

The SY100S304 is an ultra-fast quint AND/NAND gate designed for use in high-performance ECL systems. This device also features a Function (F) output which is the wire-NOR of the AND gate outputs. The inputs on the device have 75kΩ pull-down resistors.


**BLOCK DIAGRAM**



**PIN NAMES**

Pin	Function
Dna – Dne	Data Inputs (n-1...5)
E	Enable Input
Oa – Oe	Data Outputs
$\bar{O}a - \bar{O}e$	Complementary Data Outputs
VEES	VEE Substrate
VCCA	VCCO for ECL Outputs

**PACKAGE/ORDERING INFORMATION**



**28-Pin PLCC (J28-1)**

**Ordering Information**

Part Number	Package Type	Operating Range	Package Marking	Lead Finish
SY100S304JC	J28-1	Commercial	SY100S304JC	Sn-Pb
SY100S304JCTR <sup>(1)</sup>	J28-1	Commercial	SY100S304JC	Sn-Pb
SY100S304JZ <sup>(2)</sup>	J28-1	Commercial	SY100S304JZ with Pb-Free bar-line indicator	Matte-Sn
SY100S304JZTR <sup>(1, 2)</sup>	J28-1	Commercial	SY100S304JZ with Pb-Free bar-line indicator	Matte-Sn

**Notes:**

1. Tape and Reel.
2. Pb-Free package is recommended for new designs.

### DC ELECTRICAL CHARACTERISTICS

V<sub>EE</sub> = -4.2V to -5.5V unless otherwise specified, V<sub>CC</sub> = V<sub>CCA</sub> = GND


Symbol	Parameter	Min.	Typ.	Max.	Unit	Condition
I <sub>IH</sub>	Input HIGH Current D2a — D2e D1a — D1e	—	—	250	μA	V <sub>IN</sub> = V <sub>IH</sub> (Max.)
I <sub>EE</sub>	Power Supply Current	-60	-40	-30	mA	Inputs Open

### AC ELECTRICAL CHARACTERISTICS

V<sub>EE</sub> = -4.2V to -5.5V unless otherwise specified, V<sub>CC</sub> = V<sub>CCA</sub> = GND

Symbol	Parameter	T <sub>A</sub> = 0°C		T <sub>A</sub> = +25°C		T <sub>A</sub> = +85°C		Unit	Condition
		Min.	Max.	Min.	Max.	Min.	Max.		
t <sub>PLH</sub> t <sub>PHL</sub>	Propagation Delay D <sub>na</sub> — D <sub>ne</sub> to O, $\bar{O}$	300	1050	300	1050	300	1050	ps	
t <sub>PLH</sub> t <sub>PHL</sub>	Propagation Delay Data to F	600	1550	600	1550	600	1550	ps	
t <sub>TLH</sub> t <sub>THL</sub>	Transition Time 20% to 80%, 80% to 20%	300	900	300	900	300	900	ps	

### TIMING DIAGRAM






Propagation Delay and Transition Times

**NOTE:**

V<sub>EE</sub> = -4.2V to -5.5V unless otherwise specified, V<sub>CC</sub> = V<sub>CCA</sub> = GND

**28-PIN PLCC (J28-1)**



NOTES:

1. DIMENSIONS ARE IN INCHES [MM].
2. CONTROLLING DIMENSION: INCHES.
3. DIMENSION DOES NOT INCLUDE MOLD FLASH OR PROTRUSIONS, EITHER OF WHICH SHALL NOT EXCEED 0.008 [0.203].
4. LEAD DIMENSION DOES NOT INCLUDE DAMBAR PROTRUSION.
5. MAXIMUM AND MINIMUM SPECIFICATIONS ARE INDICATED AS FOLLOWS: MAX/MIN
6. PACKAGE TOP DIMENSION MAY BE SLIGHTLY SMALLER THAN BOTTOM DIMENSION.

Rev. A

**MICREL, INC. 2180 FORTUNE DRIVE SAN JOSE, CA 95131 USA**

TEL + 1 (408) 944-0800 FAX + 1 (408) 474-1000 WEB <http://www.micrel.com>

The information furnished by Micrel in this data sheet is believed to be accurate and reliable. However, no responsibility is assumed by Micrel for its use. Micrel reserves the right to change circuitry and specifications at any time without notification to the customer.

Micrel Products are not designed or authorized for use as components in life support appliances, devices or systems where malfunction of a product can reasonably be expected to result in personal injury. Life support devices or systems are devices or systems that (a) are intended for surgical implant into the body or (b) support or sustain life, and whose failure to perform can be reasonably expected to result in a significant injury to the user. A Purchaser's use or sale of Micrel Products for use in life support appliances, devices or systems is at Purchaser's own risk and Purchaser agrees to fully indemnify Micrel for any damages resulting from such use or sale.

© 2006 Micrel, Incorporated.