

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0015820322

Status:

Obsolete

Description:

1.27mm (.050") Pitch SIMM Socket, Left Polarization, Right Angle, Single Row, Plastic Latch, 72 Circuits

Replacement Part Number:

NONE

Documents:

[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Memory Module Sockets
Series	78968
Component Type	Memory Module
JEDEC Outline	N/A
Obsolete Date	2006/04/01
Product Name	SIMM
Replacement Part Number	NONE

Physical

Circuits (Loaded)	72
Color - Resin	Black
Durability (mating cycles max)	25
Entry Angle	90° Angle (Side Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	1.27mm (.050")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	3.810µm (150µ")
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1A
Voltage - Maximum	250V
Voltage Key	N/A

Solder Process Data

Lead-free Process Capability	SMC & Wave Capable (TH only)
Process Temperature max. C	260

Material Info

Old Part Number	789687212
-----------------	-----------

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

78968Series

Mates With

JEDEC MO-116 modules

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION