

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LDC		DIST		REVISIONS				
DF	AO	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			C	REV PER ECD 07-001386	1-19-07	CT	DE	

DESCRIPTION	MATERIAL	FINISH
GROMMET	FLUOROSILICONE	COLOR: BLUE
MODULE ASSEMBLY	EPOXY, EPIALL 1908B OR E484 OR FIBERITE E8354	COLOR: BLACK
CONTACT, SOCKET ASSEMBLY	BERYLLIUM COPPER PER ASTM-B194	GOLD PLATE PER MIL-G-45204
CLIP CONTACT RETAINING	BERYLLIUM COPPER PER ASTM-B194 OR STAINLESS STEEL PER QQ-S-766	NONE
BRACKET / GROUNDING PLATE	AL-ALLOY 6061-T4	NICKEL PLATE PER QQ-N-290
CONTACT QTY 11	COPPER ALLOY PER MIL-C-39029/1	GOLD PLATE PER MIL-G-45204
SEALING PLUG QTY 2	F.E.P. PER MIL-P-19468	COLOR: RED



- 1

MARK MODULE ASSEMBLY WITH "AMP", AMP PART NO., DATE CODE,
AT APPROXIMATE AREA SHOWN.
- 2

CONTACTS AND SEALING PLUGS SUPPLIED WITH MODULE ASSEMBLY.

—	SIZE 22	592836-3
—	SIZE 20	592836-2
2	SIZE 20	592836-1
REMARKS	DESCRIPTION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C. C. THOMAS 5-26-99	AMP Tyco Electronics Corporation Harrisburg, PA 17105-3608				
		CHK D. MILLER 5-26-99					
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. MILLER 5-26-99	NAME MODULE WITH GROUNDING BRACKET SIZE 20/22, TJ				
	0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH	PRODUCT SPEC - APPLICATION SPEC -					SIZE A2 CAGE CODE 00779 DRAWING NO C=592836 RESTRICTED TO -
	MATERIAL SEE TABLE	WEIGHT -					
		CUSTOMER DRAWING			SCALE 2: 1	SHEET 1 of 1	REV C