


MATERIALS	
BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
INSULATOR	PTFE
COUPLING NUT	BRASS NICKEL PLATED



SPECIFICATIONS

FREQUENCY RANGE: DC TO 18 GHz

ATTENUATION: 10 dB

IMPEDANCE: 50 OHMS

ACCURACY: ± 0.5 dB

VSWR:

DC — 4 GHz 1.15:1 MAX

4 GHz — 8 GHz 1.20:1 MAX

8 GHz — 12.4 GHz 1.25:1 MAX

12.4 GHz — 18 GHz 1.35:1 MAX

AVG. POWER HANDLING CAPABILITY: 2 WATTS



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7004-10

DES. N ATTENUATOR, MALE TO FEMALE, 10 dB
FREQUENCY RANGE: DC TO 18 GHz

REV. A **FSCM NO. 53919**

CAD FILE 030408

SCALE N/A

SIZE A 147

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.