



PRODUCT NUMBER
85353-101




NOTES:

1. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
2. LEADFREE OR RoHS DIRECTIVE LABELLING TO BE PROVIDED AS PER GS-14-920.
3. " LF " SUFFIX TO PRODUCT NUMBER FOR RoHS COMPATIBLE/ LEADFREE VERSION.
4. PARTS WITH AND WITHOUT "LF " SUFFIX ARE FORM-FIT AND FUNCTIONALLY IDENTICAL.
" LF " SUFFIX PROVIDED FOR PART NUMBER STANDARDISATION OF PART THAT MEETS RoHS REQUIREMENTS.
- 5 FINISH: Ni OVER Cu
- 6 PLASTIC MATERIAL PC, THERMOPLASTIC POLYESTER 20% GLASSFILLED, FLAME RETARDENT PER UL-94-V0
- 7 CABLE SPEC.: MINIMUM DIAMETER OF THE BRAID 3.05 MM, MAXIMUM 8.55 x 4.75 MM
- 8 FOR THIN CABLE TYPES, CABLE TIE AROUND ONE EAR ONLY



VISUAL POLARIZATION



mat'l. code				surface		tolerance		projection	product family									
SEE NOTE				ISO 1302		ISO 406		ISO 1101	BACKPANEL									
ltr	ecn no	dr	date	tolerances		unless		otherwise specified	title									
A	H50211	RVI	1995-04-03	angles		linear			3x3 COVER METALIZED									
B	H50508	RVI	1995-09-08															
C	H70044	JDE	1997-01-06															
D	F10129	VIB	2001-02-05	dr		P.POTTERS		1995-03-14	dwg no									
E	I05-0123	MINI	2005-07-27	engr		P.POTTERS		1995-03-14	sheet 1 of 1									
F	I05-0248	MINI	2005-11-22	chr		RAKHEE GEORGE		2006-06-01	size									
G	I06-0083	MINI	2006-06-01	appd		RAKHEE GEORGE		2006-06-01	type									
sheet index		revision		G														
		sheet		1														