

TRUE RMS RF POWER DETECTOR

Check for Samples: [TRF1600](#)

FEATURES

- RF True RMS Power Detector
- RMS to DC Conversion Up to 2 GHz
- Waveform and Modulation Independent (CW, GSM, WCDMA, TDMA, HSUPA)
- Linear-In-dB Output
- Input Dynamic Range of 28 dB (–29 dBm to –1 dBm)
- External Input Pin
- 6.7-mA Typical Operating Current
- 5-μA Maximum Shutdown Current

- Operating Temperature Range: –20°C to 85°C
- Small 2-mm x 2-mm QFN 6 Pin Package

APPLICATIONS

- Cellular Handsets (GSM, CDMA, TDMA)
- Power Amplifier Control Loops
- Transmitter Power Measurement and Control

DESCRIPTION

The TRF1600 is a true RMS power detector with a 28-dB dynamic input range and a linear-to-dB DC output. It is intended for use in wireless handheld devices such as cell phones and PDAs to measure and control PA output power accurately independent of the modulation scheme.

The device is designed to operate off of a lithium-ion battery (2.7 V to 5.5 V, 6 V tolerant) or a regulated supply. A low input signal at the enable pin puts the device in shut-down mode and supply current consumption is reduced to <5 μA. When asserted high the device enters active mode and outputs a DC voltage proportional to the RMS value of the input power expressed in dBm.

Table 1. ORDERING INFORMATION⁽¹⁾

T _A	PACKAGE ⁽²⁾	ORDERABLE PART NUMBER
–20°C to 85°C	DRV	TRF1600DRV


(1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI web site at www.ti.com.

(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

BLOCK DIAGRAM



*C_{IN} may be omitted if the DC level of the RF input signal is at ground.

PINOUT




Table 2. TERMINAL FUNCTIONS

TERMINAL		I/O	DESCRIPTION
NAME	NO.		
RFIN	1	I	RF input
GND	2		Ground
VOUT	3	O	Output of the device
CF	4	I	Filter capacitor. Pin needs to be connected to an off-chip filter capacitor in the application.
EN	5	I	Enable pin/Vprog
VBAT	6		Input supply pin to the device

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

All voltages values are with respect to GND. Over operating free-air temperature range (unless otherwise noted).

		VALUE	UNIT
	Unregulated input battery voltage	-0.5 to 6.0	V
	EN	-0.5 to 3.6	V
	VOUT	-0.5 to 3.6	V
	PRFIN (max RF input power)	6	dBm
θ_{JA}	Thermal resistance, junction to ambient	140	°C/W
P_D	Continuous power dissipation	50	mW
ESD integrity	HBM (human body model)	2k	V
	CMD (charged device model)	500	
	IEC Contact – V_{CC} pin ⁽²⁾	8k	
	IEC Air – V_{CC} pin ⁽²⁾	15k	
T_A	Operating ambient temperature	-40 to 125	°C
T_J	Operating junction temperature	125	°C
T_S	Storage temperature	-40 to 125	°C

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) IEC ESD tests performed on V_{CC} pin with five shunt capacitors ranging from 10 pF to 10 μ F. This is meant to evaluate the performance of the device when it is powered directly from a battery with these capacitors used as bypass capacitors on the same PC board.

RECOMMENDED OPERATING CONDITIONS

over operating free-air temperature range (unless otherwise noted)

		MIN	NOM	MAX	UNIT
V_{BAT}	Unregulated input battery voltage	2.7		5.5	V
f_{IN}	Input frequency range	800		2000	MHz
	EN pin voltage	0		3.3	V
P_D	Continuous power dissipation			35	mW
T_A	Operating ambient temperature	-20		85	°C
	C_{FILTER}	0		3000	pF

ELECTRICAL CHARACTERISTICS

$V_{BAT} = 3.0 \pm 5\%$, $T_A = -20$ to 85°C , $C_{FILTER} = 820$ pF $\pm 10\%$, unless otherwise specified.

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
SUPPLY CURRENT						
V_{BAT}	Battery voltage		2.7		5.5	V
$I_{BAT, ACTIVE}$	Supply current	EN = HIGH		6.7	8.5	mA
$I_{BAT, IDLE}$	Supply current, idle	EN = LOW RF input power present			10	μ A
$I_{BAT, S/D}$	Supply current, shutdown	EN = LOW No RF input power present			5	μ A
INPUT						
f_{IN}	Input frequency		800		2000	MHz
$P_{RFIN800}$	Input power, 800 MHz	Referred to 50- Ω Z_{in}	-34		-1	dBm
$P_{RFIN2000}$	Input power, 2 GHz	Referred to 50- Ω Z_{in}	-29		-1	dBm
OUTPUT						
$V_{OUT Max}$	Output voltage maximum	-1 dBm, 800 MHz	1.2	1.55	1.7	V
$V_{OUT Max}$	Output voltage maximum	-1 dBm, 2 GHz	1	1.32	1.55	V
$V_{OUT No RF}$	Output voltage no RF	No RF present	0	160	300	mV
$V_{OUT Range}$	Output voltage range	Over specified dynamic range		1.27		V

ELECTRICAL CHARACTERISTICS (continued)

 $V_{BAT} = 3.0 \pm 5\%$, $T_A = -20$ to 85°C , $C_{FILTER} = 820$ pF $\pm 10\%$, unless otherwise specified.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$V_{OUT,GAIN}$	Output voltage gain		30	35	40	mV/dB
	10-dB log conformance error over temperature ⁽¹⁾	See Appendix A.1	–1		1	dB
	1-dB log conformance error	Ideal 1-dB power step	–0.3		0.3	dB
	Straight line 5-dB step error ⁽²⁾	See Appendix A.2		0.06		dB
	Output variation due to modulation at same input power	Anywhere in dynamic range. (AM modulation 100% modulation depth with a 1-MHz tone)		0.1	0.35	dB
TC_{VOUT}	Response temperature coefficient ⁽¹⁾	$P_{RFIN} = -4$ dBm See Appendix A.3		2.2		mdB/ $^\circ\text{C}$
ΔTC_{VOUT}	Response temperature sensitivity spread - 1σ ⁽¹⁾	$P_{RFIN} = -4$ dBm See Appendix A.3		4.1		mdB/ $^\circ\text{C}$
ΔV_{OUT_TEMP}	Output voltage repeatability over temperature ⁽¹⁾			0.04	0.11	dB
PSRR	Power supply rejection ratio	$V_{BAT} = 2.7$ V to 5.5 V	30			dB
$V_{OUT, NOISE}$	Output referred noise	Integrated over bandwidth 1 kHz – 6.5 kHz		100	200	μV_{RMS}
$R_{OUT, EN1}$	Output impedance	EN = HIGH		9	50	Ω
$I_{OUT, EN0}$	Output leakage	EN = LOW			3	μA
t_{SAMPLE}	Sampling time (time to valid output)	EN = HIGH $P_{RFIN} = \text{MAX}$ V_{OUT} 10% to 90%			13	μs
t_{WAKEUP}	Wakeup time	EN LOW to HIGH No RF input V_{OUT} to 90%			13	μs
LOGIC LEVEL INPUTS (EN)						
V_{IL}	Input low level				0.6	V
V_{IH}	Input high level		1.1			V
I_{IH}, I_{IH}	Input bias current		–1		1	μA

- (1) Parameters require temperature testing. Limits based on 3σ statistics characterized on a limited number of samples. Limits not guaranteed in production.
- (2) Limits based on 3σ statistics characterized on a limited number of samples. Limits not guaranteed in production.

TYPICAL PERFORMANCE CHARACTERISTICS

**CURRENT CONSUMPTION
vs
TEMPERATURE**




Figure 1.

**RF INPUT REFLECTION COEFFICIENT
(800 MHz TO 2 GHz)**




Figure 2.

**OUTPUT VOLTAGE
vs
INPUT POWER AT 800 MHz**




Figure 3.

**OUTPUT VOLTAGE
vs
INPUT POWER AT 2 GHz**




Figure 4.




Figure 5.




Figure 6.




Figure 7.




Figure 8.




Figure 9.




Figure 10.

DEVIATION DUE TO MODULATION
(HS-DPCCH, 3GPP TS 34.121-1 V8.7.0,
Table C10.1.4, Subtest 1, 800 MHz)




Figure 11.

DEVIATION DUE TO MODULATION
(HS-DPCCH, 3GPP TS 34.121-1 V8.7.0,
Table C10.1.4, Subtest 1, 2 GHz)




Figure 12.

DEVIATION DUE TO MODULATION
(HS-DPCCH, 3GPP TS 34.121-1 V8.7.0,
Table C10.1.4, Subtest 2, 800 MHz)




Figure 13.

DEVIATION DUE TO MODULATION
(HS-DPCCH, 3GPP TS 34.121-1 V8.7.0,
Table C10.1.4, Subtest 2, 2 GHz)




Figure 14.

DEVIATION DUE TO MODULATION
(HS-DPCCH, 3GPP TS 34.121-1 V8.7.0,
Table C10.1.4, Subtest 3, 800 MHz)




Figure 15.

DEVIATION DUE TO MODULATION
(HS-DPCCH, 3GPP TS 34.121-1 V8.7.0,
Table C10.1.4, Subtest 3, 2 GHz)




Figure 16.




Figure 17.




Figure 18.




Figure 19.




Figure 20.




Figure 21.




Figure 22.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH, 3GPP TS 34.121-1 V8.7.0,
Table C11.1.3, Subtest 3, 800 MHz)




Figure 23.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH, 3GPP TS 34.121-1 V8.7.0,
Table C11.1.3, Subtest 3, 2 GHz)




Figure 24.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH, 3GPP TS 34.121-1 V8.7.0,
Table C11.1.3, Subtest 4, 800 MHz)




Figure 25.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH, 3GPP TS 34.121-1 V8.7.0,
Table C11.1.3, Subtest 4, 2 GHz)




Figure 26.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH, 3GPP TS 34.121-1 V8.7.0,
Table C11.1.3, Subtest 5, 800 MHz)




Figure 27.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH, 3GPP TS 34.121-1 V8.7.0,
Table C11.1.3, Subtest 5, 2 GHz)




Figure 28.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH with 16QAM , 3GPP TS 34.121-1
V8.7.0,
Table C11.1.4, 800 MHz)




Figure 29.

DEVIATION DUE TO MODULATION
(HS-DPCCH and E-DCH with 16QAM , 3GPP TS 34.121-1
V8.7.0,
Table C11.1.4, 2 GHz)





Figure 30.



*The input coupling capacitor on the RF input pin may be omitted if the DC voltage on this pin is at ground.

Figure 31. Application Circuit

APPENDIX A: MEASUREMENT PROCEDURES

10-dB Log Conformance Error Over Temperature

The 10-dB log conformance error over temperature is a measure of the change in slope of the rms detector output over temperature. The measurement is performed by taking an ideal 10-dB step in input power with a CW signal at room temperature and measuring the change in output voltage. The measurement is then repeated at a different temperature and the 10-dB log conformance error over temperature is given in dB by [Equation 1](#).

$$10\text{-dB log conformance error} = 10 \cdot \left(\frac{\Delta V_{OUT}(T)}{\Delta V_{OUT}(25^{\circ}\text{C})} - 1 \right) \quad (1)$$

This measurement is taken on a statistical sample of parts. The 3σ limits from these samples are within the limits provided in the Electrical Characteristics table.

Straight Line 5-dB Step Error

The straight line 5-dB step error is a measure of the maximum error that results from fitting a straight line between two points of a 5-dB step as shown in [Figure 32](#). The straight line shown in bold represents a perfect 5-dB step, while the curved line represents the detector output (the curvature in this figure is exaggerated for explanation purposes). The maximum difference output voltage between these two curves is the straight line 5-dB step error.




Figure 32. Straight Line 5-dB Step Error

Response Temperature Coefficient & Response Temperature Sensitivity Spread - 1σ

The response temperature coefficient is a measure of the change in detector output voltage for a given RF input power. The measurement is performed by measuring the detector output voltage over temperature for a set CW RF input power. The response temperature gain coefficient expressed in $\text{m dB}/^{\circ}\text{C}$ is given by [Equation 2](#).

$$\text{Response temperature gain coefficient} = 1000 \cdot \frac{\Delta V_{OUT}}{V_{OUT,GAIN} \cdot \Delta T} \quad (2)$$

Where $V_{OUT,GAIN}$ is the output voltage gain expressed in V/dB . This measurement is taken on a statistical sample of parts. The mean of these samples are provided in the Electrical Characteristics table.

The response temperature sensitivity spread - 1σ , ΔTC_{VOUT} , is the 1σ variation in TC_{VOUT} .

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TRF1600DRV	PREVIEW	SON	DRV	6		TBD	Call TI	Call TI	0 to 70	6061	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBsolete: TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

TBD: The Pb-Free/Green conversion plan has not been defined.

Pb-Free (RoHS): TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

Pb-Free (RoHS Exempt): This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

(3) MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

DRV (S-PWSON-N6)

PLASTIC SMALL OUTLINE NO-LEAD



4206925/E 10/10

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
 - B. This drawing is subject to change without notice.
 - C. Small Outline No-Lead (SON) package configuration.
 -  D. The package thermal pad must be soldered to the board for thermal and mechanical performance. See the Product Data Sheet for details regarding the exposed thermal pad dimensions.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com