



S3880 - 32.768K CMOS Clock Oscillator

August 2011



- The Pletronics' S3880 is a quartz crystal controlled precision square wave generator with a CMOS output.
- The package is designed for high density surface mount designs.
- This is a low cost mass produced oscillator.
- Tape and Reel packaging
- 32.768 kHz
- 1.5 x 3.2 x 1.0 mm LCC Ceramic Package
- **Enable/Disable Function on pad 3**
- **Output on pad 1**
- **Excellent shock resistance**
- **Start-up Time of 0.5 Seconds or less**

Pletronics Inc. certifies this device is in accordance with the RoHS 6/6 (2002/95/EC) and WEEE (2002/96/EC) directives.

Pletronics Inc. guarantees the device does not contain the following:

Cadmium, Hexavalent Chromium, Lead, Mercury, PBB's, PBDE's

Weight of the Device: 0.04 grams

Moisture Sensitivity Level: 1 As defined in J-STD-020D.1

Second Level Interconnect code: e4

Absolute Maximum Ratings:

Parameter	Unit
V_{CC} Supply Voltage	-0.5V to +7.0V
V_i Input Voltage	-0.5V to V_{CC} + 0.5V
V_o Output Voltage	-0.5V to V_{CC} + 0.5V

Thermal Characteristics

The maximum die or junction temperature is 145°C

The thermal resistance junction to board is 60 to 100°C/Watt depending on the solder pads, ground plane and construction of the PCB.

ESD Rating

Model	Minimum Voltage	Conditions
Human Body Model	1500	MIL-STD-883 Method 3115
Charged Device Model	1000	JESD 22-C101

Part Number:

S3880	- 32.768K	-XX	
Packaging code or blank			T1K = 1000 per Tape and Reel T3K = 3000 per Tape and Reel
Smaller quantities or quantities that are not in 1K or 3K increments are all supplied as "cut tape" with no leader or trailer.			
Frequency in kHz			
Series Model			

Part Marking:



Y Year
 WW Week
 xxx Manufacturing lot information
 7604 Part designation

Reliability: Environmental Compliance

Parameter	Maximum Frequency Change	Condition
Mechanical Shock	±5ppm	5000g at 0.3mS, ½ sine
Vibration	±5ppm	20g from 10Hz to 2,000Hz

Parameter	Condition
Solderability	MIL-STD-883 Method 2003
Thermal Shock	MIL-STD-883 Method 1011, Condition A


Electrical Specification for Vcc 1.2V to 5.5V over - 55 to +125°C

Item	Min	Max	Unit	Condition
Frequency	32.768		kHz	
Frequency Calibration Tolerance	-20	+20	ppm	at $V_{CC} = 3.3V$ and $25^\circ C$
Frequency Stability *	-70	+20	ppm	when operating at -20 to $+70^\circ C$
	-170	+20	ppm	when operating at -40 to $+85^\circ C$
Frequency versus Supply	0	± 1.5	ppm/V	for V_{CC} range of 2.3 V to 5.5V
Output Waveform	CMOS			
Output High Level	$V_{CC} - 0.4$	-	V	$I_{OH} = 1.0mA$
Output Low Level	-	0.4	V	$I_{OL} = -1.0mA$
Output T_{RISE} and T_{FALL}	-	70	nS	$C_{LOAD} = 10pF$ T_R / T_F 10% to 90% and D.C. at 50% point of V_{CC} (See load circuit)
Output Symmetry	40	60	%	
V disable	-	20	%	of V_{CC} applied to pad 3
V enable	80	-	%	of V_{CC} applied to pad 3
Output leakage $V_{OUT} = V_{CC}$	-10	+10	uA	Pad 3 low, device disabled
$V_{OUT} = 0V$	-10	+10	uA	
Supply Current (I_{CC})	-	0.3	uA	$V_{CC} = 1.2 V$
	-	0.5	uA	$V_{CC} = 3.0 V$
	-	0.9	uA	$V_{CC} = 5.5 V$
Enable time	-	100	nS	Time for output to reach a logic state
Disable time	-	100	nS	Time for output to reach a high Z state
Start up time	-	0.5	S	Time for output to reach specified frequency
Operating Temperature Range	-55	+125	°C	
Storage Temperature Range	-55	+125	°C	



* Temperature characteristics Deviation in ppm = $(T - T_0)^2 * (-0.035\text{ppm/}^\circ\text{C}^2) \pm 10\%$
 T is temperature in $^\circ\text{C}$ T_0 is the turn over temperature in $^\circ\text{C}$

Specifications with Pad 3 E/D open circuit unless otherwise stated.


Typical Frequency versus Temperature Characteristics



Load Circuit and Test Waveform



Mechanical:



	Inches	mm
A	0.059 \pm 0.006	1.5 \pm 0.15
B	0.126 \pm 0.006	3.2 \pm 0.15
C	0.039 max	1.0 max
D ¹	0.020	0.50
E ¹	0.030	0.75

Contacts :

Gold 11.8 μ inches 0.3 μ m minimum over
 Nickel 50 to 350 μ inches 1.27 to 8.89 μ m

Not to Scale

¹ Typical dimensions

IMPORTANT: The pin assignments are different from many clock oscillators

Pad	Function	Note
1	Output	
2	Ground (GND)	
3	Enable/Disable Output	When this pad is not connected the oscillator shall operate. When this pad is logic low the output will be inhibited (high impedance state.) Recommend connecting this pad to V _{CC} if the oscillator is to be always on.
4	Supply Voltage (V _{CC})	Recommend connecting appropriate power supply bypass capacitors as close as possible.




Layout and application information

For Optimum Jitter Performance, Pletronics recommends:

- a ground plane under the device while avoiding connection to the two dot pads on the bottom. Use the PCB solder mask to isolate the two dot pads
- no large transient signals (both current and voltage) should be routed under the device
- do not layout near a large magnetic field such as a high frequency switching power supply
- do not place near piezoelectric buzzers or mechanical fans.

Reflow Cycle (typical for lead free processing)



The part may be reflowed 2 times without degradation.

Package Labeling

Label is 1" x 2.6" (25.4mm x 66.7mm)

Font is Courier New


Bar code is 39-Full ASCII

Label is 1" x 2.6" (25.4mm x 66.7mm)

Font is Arial



Tape and Reel: available for quantities of 1000 per reel, cut tape for < 1000



All Dimensions are in mm.

Tape and Reel	12mm Carrier Tape	Polycarbonate black, conductive
	300mm Leader and trailer	if Quantity in 1K or 3K increments
Cover Tape	Base Material	Polyester, conductive
	Adhesive Material	Pressure-sensitive
Reel	7 inch	Polystyrene

IMPORTANT NOTICE

Pletronics Incorporated (PLE) reserves the right to make corrections, improvements, modifications and other changes to this product at anytime. PLE reserves the right to discontinue any product or service without notice. Customers are responsible for obtaining the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to PLE's terms and conditions of sale supplied at the time of order acknowledgment.

PLE warrants performance of this product to the specifications applicable at the time of sale in accordance with PLE's limited warranty. Testing and other quality control techniques are used to the extent PLE deems necessary to support this warranty. Except where mandated by specific contractual documents, testing of all parameters of each product is not necessarily performed.

PLE assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using PLE components. To minimize the risks associated with the customer products and applications, customers should provide adequate design and operating safeguards.

PLE products are not designed, intended, authorized or warranted to be suitable for use in life support applications, devices or systems or other critical applications that may involve potential risks of death, personal injury or severe property or environmental damage. Inclusion of PLE products in such applications is understood to be fully at the risk of the customer. Use of PLE products in such applications requires the written approval of an appropriate PLE officer. Questions concerning potential risk applications should be directed to PLE.

PLE does not warrant or represent that any license, either express or implied, is granted under any PLE patent right, copyright, artwork or other intellectual property right relating to any combination, machine or process which PLE product or services are used. Information published by PLE regarding third-party products or services does not constitute a license from PLE to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from PLE under the patents or other intellectual property of PLE.

Reproduction of information in PLE data sheets or web site is permissible only if the reproduction is without alteration and is accompanied by associated warranties, conditions, limitations and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. PLE is not responsible or liable for such altered documents.

Resale of PLE products or services with statements different from or beyond the parameters stated by PLE for that product or service voids all express and implied warranties for the associated PLE product or service and is an unfair or deceptive business practice. PLE is not responsible for any such statements.

Contacting Pletronics Inc.

Pletronics Inc.
19013 36th Ave. West
Lynnwood, WA 98036-5761 USA

Tel: 425-776-1880
Fax: 425-776-2760
E-mail: ple-sales@pletronics.com
URL: www.pletronics.com

Copyright © 2009, 2010, 2011 Pletronics Inc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pletronics:](#)

[S3880-32.768K](#)