

LOC	DIST	REVISIONS				DAP		
		P	LTR	DESCRIPTION		DATE	DWN	APVD
G	14		D2	REVISED PER ECO-11-005027		11MAR11	RK	HMR



 WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
8 AWG SOLID OR STRANDED	8 AWG STRANDED	8 AWG SOLID OR STRANDED

- 1

STAMP AMP 8* APPROX AS SHOWN
- 2

COPPER PER ASTM B-152, ANNEALED
- 3

TIN PLATE 0.00254 [.000100] MIN THK
PER ASTM B-545



MAX RECOMMENDED OPERATING TEMPERATURE: 170°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93		 TE Connectivity						
			CHK DA PATTERSON 3-24-93								
VOLTAGE RATING: N/A	DIMENSIONS: mm[INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY 3-24-93	NAME						
CIRCULAR MIL AREA: 6.64-10.5mm² [13,100-20,800] SOLID OR STRANDED		0 PLC ± -		PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND - SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-35665 -						
		1 PLC ± -		-							
		2 PLC ± -		APPLICATION SPEC							
		3 PLC ± -		-							
		4 PLC ± -		ANGLES ± -							
	MATERIAL	FINISH		WEIGHT -							
				CUSTOMER DRAWING					SCALE 4:1	SHEET 1 of 1	REV D2