

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

31372-1000

Status:


Active

Overview:

Stac64™ Single, Multi-Pocket and Hybrid Header System

Description:

Stac64™ Hybrid Receptacle Assembly, 10 Circuit, Black, Polarization A



Documents:	
3D Model	Application Specification AS-31372-100 (PDF)
Drawing (PDF)	Application Specification AS-34729-020 (PDF)
Product Specification PS-31372-100 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	31372
Application	Power, Wire-to-Board
Comments	Polarization A, 6 x 1.50 and 4 x 2.8
Overview	Stac64™ Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64™
UPC	822348054497
Physical	
Circuits (maximum)	10
Circuits Detail	10
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.060/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Ports	10
Stackable	No
Temperature Range - Operating	-40°C to +100°C
Electrical	
Current - Maximum per Contact	22A, 30A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-31372-100, AS-34729-020
Product Specification	PS-31372-100
Sales Drawing	SD-31372-900

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[31372Series](#)

Mates With

34696 Stac64 Right Angle Assembly. [34695](#) Stac64 Vertical Assembly

Use With

MX150™ Terminal [33012](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

31372-1000