


TH-TM Indent Hinge







Characteristic

Choose the size from wide variety of selections.

Application

Various types of devices



Parts List

No.	Part Name	Material	Finish	Quantity
1	Hinge Piece(A)	BSP	Ni	1
2	Hinge Piece(B)			1
3	Shaft	BSW		1


Specification (a)

Model No.	A	B	C	D	E	F	F1	G	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM- 5	26	40	φ3	t1.5	17	7	13	φ3.2	4	3	19.5	2005
TH-TM-11	40	60	φ4		26	10	20	φ4.3	5	5	44.0	2011

Specification (b)

Model No.	A	B	C	D	E	F	F1	G	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM-19	16	30	φ1.5	t0.5	9	4.25	21.5	φ2.7	4	—	3.0	2019
TH-TM-16	20	25	φ2	t1	12	5.5	14	φ2.8		—	5.5	2016
TH-TM- 1		30	φ3		13	5	20	φ3.2		—	9.0	2001

TH-TM Hinge - Drawn bar





Characteristic

By using drawn material, the diameters of the pin and spine of the hinge are minimized.

Application

Measuring instruments



Parts List

No.	Part Name	Material	Finish	Quantity
1	Hinge Piece(A)	C3604	Ni	1
2	Hinge Piece(B)			1
3	Shaft	BSW		1

Specification (a)

Model No.	B	F	F1	G	M	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM-92	50	7	18	φ6.5	φ3.2	5	20	55.0	2106
TH-TM-15	76	8	30	φ8.6	φ4.6		—	83.0	2015
TH-TM-93	90	15				9	—	98.0	2107

Specification (b)

Model No.	B	F	F1	G	M	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM-94	130	20	30	φ8.6	φ4.6	13	—	144.0	2108

